




Help for choosing the TRIO AC UPS

Select your Buffer times for TRIO AC UPS with integrated battery.



TRIO UPS, 1~		
		
Input	96 V AC ... 138 V AC	184 V AC ... 264 V AC
W x H x D in mm	210 x 170 x 136	210 x 170 x 136
	120 V / 750 VA	230 V / 750 VA
Type	TRIO-UPS-2G/1AC/1AC/120V/750VA	TRIO-UPS-2G/1AC/1AC/230V/750VA
Item no.	2905908	2905909
Information	Lead AGM technology	Lead AGM technology

Buffer times for TRIO AC UPS:

2x: In these cases, you need another UPS-BAT/PB/24DC/4AH type battery module ([1274117](#)) with the same capacity (4 Ah).

Load Current	Buffertime														
	Minutes												Hours		
	1	1.5	2	4	6	8	10	15	20	30	40	50	1	1.5	
50 W													2x	2x	2x
100 W										2x	2x	2x			
150 W								2x	2x	2x					
200 W							2x	2x	2x						
250 W						2x	2x	2x							
300 W				2x	2x	2x									
400 W				2x	2x	2x									
500 W			2x	2x	2x										
600 W		2x	2x	2x											

2x: In this case, two battery modules of the same capacity are required.
The data is based on an ambient temperature of +25°C at start of use.