

2025 Winter Specials

Quarterly Special valid from January 1st – March 31st, 2025

New Automatic Stripping Device E.FOX S 10

NEW

With the electric E.FOX S 10 automatic stripping device, you can strip wires with different cross-sections and types of insulation easily and efficiently. The compact automatic stripping device can be integrated into and controlled via worker assistance systems.



Conductor cross-section	0.08 mm ² ... 10 mm ²	28 AWG ... 8 AWG
Stripping length	2 mm ... 20 mm	
Order no.	1554298	
Promo Price	\$7,250	



All orders must reference promo code *****WINTER2025*****. Quarterly Special valid from January 1st – March 31st, 2025. All prices are customer net each.

*Please note that ALL pricing is in CAD and this special is only available in Canada

Axioline Smart Elements

Remote-I/O-systems

The plug-in Axioline Smart Elements are system-independent I/O modules without bus communication. The individual element only supports the I/O function.

Bus communication for the relevant I/O system is only realized in conjunction with a backplane, which functions similarly to an adapter. The Axioline Smart Elements are therefore universal and flexible to use.



- 1 Select a bus coupler
- 2 Select a 4 or 6 channel base
- 3 Populate with cards

Order no.	Description	Details	Promo Price
2702782	AXL F BK EIP EF	EtherNet/IP bus coupler. Supports DLR	\$595.00
2403869	AXL F BK PN TPS	Profinet bus coupler	\$580.00
2688459	AXL F BK ETH	Modbus bus coupler	\$495.00
2688899	AXL F BK EC	EtherCAT bus coupler	\$450.00
1088136	AXL F BP SE6	6 Slot base	\$185.00
1088135	AXL F BP SE4	4 Slot base	\$145.00
1088062	AXL SE AI4 I 4-20	4 channel 4-20 analog input	\$220.00
1088123	AXL SE AO4 I 4-20	4 channel 4-20 analog output	\$245.00
1088127	AXL SE DI16/1	16 channel digital input 24 V DC	\$105.00
1088129	AXL SE DO16/1	16 channel digital output 24 V DC	\$125.00

More IO cards can be found online

[View product list](#)

Features

- ✓ Compact Design
- ✓ Push-in technology
- ✓ Wide variety of IO options, analog, digital, serial, etc...
- ✓ Solutions for Safety; PROFIsafe or Safety over EtherCAT (FSOE) modules available

Current Measuring Transducers

MCR-SL-CUC Series

MCR AC/DC current measuring transducers measure DC and AC currents of all waveforms, as well as distorted currents, and convert them into an analog standard signal. The portfolio is graded with different measuring ranges for currents up to 600 A.



Order no.	Description	Input Range (Amps)	Output Signal	Promo Price
2308027	MCR-SL-CUC-100-I	0...100	4-20 mA	\$139.00
2308030	MCR-SL-CUC-200-I	0...200	4-20 mA	\$149.00
2308043	MCR-SL-CUC-300-I	0...300	4-20 mA	\$154.00
2308072	MCR-SL-CUC-400-I	0...400	4-20 mA	\$164.00
2308085	MCR-SL-CUC-500-I	0...500	4-20 mA	\$179.00
2308098	MCR-SL-CUC-600-I	0...600	4-20 mA	\$189.00

Features

- ✓ Also suitable for decentralized use due to the compact dimensions
- ✓ Variable mounting on DIN rail or mounting panel
- ✓ Easy wiring due to plug-in connection terminal blocks
- ✓ For insulated conductors up to 32 mm in diameter

Ethernet Surge Protection

DT-LAN CAT 6+

Protect your sensitive Ethernet based communication devices against transients up to 10kA with the DT-LAN-CAT6+.

Features and Benefits

- ✓ Suitable for Category 6 speeds up to 10 Gbps
- ✓ Protection for 8 signal paths via RJ45 connector
- ✓ Class E_A/CAT6_A
- ✓ PoE and ISDN S⁰ protection
- ✓ Remove ground connection adaptor for easy DIN rail installation



Order no.	Description	Promo Price
2881007	DT-LAN-CAT.6+	\$125.00

IP67 Class2 Power Supply

TRIO IP67

Your Advantages

- ✓ Direct installation at the load in the field reduces cable lengths and creates space in the control cabinet
- ✓ The robust aluminum housing ensures high system availability with resistance to extreme ambient conditions (temperature, dust, & water)
- ✓ High shock and vibration resistance, plus electric strength
- ✓ Improved diagnostic options in the field with DC OK-LED & AC OK-LED
- ✓ NEC Class2 (POUT <100 W)



Order no.	Description	Connector	Promo Price
1278302	TRIO-PS67/1AC/24DC/3.75/INC	7/8"	\$285.00
1278165	TRIO-PS67/1AC/24DC/3.75/M12	M12	\$285.00
1376306	TRIO-PS67/1AC/24DC/3.75/M12-A	M12-A	\$285.00
1278301	TRIO-PS67/1AC/24DC/3.75/IPD	Push-In	\$285.00

HEAVYCON

EVO Connector set

Heavyduty connector set consisting of sleeve housing, panel mounting base, push-in contact insert and cable gland.



Features and Benefits

- ✓ Easy handling & right connection for every application
- ✓ Push-in Contact for fast connection
- ✓ IP degree of protection (when plugged in): IP66

[Download the HEAVYCON brochure](#)

Order no.	Description	Details	Type/Size	Promo Price
1407710	HC-EVO-B06PT-BWSC-HL-M20-PLRBK	Connector set, Single locking latch, with cover	B6	\$40.00
1407711	HC-EVO-B10PT-BWD-HL-M25-PLRBK	Connector set, Double locking latch, w/o cover	B10	\$49.00
1407712	HC-EVO-B16PT-BWD-HH-M25-PLRBK	Connector set, Double locking latch, w/o cover	B16	\$52.00
1407713	HC-EVO-B24PT-BWD-HH-M32-PLRBK	Connector set, Double locking latch, w/o cover	B24	\$56.00
1408791	HC-EVO-B10PT-BWSC-HL-M25-PLRBK	Connector set, Single locking latch, with cover	B10	\$55.00
1408793	HC-EVO-B16PT-BWSC-HH-M25-PLRBK	Connector set, Single locking latch, with cover	B16	\$60.00
1408794	HC-EVO-B24PT-BWSC-HH-M32-PLRBK	Connector set, Single locking latch, with cover	B24	\$64.00

Tool deals you wouldn't want to miss!

TOOLfox

	\$33.50 CUTFOX 12 1212128 Cable cutters, up to 12 mm diameter cables		\$55.25 CUTFOX 18 1212129 Cable cutters, up to 18 mm diameter cables • Spring loaded with lock • Angled head • Ergonomic design		
	\$155.00 CRIMPFOX CENTRUS 10S 1213154 Crimping tool for ferrules from 24-8 AWG. Square crimp shape		\$155.00 CRIMPFOX CENTRUS 10H 1213156 Crimping tool for ferrules from 24-8 AWG. Hexagonal crimp shape		
	\$37.00 WIREFOX-D 11 1212160 Stripping tool for power and data lines. Diameter: 2.5-11 mm		\$79.50 WIREFOX-E 10 1212706 Stripping tool, for cables and conductors from: 0.02 - 10 mm ²		\$72.25 WIREFOX-D 40 1212161 Stripping tool for conductors and cables. 4.5-40 mm adjustable cutting depth
					\$37.00 ea. AI SORTI BOX RD 3202960 AI-TWIN SORTI BOX BU 3202986 Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs.