


2026 Fall Specials

Quarterly Special valid from October 1st – December 31st, 2026

Power Supply and UPS System Combined! TRIO3-CAP

Power interruptions can put data at risk and processes are interrupted therefore a reliable, maintenance-free power supply is becoming increasingly important.

The new TRIO3 CAP module is the first device on the market that combines a power supply, a DC UPS, and integrated energy storage, including an on-board communication interface, in one package.



Features and Benefits

- ✓ Up to 50% less wiring with a space-saving design
- ✓ CAP boost 350% for 350ms for high current dynamic loads
- ✓ Series wiring for 48 V DC networks
- ✓ Comms for parametrization and wired signals for status

Order no.	Description	Details	Promo Price
1467800	TRIO3-CAP/1AC/24DC/5/3KJ/USB-485	Single phase 5 A	\$599.00
1467808	TRIO3-CAP/1AC/24DC/10/6KJ/USB-485	Single phase 10 A	\$799.00
1467815	TRIO3-CAP/1AC/24DC/20/12KJ/USB-485	Single phase 20 A	\$1,069.00

All orders must reference promo code *****FALL2026*****. Quarterly Special valid from October 1st – December 31st, 2026. All prices are customer net each.

*Please note that ALL pricing is in CAD and this special is only available in Canada

Unmanaged Switches


Discover the robust and reliable unmanaged switches from Phoenix Contact. Our FL SWITCH 1000 and 1100 series for DIN rails feature versatile connection options and easy operation for automation applications. Simply unpack, connect, and use. Unmanaged switches are fully plug-and-play-capable and do not require configuration. This means that users can operate and install them easily. Status LEDs on the switches provide basic information on the connection statuses and port activity at a glance. This means that an interrupted connection, e.g., due to a faulty cable, can be diagnosed quickly.



Details	Five RJ45 ports with 10/100 Mbps on all ports, automatic data transmission speed detection, autocrossing, and QoS	Eight RJ45 ports with 10/100 Mbps on all ports, automatic data transmission speed detection, autocrossing, and QoS	Sixteen RJ45 ports with 10/100 Mbps on all ports, automatic data transmission speed detection, autocrossing, and QoS	Five RJ45 ports with 10/100/1000 Mbps on all ports, automatic data transmission speed detection, autocrossing, and QoS	Eight RJ45 ports with 10/100/1000 Mbps on all ports, automatic data transmission speed detection, autocrossing, and QoS
Description	FL SWITCH 1005N	FL SWITCH 1008N	FL SWITCH 1016N	FL SWITCH 1105N	FL SWITCH 1108N
Order no.	1085039	1085256	1085255	1085254	1085243
Promo Price	\$105.00	\$157.00	\$305.00	\$180.00	\$275.00

In-cabinet RJ45 Patch Cables

Phoenix Contact RJ45 In-Cabinet Patch Cables deliver reliable, high-speed Ethernet connectivity designed specifically for industrial control cabinets and protected environments



High-speed Ethernet performance up to 10 Gbps (CAT6A)

Shielded S/FTP design for dependable data transmission

Ideal for control cabinets and protected industrial environments

Available in multiple lengths and colors for easy cable management


Pre-terminated RJ45 connectors enable quick, hassle-free installation

Order no.	Description	Details	Promo Price
1227560	NBC-R4OC/1,0-BC5/R4OC	Patch cable, 2x2xAWG26/7, CAT5, gray, 1 m	\$7.99
1227562	NBC-R4OC/2,0-BC5/R4OC	Patch cable, 2x2xAWG26/7, CAT5, gray, 2 m	\$9.49
1227563	NBC-R4OC/3,0-BC5/R4OC	Patch cable, 2x2xAWG26/7, CAT5, gray, 3 m	\$10.99
1227564	NBC-R4OC/5,0-BC5/R4OC	Patch cable, 2x2xAWG26/7, CAT5, gray, 5 m	\$13.99
1227575	NBC-R4OC/1,0-BC6A/R4OC	Patch cable, 4x2xAWG26/7, CAT6A, gray, 1 m	\$9.99
1227580	NBC-R4OC/2,0-BC6A/R4OC	Patch cable, 4x2xAWG26/7, CAT6A, gray, 2 m	\$11.49
1227581	NBC-R4OC/3,0-BC6A/R4OC	Patch cable, 4x2xAWG26/7, CAT6A, gray, 3 m	\$12.99
1227583	NBC-R4OC/5,0-BC6A/R4OC	Patch cable, 4x2xAWG26/7, CAT6A, gray, 5 m	\$16.49

FIX Terminal Blocks


Unpack, connect, and you're done!

The ready-to-use FIX blocks with Push-in connection technology enable quick and easy mounting in confined spaces. The FIX block system consists of distribution blocks, function distribution blocks, and device terminal blocks.



Features and Benefits

- ✓ Significant space savings with the extremely small design
- ✓ Flexible use with DIN rail and direct mounting adapters or adhesive mounting
- ✓ Time-saving conductor connection with tool-free and maintenance-free Push-in
- ✓ Distribution and collection blocks with 2, 4, 6, 12, and 18 terminal points
- ✓ Available in 11 colours for safe and intuitive installation



Order no.	Description	Number of Connections	Current Rating	Wire Gauges	Colour	Promo Price
1045923	PTFIX 2X1,5 GY	2	20 A	26 – 12 AWG	Grey	\$0.75
1046608	PTFIX 4X1,5 GY	4	20 A	26 – 12 AWG	Grey	\$1.40
1046610	PTFIX 4X1,5 BU	4	20 A	26 – 12 AWG	Blue	\$1.40
1046611	PTFIX 4X1,5 RD	4	20 A	26 – 12 AWG	Red	\$1.40
1047466	PTFIX 4/6X1,5 GY	1+6	Input: 30 A Output: 20 A	Input: 24-10 AWG Output: 26-12 AWG	Grey	\$2.25
1047418	PTFIX 4/18X1,5 GY	1+18	Input: 30 A Output: 20 A	Input: 24-10 AWG Output: 26-12 AWG	Grey	\$5.95
1049497	PTFIX 1,5-NS35	DIN rail adapter		FIX blocks in vertical direction		\$0.70
1049503	PTFIX 1,5-F	Flange		Screw fixing, for direct mounting		\$0.35


6 Pole Force Guided Relays

RIFLINE Series

The highly compact RIFLINE complete relay module switches reliably with six force-guided contacts and Push-in connection technology. Benefit from A2 potential distribution via plug-in bridges on the input side and reliable feedback in your application.

Features and Benefits

- ✓ Push-in connection technology
- ✓ Overall width of just 20.9 mm
- ✓ Relay module with 6-position, force-guided relay
- ✓ A2 potential distribution via plug-in bridges on the input side
- ✓ Reliable feedback



Order no.	Description	Contacts	Promo Price
1732886	RIF-RPT-LDP-24DC/1X-2/5X1/AU/FG	5 NO + 1 NC	\$45.00
1732905	RIF-RPT-LDP-24DC/2X-2/4X1/AU/FG	4 NO + 2 NC	\$45.00

Tool deals you wouldn't want to miss!

TOOLfox

	\$35.50 CUTFOX 12 1212128		\$58.50 CUTFOX 18 1212129		
	Cable cutters, up to 12 mm diameter cables		Cable cutters, up to 18 mm diameter cables • Spring loaded with lock • Angled head • Ergonomic design		
	\$163.50 CRIMPFOX CENTRUS 10S 1213154		\$163.00 CRIMPFOX CENTRUS 10H 1213156		\$76.00 WIREFOX-D 40 1212161
	Crimping tool for ferrules from 24-8 AWG. Square crimp shape		Crimping tool for ferrules from 24-8 AWG. Hexagonal crimp shape		Stripping tool for conductors and cables. 4.5-40 mm adjustable cutting depth
	\$39.00 WIREFOX-D 11 1212160		\$83.75 WIREFOX-E 10 1212706		\$38.00 ea. AI SORTI BOX RD 3202960 AI-TWIN SORTI BOX BU 3202986 Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs.
	Stripping tool for power and data lines. Diameter: 2.5-11 mm		Stripping tool, for cables and conductors from: 0.02 - 10 mm²		