

UL-certified combinations of ferrule and tool

Ferrules				Hand tools			
 The ferrules from Phoenix Contact are UL-certified in combination with selected crimping tools and automatic crimping devices. With this UL 486F (E 488001) certification, we meet both global and local market requirements in terms of quality, safety, and compatibility. The UL-certified combinations of ferrules and tools can be found in this overview.							
Item no.	Type	mm²	AWG	CRIMPFOX 6 1212034	CRIMPFOX DUO 10 1031721	CRIMPFOX CENTRUS 6S 1213144/1202882 6H 1213146/1202883 10S 1213154 10H 1213156	CRIMPFOX 25R 1212039
1034128	AI 0,14 - 6 GY	0.14	26	●	●	●	
3203011	AI 0,14 - 8 GY	0.14	26	●	●	●	
2100148	AI 0,14 - 6 BN	0.14	26	●	●	●	
2100149	AI 0,14 - 8 BN	0.14	26	●	●	●	
3203024	AI 0,25 - 6 YE	0.25	24	●	●	●	
3203040	AI 0,25 - 6 BU	0.25	24	●	●	●	
3201364	AI 0,25 - 8 BU	0.25	24	●	●	●	
3203037	AI 0,25 - 8 YE	0.25	24	●	●	●	
2100145	AI 0,25 - 8 YE-1000	0.25	24	●	●	●	
2100146	AI 0,25 - 6 VT	0.25	24	●	●	●	
2100147	AI 0,25 - 8 VT	0.25	24	●	●	●	
3203053	AI 0,34 - 6 TQ	0.34	22	●	●	●	
3203066	AI 0,34 - 8 TQ	0.34	22	●	●	●	
2100141	AI 0,34 - 8 TQ-25000	0.34	22	●	●	●	
3241129	AI 0,34 - 10 TQ	0.34	22	●	●	●	
2100142	AI 0,34 - 10 TQ-25000	0.34	22	●	●	●	
3200645	AI 0,34 - 12 TQ	0.34	22	●	●	●	
2100138	AI 0,34 - 6 PK	0.34	22	●	●	●	
2100139	AI 0,34 - 8 PK	0.34	22	●	●	●	
3201301	AI 0,5 - 6 OG	0.5	20	●	●	●	
3200687	AI 0,5 - 6 WH	0.5	20	●	●	●	
3201123	AI 0,5 - 8 OG	0.5	20	●	●	●	
3202902	AI 0,5 - 8 OG-1000	0.5	20	●	●	●	
3200014	AI 0,5 - 8 WH	0.5	20	●	●	●	
3200881	AI 0,5 - 8 WH-1000	0.5	20	●	●	●	
2100133	AI 0,5 - 8 WH-25000	0.5	20	●	●	●	
2100136	AI 0,5 - 10 WH-25000	0.5	20	●	●	●	
3201275	AI 0,5 - 10 WH	0.5	20	●	●	●	
3241126	AI 0,5 - 10 OG	0.5	20	●	●	●	
3200690	AI 0,75 - 6 GY	0.75	18	●	●	●	
2100120	AI 0,75 - 6 GY-25000	0.75	18	●	●	●	
3201314	AI 0,75 - 6 WH	0.75	18	●	●	●	
2100106	AI 0,75 - 6 BU	0.75	18	●	●	●	
3200027	AI 0,75 - 8 BU	0.75	18	●	●	●	
1213200	AI 0,75 - 8 BU -1000	0.75	18	●	●	●	
3200519	AI 0,75 - 8 GY	0.75	18	●	●	●	

* Only available in selected countries.

[illegible]

UL-certified combinations of ferrule and tool

Ferrules				Hand tools			
 The ferrules from Phoenix Contact are UL-certified in combination with selected crimping tools and automatic crimping devices. With this UL 486F (E 488001) certification, we meet both global and local market requirements in terms of quality, safety, and compatibility. The UL-certified combinations of ferrules and tools can be found in this overview.							
Item no.	Type	mm ²	AWG	CRIMPFOX 6 1212034	CRIMPFOX DUO 10 1031721	CRIMPFOX CENTRUS 6S 1213144/1202882 6H 1213146/1202883 10S 1213154 10H 1213156	CRIMPFOX 25R 1212039
3200894	AI 0,75 - 8 GY-1000	0.75	18	●	●	●	
2100121	AI 0,75 - 8 GY-25000	0.75	18	●	●	●	
3201110	AI 0,75 - 8 WH	0.75	18	●	●	●	
2100118	AI 0,75 - 8 WH-1000	0.75	18	●	●	●	
3201288	AI 0,75 - 10 GY	0.75	18	●	●	●	
3203118	AI 0,75 - 10 GY-1000	0.75	18	●	●	●	
2100122	AI 0,75 - 10 GY-25000	0.75	18	●	●	●	
2100109	AI 0,75 - 10 BU	0.75	18	●	●	●	
2100114	AI 0,75 - 10 WH	0.75	18	●	●	●	
3200849	AI 0,75 - 12 GY	0.75	18	●	●	●	
2100105	AI 0,75 - 12 BU	0.75	18	●	●	●	
2100110	AI 0,75 - 12 WH	0.75	18	●	●	●	
3200742	AI 1 - 6 RD	1	18	●	●	●	
3201327	AI 1 - 6 YE	1	18	●	●	●	
3200030	AI 1 - 8 RD	1	18	●	●	●	
3200904	AI 1 - 8 RD-1000	1	18	●	●	●	
2100096	AI 1 - 8 RD-25000	1	18	●	●	●	
3201097	AI 1 - 8 YE	1	18	●	●	●	
3200182	AI 1 - 10 RD	1	18	●	●	●	
3203121	AI 1 - 10 RD-1000	1	18	●	●	●	
2100098	AI 1 - 10 RD-25000	1	18	●	●	●	
2100089	AI 1 - 10 YE	1	18	●	●	●	
3200674	AI 1 - 12 RD	1	18	●	●	●	
1200311	AI 1 - 12 RD-1000	1	18	●	●	●	
2100086	AI 1 - 12 YE	1	18	●	●	●	
3200043	AI 1,5 - 8 BK	1.5	16	●	●	●	
3200917	AI 1,5 - 8 BK-1000	1.5	16	●	●	●	
2100078	AI 1,5 - 8 BK-20000	1.5	16	●	●	●	
3201136	AI 1,5 - 8 RD	1.5	16	●	●	●	
3202928	AI 1,5 - 8 RD-1000	1.5	16	●	●	●	
2100071	AI 1,5 - 10 RD	1.5	16	●	●	●	
3200195	AI 1,5 - 10 BK	1.5	16	●	●	●	
3203134	AI 1,5 - 10 BK-1000	1.5	16	●	●	●	
2100080	AI 1,5 - 10 BK-20000	1.5	16	●	●	●	
2100070	AI 1,5 - 12 RD	1.5	16	●	●	●	

* Only available in selected countries.

[illegible]

UL-certified combinations of ferrule and tool

Ferrules				Hand tools			
 The ferrules from Phoenix Contact are UL-certified in combination with selected crimping tools and automatic crimping devices. With this UL 486F (E 488001) certification, we meet both global and local market requirements in terms of quality, safety, and compatibility. The UL-certified combinations of ferrules and tools can be found in this overview.							
Item no.	Type	mm²	AWG	CRIMPFOX 6 1212034	CRIMPFOX DUO 10 1031721	CRIMPFOX CENTRUS 6S 1213144/1202882 6H 1213146/1202883 10S 1213154 10H 1213156	CRIMPFOX 25R 1212039
3201482	AI 1,5 - 12 BK	1.5	16	●	●	●	
1200310	AI 1,5 - 12 BK-1000	1.5	16	●	●	●	
3200056	AI 1,5 - 18 BK	1.5	16	●	●	●	
3241125	AI 1,5 - 18 RD	1.5	16	●	●	●	
3200522	AI 2,5 - 8 BU	2.5	14	●	●	●	
3200920	AI 2,5 - 8 BU-1000	2.5	14	●	●	●	
2100063	AI 2,5 - 8 BU-15000	2.5	14	●	●	●	
3200069	AI 2,5 - 8 GY	2.5	14	●	●	●	
1213201	AI 2,5 - 8 GY-1000	2.5	14	●	●	●	
3200962	AI 2,5 - 12 BU	2.5	14	●	●	●	
1200309	AI 2,5 - 12 BU-1000	2.5	14	●	●	●	
2100064	AI 2,5 - 12 BU-10000	2.5	14	●	●	●	
3200205	AI 2,5 - 12 GY	2.5	14	●	●	●	
3200580	AI 2,5 - 18 BU	2.5	14	●	●	●	
3200072	AI 2,5 - 18 GY	2.5	14	●	●	●	
3200535	AI 4 - 10 GY	4	12	●	●	●	
1200308	AI 4 - 10 GY-1000	4	12	●	●	●	
2100055	AI 4 - 10 GY-5000	4	12	●	●	●	
3200085	AI 4 - 10 OG	4	12	●	●	●	
1213202	AI 4 - 10 OG-1000	4	12	●	●	●	
2100054	AI 4 - 10 OG-5000	4	12	●	●	●	
3200959	AI 4 - 12 GY	4	12	●	●	●	
1200307	AI 4 - 12 GY-1000	4	12	●	●	●	
2100053	AI 4 - 12 GY-5000	4	12	●	●	●	
3200438	AI 4 - 12 OG	4	12	●	●	●	
3200593	AI 4 - 18 GY	4	12	●	●	●	
3200098	AI 4 - 18 OG	4	12	●	●	●	
3201107	AI 6 - 12 BK	6	10	●	●	●	
3200108	AI 6 - 12 GN	6	10	●	●	●	
1213203	AI 6 - 12 GN-1000	6	10	●	●	●	
3200548	AI 6 - 12 YE	6	10	●	●	●	
2100047	AI 6 - 12 YE-1000	6	10	●	●	●	
3200111	AI 6 - 18 GN	6	10	●	●	●	
3200603	AI 6 - 18 YE	6	10	●	●	●	
2100048	AI 6 - 18 YE-2500	6	10	●	●	●	

* Only available in selected countries.

[illegible]

UL-certified combinations of ferrule and tool

Ferrules				Hand tools			
 The ferrules from Phoenix Contact are UL-certified in combination with selected crimping tools and automatic crimping devices. With this UL 486F (E 488001) certification, we meet both global and local market requirements in terms of quality, safety, and compatibility. The UL-certified combinations of ferrules and tools can be found in this overview.							
Item no.	Type	mm ²	AWG	CRIMPFOX 6 1212034	CRIMPFOX DUO 10 1031721	CRIMPFOX CENTRUS 6S 1213144/1202882 6H 1213146/1202883 10S 1213154 10H 1213156	CRIMPFOX 25R 1212039
2100043	AI 6 - 18 BK	6	10	●	●	●	
3200124	AI 10 - 12 BN	10	8		●	●	●
3201068	AI 10 - 12 IV	10	8		●	●	●
3200551	AI 10 - 12 RD	10	8		●	●	●
2100041	AI 10 - 12 RD-2500	10	8		●	●	●
3200137	AI 10 - 18 BN	10	8		●	●	●
2100038	AI 10 - 18 IV	10	8		●	●	●
3200616	AI 10 - 18 RD	10	8		●	●	●
2100037	AI 10 - 18 RD-1500	10	8		●	●	●
3200564	AI 16 - 12 BU	16	6				●
2100036	AI 16 - 12 BU-1500	16	6				●
3201152	AI 16 - 12 GN	16	6				●
3201181	AI 16 - 12 IV	16	6				●
3200140	AI 16 - 12 WH	16	6				●
3200629	AI 16 - 18 BU	16	6				●
2100035	AI 16 - 18 BU-1000	16	6				●
3201330	AI 16 - 18 GN	16	6				●
3200153	AI 16 - 18 WH	16	6				●
3200412	AI 25 - 16 BK	25	4				●
3201084	AI 25 - 16 BN	25	4				●
3200577	AI 25 - 16 YE	25	4				●
2100030	AI 25 - 18 BN	25	4				●
2100032	AI 25 - 18 BK	25	4				●
3201505	AI 25 - 18 YE	25	4				●
2100031	AI 25 - 22 BN	25	4				●
3200739	AI 25 - 22 BK	25	4				●
3200700	AI 25 - 22 YE	25	4				●
3201071	AI 35 - 16 BE	35	2				
3200441	AI 35 - 16 RD	35	2				
2100028	AI 35 - 18 BE	35	2				
3201495	AI 35 - 18 RD	35	2				
2100027	AI 35 - 25 BE	35	2				
3200713	AI 35 - 25 RD	35	2				
3200454	AI 50 - 20 BU	50	1/0				
3201178	AI 50 - 20 OL	50	1/0				

* Only available in selected countries.

[illegible]

UL-certified combinations of ferrule and tool

Ferrules				Hand tools			
 The ferrules from Phoenix Contact are UL-certified in combination with selected crimping tools and automatic crimping devices. With this UL 486F (E 488001) certification, we meet both global and local market requirements in terms of quality, safety, and compatibility. The UL-certified combinations of ferrules and tools can be found in this overview.							
Item no.	Type	mm ²	AWG	CRIMPFOX 6 1212034	CRIMPFOX DUO 10 1031721	CRIMPFOX CENTRUS 6S 1213144/1202882 6H 1213146/1202883 10S 1213154 10H 1213156	CRIMPFOX 25R 1212039
2100023	AI 50 - 25 OL	50	1/0				
3240678	AI 50 - 25 BK	50	1/0				
3200726	AI 50 - 25 BU	50	1/0				
3200218	A 0,5 - 6	0.5	20	●	●	●	
3202481	A 0,5 - 8	0.5	20	●	●	●	
3202494	A 0,5 - 10	0.5	20	●	●	●	
3200221	A 0,75 - 6	0.75	18	●	●	●	
3200234	A 0,75 - 10	0.75	18	●	●	●	
3200247	A 1 - 6	1	18	●	●	●	
3200250	A 1 - 10	1	18	●	●	●	
3200263	A 1,5 - 7	1.5	16	●	●	●	
3200276	A 1,5 - 10	1.5	16	●	●	●	
3202588	A 1,5 - 12	1.5	16	●	●	●	
3202601	A 1,5 - 18	1.5	16	●	●	●	
3200289	A 2,5 - 7	2.5	14	●	●	●	
2100062	A 2,5 - 10	2.5	14	●	●	●	
3200292	A 2,5 - 12	2.5	14	●	●	●	
3202821	A 2,5 - 18	2.5	14	●	●	●	
3200302	A 4 - 9	4	12	●	●	●	
3200315	A 4 - 12	4	12	●	●	●	
2100050	A 4 - 15	4	12	●	●	●	
3202834	A 4 - 18	4	12	●	●	●	
3202520	A 6 - 10	6	10	●	●	●	
3200328	A 6 - 12	6	10	●	●	●	
2100042	A 6 - 15 -1000	6	10	●	●	●	
2100044	A 6 - 18 -1000	6	10	●	●	●	
3200331	A 10 - 12	10	8		●	●	●
2100039	A 10 - 15	10	8		●	●	●
3200344	A 10 - 18	10	8		●	●	●
3200425	A 16 - 12	16	6				●
2100033	A 16 - 18	16	6				●
1090632	A 16 - 25	16	6				●
1090633	A 16 - 32	16	6				●
3200360	A 25 - 15	25	4				●
3200373	A 25 - 18	25	4				●

* Only available in selected countries.

[illegible]

UL-certified combinations of ferrule and tool

Ferrules				Hand tools			
 The ferrules from Phoenix Contact are UL-certified in combination with selected crimping tools and automatic crimping devices. With this UL 486F (E 488001) certification, we meet both global and local market requirements in terms of quality, safety, and compatibility. The UL-certified combinations of ferrules and tools can be found in this overview.							
Item no.	Type	mm ²	AWG	CRIMPFOX 6 1212034	CRIMPFOX DUO 10 1031721	CRIMPFOX CENTRUS 6S 1213144/1202882 6H 1213146/1202883 10S 1213154 10H 1213156	CRIMPFOX 25R 1212039
1090634	A 25 - 25	25	4				•
1090636	A 25 - 32	25	4				•
3200399	A 35 - 18	35	2				
1090638	A 35 - 32	35	2				
2100025	A 50 - 18	50	1/0				
2100024	A 50 - 25	50	1/0				
1090639	A 50 - 32	50	1/0				
1208966	AI 0,5 - 8 WH-GB	0.5	20	•	•	•	
3203150	AI 0,5 - 10 WH-GB	0.5	20	•	•	•	
1208979	AI 0,75 - 8 GY-GB	0.75	18	•	•	•	
3203163	AI 0,75 - 10 GY-GB	0.75	18	•	•	•	
3203299	AI 0,75 - 10 GY-GB-1000	0.75	18	•	•	•	
1208982	AI 1 - 8 RD-GB	1	18	•	•	•	
1208869	AI 1 - 10 RD-GB-1000	1	18	•	•	•	
3202892	AI 1,5 - 8 BK-GB-1000	1.5	16	•	•	•	
1208872	AI 1,5 - 10 BK-GB-1000	1.5	16	•	•	•	
2100128	AI-GB 0,5 - 8 OG	0.5	20	•	•	•	
2100130	AI-GB 0,5 - 10 OG	0.5	20	•	•	•	
2100131	AI-GB 0,5 - 8 WH	0.5	20	•	•	•	
2100134	AI-GB 0,5 - 8 WH-25000	0.5	20	•	•	•	
2100132	AI-GB 0,5 - 10 WH	0.5	20	•	•	•	
2100135	AI-GB 0,5 - 10 WH-25000	0.5	20	•	•	•	
2100129	AI-GB 0,5 - 12 OG	0.5	20	•	•	•	
2100111	AI-GB 0,75 - 8 WH	0.75	18	•	•	•	
2100116	AI-GB 0,75 - 8 GY	0.75	18	•	•	•	
2100123	AI-GB 0,75 - 8 GY-25000	0.75	18	•	•	•	
2100113	AI-GB 0,75 - 10 WH	0.75	18	•	•	•	
2100117	AI-GB 0,75 - 10 GY	0.75	18	•	•	•	
2100119	AI-GB 0,75 - 10 GY-1000	0.75	18	•	•	•	
2100124	AI-GB 0,75 - 10 GY-25000	0.75	18	•	•	•	
2100107	AI-GB 0,75 - 10 BU	0.75	18	•	•	•	
2100104	AI-GB 0,75 - 12 GY	0.75	18	•	•	•	
2100108	AI-GB 0,75 - 12 BU	0.75	18	•	•	•	
2100112	AI-GB 0,75 - 12 WH	0.75	18	•	•	•	
2100085	AI-GB 1 - 8 YE	1	18	•	•	•	

* Only available in selected countries.

[illegible]

UL-certified combinations of ferrule and tool

Ferrules				Hand tools			
 The ferrules from Phoenix Contact are UL-certified in combination with selected crimping tools and automatic crimping devices. With this UL 486F (E 488001) certification, we meet both global and local market requirements in terms of quality, safety, and compatibility. The UL-certified combinations of ferrules and tools can be found in this overview.							
Item no.	Type	mm ²	AWG	CRIMPFOX 6 1212034	CRIMPFOX DUO 10 1031721	CRIMPFOX CENTRUS 6S 1213144/1202882 6H 1213146/1202883 10S 1213154 10H 1213156	CRIMPFOX 25R 1212039
2100091	AI-GB 1 - 8 RD	1	18	●	●	●	
2100095	AI-GB 1 - 8 RD-20000	1	18	●	●	●	
2100088	AI-GB 1 - 10 YE	1	18	●	●	●	
2100092	AI-GB 1 - 10 RD-1000	1	18	●	●	●	
2100097	AI-GB 1 - 10 RD-20000	1	18	●	●	●	
2100087	AI-GB 1 - 12 YE	1	18	●	●	●	
2100090	AI-GB 1 - 12 RD	1	18	●	●	●	
2100069	AI-GB 1,5 - 8 RD	1.5	16	●	●	●	
2100074	AI-GB 1,5 - 8 BK-1000	1.5	16	●	●	●	
2100077	AI-GB 1,5 - 8 BK-15000	1.5	16	●	●	●	
2100076	AI-GB 1,5 - 10 BK-1000	1.5	16	●	●	●	
2100079	AI-GB 1,5 - 10 BK-15000	1.5	16	●	●	●	
2100237	AI-GB 2,5 - 8 BU	2.5	14	●	●	●	
2100239	AI-GB 2,5 - 8 GY	2.5	14	●	●	●	
2100244	AI-GB 2,5 - 10 BU	2.5	14	●	●	●	
2100241	AI-GB 2,5 - 12 BU	2.5	14	●	●	●	
2100242	AI-GB 2,5 - 12 GY	2.5	14	●	●	●	
2100245	AI-GB 4 - 10 GY	4	12	●	●	●	
2100247	AI-GB 4 - 12 GY	4	12	●	●	●	
2100249	AI-GB 6 - 12 YE	6	10	●	●	●	
3201916	AI-XL 1,5 - 8 BK	1.5	16	●	●	●	
3201974	AI-XL 1,5 - 10 BK	1.5	16	●	●	●	
3201929	AI-XL 2,5 - 8 BU	2.5	14	●	●	●	
3201987	AI-XL 2,5 - 12 BU	2.5	14	●	●	●	
3201932	AI-XL 4 - 10 GY	4	12	●	●	●	
3201945	AI-XL 6 - 12 YE	6	10	●	●	●	
3201958	AI-XL 10 - 12 RD	10	8		●	●	●
3201961	AI-XL 16 - 12 BU	16	6				●
3200933	AI-TWIN 2X 0,5 - 8 WH	2 x 0.5	2 x 20	●	●	●	
2100015	AI-TWIN 2X 0,5 - 8 OG	2 x 0.5	2 x 20	●	●	●	
3200807	AI-TWIN 2X 0,75 - 8 GY	2 x 0.75	2 x 18	●	●	●	
2100011	AI-TWIN 2X 0,75 - 8 WH	2 x 0.75	2 x 18	●	●	●	
3240668	AI-TWIN 2X 0,75 - 8 BU	2 x 0.75	2 x 18	●	●	●	
3200975	AI-TWIN 2X 0,75 - 10 GY	2 x 0.75	2 x 18	●	●	●	
2100009	AI-TWIN 2X 0,75 - 10 BU	2 x 0.75	2 x 18	●	●	●	

* Only available in selected countries.

[illegible]

UL-certified combinations of ferrule and tool

Ferrules				Hand tools			
 The ferrules from Phoenix Contact are UL-certified in combination with selected crimping tools and automatic crimping devices. With this UL 486F (E 488001) certification, we meet both global and local market requirements in terms of quality, safety, and compatibility. The UL-certified combinations of ferrules and tools can be found in this overview.							
Item no.	Type	mm ²	AWG	CRIMPFOX 6 1212034	CRIMPFOX DUO 10 1031721	CRIMPFOX CENTRUS 6S 1213144/1202882 6H 1213146/1202883 10S 1213154 10H 1213156	CRIMPFOX 25R 1212039
2100010	AI-TWIN 2X 0,75 - 10 WH	2 x 0.75	2 x 18	●	●	●	
3200810	AI-TWIN 2X 1 - 8 RD	2 x 1	2 x 18	●	●	●	
2100008	AI-TWIN 2X 1 - 8 YE	2 x 1	2 x 18	●	●	●	
3200988	AI-TWIN 2X 1 - 10 RD	2 x 1	2 x 18	●	●	●	
3240679	AI-TWIN 2X 1 - 12 RD	2 x 1	2 x 18	●	●	●	
2100007	AI-TWIN 2X 1 - 12 YE	2 x 1	2 x 18	●	●	●	
3200823	AI-TWIN 2X 1,5 - 8 BK	2 x 1.5	2 x 16	●	●	●	
3200991	AI-TWIN 2X 1,5 - 12 BK	2 x 1.5	2 x 16	●	●	●	
2100005	AI-TWIN 2X 1,5 - 12 RD	2 x 1.5	2 x 16	●	●	●	
2100006	AI-TWIN 2X 1,5 - 8 RD	2 x 1.5	2 x 16	●	●	●	
3200836	AI-TWIN 2X 2,5 - 10 BU	2 x 2.5	2 x 14	●	●	●	
3240669	AI-TWIN 2X 2,5 - 10 GY	2 x 2.5	2 x 14	●	●	●	
3200878	AI-TWIN 2X 2,5 - 13 BU	2 x 2.5	2 x 14	●	●	●	
1213204	AI-TWIN 2X 4 - 12 OG	2 x 4	2 x 12	●	●	●	
3201000	AI-TWIN 2X 4 - 12 GY	2 x 4	2 x 12	●	●	●	
1213205	AI-TWIN 2X 6 - 14 GN	2 x 6	2 x 10				
1213206	AI-TWIN 2X 10 - 14 BN	2 x 10	2 x 8				
3201026	AI-TWIN 2X 10 - 14 RD	2 x 10	2 x 8				
1200104	AI 0,5 - 8 WH S1	0.5	20				
1200163	AI 0,75 - 8 BU S1	0.75	18				
1200105	AI 0,75 - 8 GY S1	0.75	18				
1200106	AI 1,0 - 8 RD S1	1	18				
1200107	AI 1,5 - 8 BK S1	1.5	16				
1200108	AI 2,5 - 8 BU S1	2.5	14				
1200164	AI 2,5 - 8 GY S1	2.5	14				
1212521	AI 0,5 - 8 WH-S	0.5	20				
1212784	AI 0,5 - 8 OG-S	0.5	20				
1212522	AI 0,75 - 8 GY-S	0.75	18				
1212783	AI 0,75 - 8 WH-S	0.75	18				
1212785	AI 0,75 - 8 BU-S	0.75	18				
1212523	AI 1,0 - 8 RD-S	1	18				
1212782	AI 1,0 - 8 YE-S	1	18				
1212524	AI 1,5 - 8 BK-S	1.5	16				
1212781	AI 1,5 - 8 RD-S	1.5	16				
3240250	AI 0,25 - 8 BU-B	0.25	24				

* Only available in selected countries.

			Automatic tools				
							
CRIMPFOX 50R 1212041	CRIMPFOX 16R TWIN 1212845	CRIMPFOX 4 IN 1 1200101	CF 500 230V 1208348* 120V 1208351*	CF 1000-1.5 1208199	CF 1000-10 1212456	CF 3000 230V 1205477* 120V 1205516*	CF CRIMPHANDY 0,5 1212463 0,75 1212464 1,0 1212465 1,5 1212466
			•				
			•				
			•				
			•				
			•				
			•				
			•				
			•				
			•				
			•				
			•				
			•				
			•				
			•				
	•		•				
	•		•				
	•		•				
		•					
		•					
		•					
		•					
		•					
							0.5 version
							0.5 version
							0.75 version
							0.75 version
							0.75 version
							1.0 version
							1.0 version
							1.5 version
							1.5 version
						•	

UL-certified combinations of ferrule and tool

Ferrules				Hand tools			
 The ferrules from Phoenix Contact are UL-certified in combination with selected crimping tools and automatic crimping devices. With this UL 486F (E 488001) certification, we meet both global and local market requirements in terms of quality, safety, and compatibility. The UL-certified combinations of ferrules and tools can be found in this overview.							
Item no.	Type	mm²	AWG	CRIMPFOX 6 1212034	CRIMPFOX DUO 10 1031721	CRIMPFOX CENTRUS 6S 1213144/1202882 6H 1213146/1202883 10S 1213154 10H 1213156	CRIMPFOX 25R 1212039
3240251	AI 0,25 - 8 YE-B	0.25	24				
3240249	AI 0,34 - 8 TQ-B	0.34	22				
3240663	AI 0,5 - 8 WH-B 3000	0.5	20				
3201563	AI 0,5 - 8 OG-B	0.5	20				
3201369	AI 0,5 - 8 WH-B	0.5	20				
3201547	AI 0,75 - 8 BU-B	0.75	18				
3201372	AI 0,75 - 8 GY-B	0.75	18				
3201576	AI 0,75 - 8 WH-B	0.75	18				
3240664	AI 0,75 - 8 GY-B 3000	0.75	18				
3240677	AI 0,75 - 8 WH-B 3000	0.75	18				
3201385	AI 1 - 8 RD-B	1	18				
3201589	AI 1 - 8 YE-B	1	18				
3240665	AI 1 - 8 RD-B 3000	1	18				
3240666	AI 1,5 - 8 BK-B 2500	1.5	16				
3201398	AI 1,5 - 8 BK-B	1.5	16				
3201592	AI 1,5 - 8 RD-B	1.5	16				
3201408	AI 2,5 - 8 BU-B	2.5	14				
3201550	AI 2,5 - 8 GY-B	2.5	14				
3240667	AI 2,5 - 8 BU-B 1500	2.5	14				

* Only available in selected countries.

			Automatic tools				
							
CRIMPFOX 50R 1212041	CRIMPFOX 16R TWIN 1212845	CRIMPFOX 4 IN 1 1200101	CF 500 230V 1208348* 120V 1208351*	CF 1000-1.5 1208199	CF 1000-10 1212456	CF 3000 230V 1205477* 120V 1205516*	CF CRIMPHANDY 0,5 1212463 0,75 1212464 1,0 1212465 1,5 1212466
						•	
						•	
		•				•	
		•				•	
		•				•	
		•				•	
		•				•	
		•				•	
		•				•	
		•				•	
		•				•	
		•				•	
		•				•	
		•				•	
		•				•	
		•				•	
		•				•	
		•				•	
		•				•	
		•				•	