

Ink Ribbons for Thermomark Printers

	FOR PRINTING:		RIBBON NEEDED:		
	MATERIAL	DETAILS	P/N	DESCRIPTION	COLOR
TM CARD PRINTER	US-TM	UniSheet terminal block marker	0801371	THERMOMARK-RIBBON 110-TC	BLACK
	US-WM	UniSheet wire marker	0801384	THERMOMARK-RIBBON 110/50-TC*	
	US-EM	UniSheet equipment marker			
	UCT-TM(F)...	Card marker for PxC terminal blocks	1014402	TM-RIBBON 110-TC/TR WH	WHITE
	UCT1,2,3-TM(F)...	Card marker for other manf. Terminal blocks			
	UCT-WMS	Card wire marker (slip on)			
TM ROLL and X1.2 PRINTERS	WMS...R, RL, RXL	Shrink Sleeves - endless or configured	0801358	THERMOMARK-RIBBON 110-WMSU	BLACK
	WMS...(E...)R, RL		0801359	THERMOMARK-RIBBON 110-WMSU WH	WHITE
	WMS...(E...)R, RL	Shrink Sleeves – endless	0801360	THERMOMARK-RIBBON 64-WMSU	BLACK
			5145737	THERMOMARK-RIBBON 64-WMSE BU	BLUE
			5145740	THERMOMARK-RIBBON 64-WMSE RD	RED
			0801361	THERMOMARK-RIBBON 64-WMSU WH	WHITE
			0803390	THERMOMARK-RIBBON 25-WMSU	BLACK
	TMT...R	Flexible Terminal block Markers	5145384	THERMOMARK-RIBBON 110	BLACK
	WMT...R	Wire marker inserts for PATG	0800687	THERMOMARK-RIBBON 110/50*	
	WMS...R	Shrink sleeves	0829544	THERMOMARK-RIBBON 110 BU	BLUE
	WML...R	Wire wraps	0829542	THERMOMARK-RIBBON 110 GN	GREEN
	EML...R	Adhesive labels	0829543	THERMOMARK-RIBBON 110 RD	RED
	EMLP...R	Raised adhesive labels			
	EMLC...R	Cloth adhesive labels			
	EMLS...R	Security adhesive labels			
	EMLHT...R	Adhesive labels for high temp applications	0800342	THERMOMARK-RIBBON 110-EMLHT	BLACK
	WMTB-HF...R	Halogen free cable markers used with wire tie	5148007	THERMOMARK-RIBBON 110-WMTB HF	BLACK

*All ribbons are 300 meters long unless denoted with /50 which indicates ribbon is 50 meters in length