


VAL-US シリーズ製品リスト

DINレール取付け式の UL Listed 認証済みサージ保護機器 (SPD)

IEC		電源/接地方式				SPD タイプ			型式	製品番号
3-phase		電圧	相数	IEC 呼称 *	UL 呼称 *	UL	IEC			
TN-S							T1/T2	T2		
TN-C		400/690V AC	3-phase	TN-S	Three Phase Wye	1		✓	VAL-US-347/30/3+1V-FM	1079099
		347/600V AC		TN-C				✓	VAL-US-347/30/3+0-FM	2910383
		277/480V AC	TN-S	Three Phase Wye	1		✓	VAL-US-277/40/3+1-FM	2910374	
240/415V AC	3-phase	TN-S	Three Phase Wye	1		✓	VAL-US-240/40/3+1-FM	2910367		
						✓	VAL-US-277/80/4+0-FM	2910380		
						✓	VAL-US-277/80/3+0-FM	1075896		
						✓	VAL-US-240/40/3+0-FM	2910366		
120/208V AC	3-phase	TN-S	Three Phase Wye	1	✓		VAL-US-120/65/3+1-FM	2910360		
						✓	VAL-US-120/40/3+1-FM	2910354		
					✓		VAL-US-120/65/3+0-FM	2910359		
						✓	VAL-US-120/40/3+0-FM	2910353		
240/480V AC	2-phase	TN-S	Single Split Phase	1		✓	VAL-US-240/40/2+1-FM	2910365		
		TN-C				✓	VAL-US-240/40/2+0-FM	2910364		
120/240V AC	2-phase	TN-S	Single Split Phase	1	✓		VAL-US-120/65/2+1-FM	2910358		
						✓	VAL-US-120/40/2+1-FM	2910352		
					✓		VAL-US-120/65/2+0-FM	2910357		
						✓	VAL-US-120/40/2+0-FM	2910351		
400V AC - 347V AC	1-phase	TN-C	Single Phase	1		✓	VAL-US-347/30/1+0-FM	2910381		
277V AC	1-phase	TN-S	Single Phase	1		✓	VAL-US-277/40/1+1-FM	2910373		
240V AC	1-phase	TN-S	Single Phase	1		✓	VAL-US-240/40/1+1-FM	2910362		
		TN-C				✓	VAL-US-277/80/1+0-FM	2910377		
120V AC	1-phase	TN-S	Single Phase	1	✓		VAL-US-120/65/1+1-FM	2910356		
						✓	VAL-US-120/40/1+1-FM	2910349		
(±)48V DC 60V DC	1-phase	TN-S	Single Phase	1	✓		VAL-US-48/65/1+1V-FM	2910346		
				4CA		✓	VAL-US-48/40/1+1V-FM	2910344		
		TN-C		1	✓		VAL-US-48/65/1+0-FM	2910345		
				4CA		✓	VAL-US-48/40/1+0-FM	2910343		

デルタ結線式					
電源/接地方式		UL/IEC SPDタイプ		型式	製品番号
電圧	UL 呼称 *	UL	IEC T2		
960V AC	Corner Grounded	1	✓	VAL-US-600D/30/2+0-FM	2910390
	High-Impedance and Ungrounded		✓	VAL-US-600D/30/3+0-FM	2910391
690V AC	Corner Grounded	1	✓	VAL-US-480D/30/2+0-FM	2910385
	High-Impedance and Ungrounded		✓	VAL-US-480D/30/3+0-FM	2910386
480V AC	High Leg Delta	1	✓	VAL-US-480HLD/30/3+1V-FM	2910387
240V AC	Corner Grounded	1	✓	VAL-US-240D/40/2+0-FM	2910369
	High-Impedance and Ungrounded		✓	VAL-US-240D/40/3+0-FM	2910370
	High Leg Delta		✓	VAL-US-240HLD/40/3+1-FM	2910371

* UL呼称、IEC呼称については左図をご参照願います。

* UL呼称、IEC呼称については左図をご参照願います。