



# Help for choosing the QUINT DC UPS

Select your combination of QUINT DC UPS and battery module.




| UPS-BAT/LI      |                         |  |
|-----------------|-------------------------|--|
|                 |                         |  |
| W x H x D in mm | 135 x 202 x 110         |  |
|                 | <b>128 Wh</b>           |  |
| Type            | UPS-BAT/LI/24DC/128WH   |  |
| Item no.        | <a href="#">1396415</a> |  |

| QUINT UPS                               |   |   |   | IQ Technology <sup>TM</sup><br>Designed by Phoenix Contact | ... with dual output                                    |
|---|---|---|---|--|---|
|   |   |   |   |  |   |
| W x H x D in mm                         | 35 x 130 x 132  | 35 x 130 x 132  | 40 x 130 x 132  | 47 x 130 x 125   | 35 x 130 x 125  |
|   | <b>24 V / 5 A</b>                                       | <b>24 V / 10 A</b>                                      | <b>24 V / 20 A</b>                                      | <b>24 V / 40 A</b>   | <b>12 V / 5 A / 24 V / 10 A</b>                         |
| Type                                    | QUINT4-UPS/24DC/24DC/5 ...                              | QUINT4-UPS/24DC/24DC/10 ...                             | QUINT4-UPS/24DC/24DC/20 ...                             | QUINT4-UPS/24DC/24DC/40 ...                                | QUINT-UPS/24DC/12DC/5/24DC/10                           |
| Recommended battery modules UPS/BAT/... | LI<br>VRLA-WTR PB<br>(1.2 Ah ... 40 Ah)<br>(max. 40 Ah) | LI<br>VRLA-WTR PB<br>(1.2 Ah ... 40 Ah)<br>(max. 80 Ah) | LI<br>VRLA-WTR PB<br>(4 Ah ... 110 Ah)<br>(max. 135 Ah) | LI<br>VRLA-WTR PB<br>(5 Ah ... 110 Ah)<br>(max. 135 Ah)    | LI<br>VRLA-WTR PB<br>(1.2 Ah ... 40 Ah)<br>(max. 60 Ah) |

| UPS-BAT/VRLA-WTR |                            |                            |
|------------------|----------------------------|----------------------------|
|                  |                            |                            |
| W x H x D in mm  | 172 x 177 x 178            | 358 x 174 x 169            |
|                  | <b>13 Ah</b>               | <b>26 Ah</b>               |
| Type             | UPS-BAT/VRLA-WTR/24DC/13AH | UPS-BAT/VRLA-WTR/24DC/26AH |
| Item no.         | <a href="#">2320416</a>    | <a href="#">2320429</a>    |

## Buffer times for QUINT DC UPS with lithium battery module

Example: 10 A can be buffered for a maximum of 25 minutes.




The data is based on an ambient temperature of +25°C at start of use.

## Buffer times for QUINT DC UPS with VRLA-WTR battery module

Select the battery module for your 24 V DC applications here.

Example: 20 A is to be buffered for 45 minutes.

- 
- QUINT4-UPS/24DC/24DC/20A and
- UPS-BAT/VRLA-WTR/24DC/26AH



The data is based on an ambient temperature of +25°C at start of use.