


2024 Summer Specials

Quarterly Special valid from July 1st – September 30th, 2024


Terminal blocks with Push-X technology *Maximum efficiency, minimum wiring time*

The Push-X technology is one of the most promising and forward-looking connection technologies available in the market from Phoenix Contact. The big advantage of this new technology is a pre-tensioned contact spring. Push-X technology enables direct conductor connection of flexible and rigid conductors with or without ferrules. The stripped conductor is inserted directly into the open connection point and the connection snaps into place with an audible click.



Your advantages

- ✓ Wiring of all conductor types, whether rigid or flexible, with or without ferrules
- ✓ Reduced assembly times due to factory-opened terminal compartment
- ✓ Clear identification of the conductor connection due to the positively driven pusher element and the acoustic click sound when the spring is released
- ✓ Feather-light plugging and superior handling comfort with a pretensioned contact spring
- ✓ Full compatibility with existing systems from CLIPLINE complete



 [Order a free sample](#)

All orders must reference promo code *****SUMMER2024*****. Quarterly Special valid from July 1st – September 30th, 2024. All prices are customer net each.

**Please note that ALL pricing is in CAD and this special is only available in Canada*


Electronic circuit breaker system CAPAROC

Make CAPAROC your system


CAPAROC is your individual modular system for overcurrent protection. With many combination options, intuitive operation, and strikingly simple design-in you will get your very personal standard in device protection. Using this system, you are perfectly positioned for the future.



Power Reliability



Order no.	Description	Details	Promo Price
1115661	CAPAROC PM S-R	Power Module status/reset	\$46.83
1344363	CAPAROC PM S-R EX	Power Module status/reset Hazloc	\$58.88
1115670	CAPAROC PM IOL	Power Module IO-Link	\$110.88
1110986	CAPAROC PM PN	Power Module Profinet	\$509.06
1393553	CAPAROC PM EIP	Power Module Ethernet IP	\$425.00
1157284	CAPAROC E1 12-24DC/10A	1 channel 10A	\$57.50
1115649	CAPAROC E1 12-24DC/1-10A	1 channel 1-10A	\$57.50
1115415	CAPAROC E1 12-24DC/1-4A	1 channel 1-4A	\$57.50
1157288	CAPAROC E1 12-24DC/1A	1 channel 1A	\$57.50
1157290	CAPAROC E1 12-24DC/2A	1 channel 2A	\$57.50
1157285	CAPAROC E1 12-24DC/4A	1 channel 4A	\$57.50
1157286	CAPAROC E1 12-24DC/6A	1 channel 6A	\$57.50
1157279	CAPAROC E1 12-24DC/8A	1 channel 8A	\$57.50
1344361	CAPAROC E2 12-24DC/1-4A EX	2 channel 1-4A EX	\$122.81
1115655	CAPAROC E2 12-24DC/1-4A	2 channel 1-4A	\$114.23
1110984	CAPAROC E2 12-24DC/2-10A	2 channel 2-10A	\$114.23
1344364	CAPAROC E2 12-24DC/2-10A EX	2 channel 2-10A EX	\$122.81
1115658	CAPAROC E4 12-24DC/1-10A	4 channel 1-10A	\$135.49
1115657	CAPAROC E4 12-24DC/1-4A	4 channel 1-4A	\$135.49
1110987	CAPAROC PD 0V	0V module 4 Channel	\$32.42
1110989	CAPAROC CR 20	20 slot Current rail	\$27.69
1115672	CAPAROC CR 8	8 slot Current rail	\$22.31
1115674	CAPAROC CR EXT20	Current rail extension 20 slot	\$27.69
1110991	CAPAROC CR EXT4	Current rail extension 4 slot	\$11.60
1110990	CAPAROC CR EXT8	Current rail extension 8 slot	\$22.31
1270955	CAPAROC CR CON	Replacement current rail metal	\$2.68



High-performance cellular router for industrial applications

Worldwide use

Industrial 4G LTE router, worldwide use, fallback to 3G (HSPA+) and 2G (EDGE), 2 Ethernet interfaces, firewall, NAT, IPsec and OpenVPN support, 2x SMA-F antenna socket, SMS and email transmission, 2 digital inputs, 1 digital output.

Your advantages

- ✓ Worldwide use
- ✓ Extended Temp range -40° to +70°C
- ✓ Approved for use in Hazardous locations Class 1 Div/Zone 2

Order no.	Description	Promo Price
1632697	TC ROUTER 3002T-4G GL	\$950.00

ⓘ Antennas not included



[Learn more online](#)

VL3 UPC

Ultra-compact box PCs

VL3 UPC is a series of ultra-compact box PCs with the latest (Elkhart Lake) CPU technology and innovative features that make it a perfect extension of the VL3 product family. With industry-leading connectivity capabilities in its class, the VL3 UPC represents excellent value for money.



Order no.
1459506

Your advantages

- ✓ A state-of-the-art hardware platform that can be tailored with scalability in performance, storage, and memory capacity
- ✓ With advanced Elkhart Lake processor technology, it delivers powerful system performance in a compact design
- ✓ Ideally suited for demanding edge computing installations in distributed control cabinets
- ✓ Practical connectivity capabilities enable simultaneous communication with numerous networks and peripheral devices

Main features

- Intel's long-term available sixth-generation Atom® processors (Elkhart Lake)
- Three fixed and one configurable item
- Flexible extension options such as WLAN, serial communication, Ethernet extension, and 4G/LTE modem
- Windows 11 capable

WLAN option: a, b, g, n

1x DP++ 1.4

2x USB 3.1

Easy access to micro SIM

2x Ethernet: 10 / 100 / 1000 Mbps (i226)

2x COM option: RS-232/422/485

24 V DC ±20%

4G / LTE modem



[Learn more online](#)

Switch and Protect

Relay with Integrated Circuit Breaker

PLC-INTERFACE offers the innovative combination of a relay interface and circuit breaker in an overall width of just 6.2 mm, for more space in the control cabinet. The nominal current and shutdown behavior can be configured individually via DIP switches on the device.

Features and benefits

- ✓ Configurable with DIP switch
- ✓ Circuit breaker with physical disconnection via relay
- ✓ Compatible with PLC-INTERFACE relay modules
- ✓ Easy function extension in existing systems
- ✓ Space-saving design with an overall width of 6.2 mm



Order no.	Description	Connection type	Promo Price
1328357	PLC-RSC- 24DC/1/CB1-6	Screw	\$49.00
1328360	PLC-RPT- 24DC/1/CB1-6	Push-in	\$49.00

THERMOMARK GO — Handheld Bluetooth printer

Professional marking on-site

The mobile THERMOMARK GO (1090747) label printer and the MARKING system app allow you to create labels for industrial identification directly on site. Simply design the markings on your smart device and send them to the printer.

Heat Shrink Labels	Order no.	Description	Colour	Length
	0803923	MM-WMS 3,2 (EX5)R C1 WH/BK	Black on White	1.8m / 5.9ft
	0803924	MM-WMS 4,8 (EX9)R C1 WH/BK	Black on White	1.8m / 5.9ft
	0803925	MM-WMS 6,4 (EX10)R C1 WH/BK	Black on White	1.8m / 5.9ft
	0803926	MM-WMS 9,5 (EX16)R C1 WH/BK	Black on White	1.8m / 5.9ft
Wrap Around Labels				
	0803931	MM-WML 3 (EX10)R C1 WH/BK	Black on White	6.5m / 21.3ft
	0803932	MM-WML 5 (EX10)R C1 WH/BK	Black on White	6.5m
Nylon Cloth Labels				
	0803934	MM-EMLC (EX12)R C1 WH/BK	Black on White	6m
	0803936	MM-EMLC (EX18)R C1 WH/BK	Black on White	6m
Flexible Vinyl Labels				
	0803938	MM-EMLF (EX12)R C1 WH/BK	Black on White	8m
	0803939	MM-EMLF (EX18)R C1 WH/BK	Black on White	8m
Polyester Device Labels				
	0803971	MM-EML (EX12)R C1 WH/BK	Black on White	8m
	0803972	MM-EML (EX18)R C1 WH/BK	Black on White	8m

A handheld Bluetooth printer with a black and white body and a small color screen at the top. It has a green indicator light and a label being printed.

WAS: \$550

NOW: **\$100***

Order no. 1090747

*THERMOMARK GO for \$100 with the purchase of 5 cartridges.

More cartridges and sizes available upon request.