




**COMPLETE
CABINET
CONFIDENCE**

BUILD WITH CONFIDENCE

Quick Reference Guide

Technical Support 1300 786 411

customerservice@phoenixcontact.com.au





Build with complete confidence

Phoenix Contact is a global market leader in industrial electronics and automation technologies with a comprehensive product and service offering that ensures the most functional, reliable, innovative, future proof, and cost-effective control cabinet solution.

Partnering with Phoenix Contact ensures an unparalleled offering, consisting of:

- ★ **Lifetime Warranty**
The industry's most comprehensive warranty program, guarantees you long-term reliability of your systems and applications.
- ★ **Price Guarantee**
The perfect combination of price and features.
- ★ **Availability Guarantee**
We help you build effective and efficient systems fast by providing you products right when you need them
- ★ **E-Platform**
Information at your fingertips enables automatic checking and direct ordering.
- ★ **Industry 4.0/IoT Readiness**
Be ready now and for the future with Phoenix Contact.

VALUE-ADDED SERVICES

- Fully assembled and marked terminal strips with accessories.
- Order complete assembly under a single article number.
- Simply install and connect.
- Reduce the effort of materials and stock management.
- Flexible supply chain management.

COMPLETE DIN-RAIL ASSEMBLY DESIGN

- Intuitive user interface for configuring terminal strips with intelligent functions such as auto correction, speed marking, or 3D visualisation of projects.
- Professional software for marking of labelling materials for terminal blocks, conductors, cables, devices, and systems.
- Perfect integration, thanks to optimised interfaces to all common CAE programs and spreadsheet formats.
- Equipped with an official template designer which allows users to create their own markings and adapt existing material descriptions.

COMPLETE PRODUCT PORTFOLIO

- Optimises control cabinet design and construction.
- Technologically leading products.
- Minimise logistics costs by reducing the variety of parts, thanks to standardised marking, bridging, and testing accessories.

FIVE FUNCTIONAL AREAS



Power Reliability

The heart of your installation, all control systems are dependent on being properly powered and protected. Surge and circuit protection, UPS backup, and redundant power solutions are the foundation on which reliable control systems should be built.



Connectivity, Switching and Conversion

Never take a good connection for granted, the connection of those wires, the switching and/or isolation of the signals are only as reliable as the quality of the terminations and electronics.



Automation, Networks and I/O

From single components to complete integrated systems, Phoenix Contact provides cost-effective, reliable solutions for industrial networking and automation.



Safety

Enact safety measures without limiting production flexibility of machines or production cells. Proper implementation means increased productivity, uptime, and profitability.



Shopfloor Productivity

Efficiently building a quality control cabinet starts with what you use to build it. A thoughtful selection of products to reduce cost and save time translates directly to the bottom-line profitability of any shop floor.

Table of Contents

Power Reliability

Power Supplies	6
Redundancy	8
Uninterruptible Power Supplies (UPS)	10
Surge Protection - Power	14
Circuit Breakers: Industrial and Device	16

Connectivity, Switching and Conversion

Modular Terminal Blocks	18
Distribution Blocks	20
Interposing Relays	21
Hybrid Motor Starters	23
CONTRACTRON Speed Starter	24
Signal Conditioners	25
Heavy-Duty Connectors	26
M12 Connectors	27
Cordsets	28
M8/M12 Distributor Boxes	29

Automation, Networks and I/O


Ethernet Switches	30
PoE and Installation Technologies	31
Industrial Wireless	33
Secure Remote Connectivity	34
Axioline F for the Control Cabinet	35
Control Cabinet Lights	37
HMI's	38

Functional Safety

Safety Relays	39
---------------	----

Shopfloor Productivity

Marking	42
Printing	43
Installation	44
Cable Duct and Din Rail	45



Power Supplies

AC Input to DC Output

Power supply					
AC Input to DC Output					
					
Do you need a single-phase or a three-phase power supply? What is the output DC voltage? What is your output current (Amps)? What functionality do you require? Have you considered surge protection with a Lifetime Warranty? Resulting Phoenix Contact part number					
Phase	Output Voltage	Output Current	Description	Connection Technology	Order #
1-Phase	5 V DC	3A	STEP3-PS/1AC/5DC/3/PT	Push-in	1170954
		5A	UNO-PS/1AC/ 5DC/ 25V	Screw	2904374
		5A	QUINT4-PS/1AC/5DC/5/PT	Push-in	2904595
		6.5A	STEP-PS/ 1AC/ 5DC/6.5	Screw	2868541
	12 V DC	1.3A	STEP3-PS/1AC/12DC/1.3/PT	Push-in	1170952
		2.5A	STEP3-PS/1AC/12DC/2.5/PT	Push-in	1170953
		2.5A	UNO-PS/1AC/12DC/ 30W	Screw	2902998
		2.5A	QUINT4-PS/1AC/12DC/2.5/PT	Push-in	2904605
		3A	STEP-PS/ 1AC/12DC/3	Screw	2868570
		5A	STEP-PS/ 1AC/12DC/5	Screw	2868583
		5A	TRIO-PS-2 G/1AC/12DC/5/C2LPS	Push-in	2903157
		7.5A	QUINT4-PS/1AC/12DC/7.5D/PT	Push-in	2904607
		8.3A	UNO-PS/1AC/12DC/100W	Screw	2902997
		10A	TRIO-PS-2G/1AC/12DC/10	Push-in	2903158
		15A	QUINT4-PS/1AC/12DC/15	Screw	2904608
		20A	QUINT-PS/1AC/12DC/20	Screw	2866721
	15 V DC	2.0A	UNO-PS/1AC/15DC/30V	Screw	2903000
		4.0A	STEP-PS/1AC/15DC/4	Screw	2868619
		0.63A	STEP3-PS/1AC/24DC/0.63/PT	Push-in	1088495
	24 V DC	1.25A	UNO-PS/1AC/24DC/ 30W	Screw	2902991
		1.3A	STEP3-PS/1AC/24DC/1.3/PT	Push-in	1088494
		1.3A	QUINT4-PS/1AC/24 DC/1.3/PT	Push-in	2909575
		1.3A	QUINT4-PS/1AC/24 DC/1.3/SC	Screw	2904597
		2.5A	STEP3-PS/1AC/24DC/2.5/PT	Push-in	1088491
		2.5A	UNO-PS/1AC/24DC/ 60W	Screw	2902992
		2.5A	TRIO-PS/1AC/24 DC/2.5	Push-in	2866268
		2.5A	QUINT4-PS/1AC/24DC/2.5/PT	Push-in	2909576
		2.5A	QUINT4-PS/1AC/24DC/2.5/SC	Screw	2904598
		3A	TRIO-PS-2G/1AC/24DC/3/C2LPS	Push-in	2903147
		3.8A	QUINT4-PS/1AC/24DC/3.8/PT	Push-in	2909577
		3.8A	QUINT4-PS/1 AC/24 DC/3.8/SC	Screw	2904599
		4A	STEP3-PS/1AC/24DC/4/PT	Push-in	1140066
		4.2A	UNO-PS/1AC/24DC/100W	Screw	2902993
		5A	STEP3-PS/1AC/24DC/5/PT	Push-in	1088478
		5A	ESSENTIAL-PS/1AC/24DC/120W/EE	Screw	2910586
		5A	TRIO-PS-2G/1AC/24DC/5	Push-in	2903148
		5A	QUINT4-PS/1AC/24DC/5	Screw	2904600
		10A	ESSENTIAL-PS/1AC/24DC/240W/EE	Screw	2910587
		10A	TRIO-PS-2G/1AC/24DC/10	Push-in	2903149
		10A	QUINT4-PS/1AC/24DC/10	Screw	2904601
		20A	ESSENTIAL-PS/1AC/24DC/480W/EE	Screw	2910588
		20A	TRIO-PS-2G/1AC/24DC/20	Push-in	2903151
		20A	QUINT4-PS/1AC/24DC/20	Screw	2904602
		40A	QUINT4-PS/1AC/24DC/40	Screw	2904603
	48 V DC	1.25A	UNO-PS/1AC/48DC/ 60W	Screw	2902995
		2.1A	UNO-PS/1AC/48DC/100W	Screw	2902996
		5A	UNO2-PS/1AC/48DC/240W	Screw	1110155
		5A	TRIO-PS-2G/1AC/48DC/5	Push-in	2903159
		5A	QUINT4-PS/1AC/48DC/5	Screw	2904610
		10A	TRIO-PS-2G/1AC/48DC/10	Push-in	2903160
		10A	QUINT4-PS/1AC/48DC/10	Screw	2904611
		20A	QUINT4-PS/1AC/48DC/20	Screw	2904612
	110 V DC	4A	QUINT4-PS/1AC/110DC/4	Screw	2904613
Phase	Output Voltage	Output Current	Description	Connection Technology	Order #
3-Phase	24 V DC	5A	TRIO-PS-2G/3AC/24DC/5	Push-in	2903153
		5A	QUINT4-PS/3AC/24DC/5	Screw	2904620
		10A	TRIO-PS-2G/3AC/24DC/10	Push-in	2903154
		10A	QUINT4-PS/3AC/24 DC/10	Screw	2904621
		20A	TRIO-PS-2G/3AC/24DC/20	Push-in	2903155
		20A	QUINT4-PS/3AC/24DC/20	Screw	2904622
		40A	TRIO-PS-2G/3AC/24DC/40	Push-in	2903156
		40A	QUINT4-PS/3AC/24DC/40	Screw	2904623
		20A	QUINT4-PS/3AC/48DC/20	Screw	2904627
	48 V DC	20A	QUINT4-PS/3AC/48DC/20	Screw	2904627



QUINT4 Power Supplies



TRIO Power Supplies



UNO Power Supplies



Essential Power Supplies



STEP Power Supplies




The Unbeatable Team!



Power Supplies - DC to DC Converters

DC Input to DC Output



Power supply

DC Input to DC Output

Do you need a single-phase or a three-phase power supply?					
What is the output DC voltage?					
What is your output current (Amps)?					
What functionality do you require?					
Have you considered surge protection with a Lifetime Warranty?					
Resulting Phoenix Contact part number					
Input Voltage	Output Voltage	Output Current	Description	Connection Technology	Order #
12-24 V DC	5 -15 V DC	2A	MINI-PS- 12- 24DC/ 5-15DC/2	Screw	2320018
		2.5A	QUINT4-PS/12-24DC/5-15DC/2.5/PT	Push-in	1066704
		8A	QUINT-PS/12DC/12DC/8	Screw	2905007
		8A	QUINT4-PS/24DC/12DC/8/PT	Push-in	2910122
12-24 V DC	24 V DC	1.3A	QUINT4-PS/12-24DC/24DC/1.3/PT	Push-in	1066716
		1.3A	QUINT4-PS/12-24DC/24DC/1.3/SC	Screw	1066703
		2.5A	QUINT4-PS/12-24DC/24DC/2.5/PT	Push-in	1066714
		2.5A	QUINT4-PS/12-24DC/24DC/2.5/SC	Screw	1066718
12 V DC	24 V DC	5A	QUINT4-PS/12DC/24DC/5/PT	Push-in	2910124
		5A	QUINT-PS/12DC/24DC/ 5	Screw	2320131
		5A	QUINT4-PS/24DC/24DC/5/PT	Push-in	2910119
		5A	QUINT4-PS/24DC/24DC/5/SC	Screw	1046800
24 V DC	24 V DC	10A	QUINT4-PS/24DC/24DC/10/PT	Push-in	2910120
		10A	QUINT4-PS/24DC/24DC/10/SC	Screw	2903158
		20A	QUINT4-PS/24DC/24DC/20/PT	Push-in	2910121
		20A	QUINT4-PS/24DC/24DC/20/SC	Screw	1046805
48-60 V DC	24 V DC	1.0A	MINI-PS- 48- 60DC/24DC/1	Screw	2866271
48-110 V DC	24 V DC	2.5A	QUINT4-PS/48-110DC/24DC/2.5/PT	Push-in	1066708
96-110 V DC	24 V DC	10A	QUINT-PS/96-110DC/24DC/10	Screw	2905010
48 V DC	24 V DC	5A	QUINT-PS/48DC/24DC/ 5	Screw	2320144
		5A	QUINT4-PS/48DC/24DC/5/PT	Push-in	2910125
12-24 V DC	48 V DC	0.7A	MINI-PS- 12- 24DC/48DC/0.7	Screw	2320021
24-48 V DC	48 V DC	2A	QUINT4-PS/24-48DC/48DC/2/PT	Push-in	1098676
24 V DC	48 V DC	5A	QUINT4-PS/24DC/48DC/5/PT	Push-in	2910123
			QUINT-PS/24DC/48DC/ 5	Screw	2320128
48 V DC	48 V DC	5A	QUINT4-PS/48DC/48DC/5/PT	Push-in	2910128
			QUINT-PS/48DC/48DC/5	Screw	2905008

DC to DC Converters for Photovoltaic Applications					
Input Voltage	Output voltage	Output Current	Description	Connection Technology	Order #
350 - 900 V DC	24 V DC	2.5A	MINI-PS- 12- 24DC/ 5-15DC/2	Screw	2906300
1500 V DC	24 V DC	1.5A	QUINT-PS/12DC/12DC/8	Push-in	1107892
1500 V DC	24 V DC	8A	QUINT4-PS/24DC/12DC/8/PT	Push-in	1075240

QUINT4 DC-DC Converters



Mini Power DC-DC Converters



DC-DC Converters for Photovoltaics



Recommended Surge Protection for LIFETIME WARRANTY

Recommended Surge Protection on Power Supply Input for Lifetime Warranty**						
Phase	Voltage	Max Surge Current (IMAX)	Load Current	Type Description	Connection Technology	Order #
1-phase	230 V AC	10 kA	26A	PLT-SEC-T3-230-FM-PT*	Push-in	2907928
	230 V AC	10 kA	26A	PLT-SEC-T3-230-FM-UT*	Screw	2907919
	230 V AC	40 kA	NA	VAL-MS 230/1+1	Screw	2804429
	230 V AC	40 kA	NA	VAL-MS 230/1+1-FM*	Screw	2804432
3-phase	230/400 V AC	40 kA	NA	VAL-MS 230/3+1-PT	Push-in	1248961
	230/400 V AC	40 kA	NA	VAL-MS 230/3+1 FM-PT*	Push-in	1248960
	230/400 V AC	40 kA	NA	VAL-MS 230/3+1	Screw	2838209
	230/400 V AC	40 kA	NA	VAL-MS 230/3+1-FM*	Screw	2838199

* FM - Remote relay alarm output. ** Go to www.phoenixcontact.com/en-au/au-lifetime-warranty for full details

The Unbeatable Team!



Recommended Surge Protection on Power Supply Input for Lifetime Warranty**						
Power Supply Input Voltage	Voltage	Max Surge Current (IMAX)	Load Current	Type Description	Connection Technology	Order #
48-110 V DC	120 V AC / DC	10 kA	26A	PLT-SEC-T3-120-FM-PT*	Push-in	2907927
	120 V AC / DC	10 kA	26A	PLT-SEC-T3-120-FM-UT*	Screw	2907918
48 V DC	60 V AC / DC	4 kA	26A	PLT-SEC-T3-60-FM-PT*	Push-in	2907926
	60 V AC / DC	4 kA	26A	PLT-SEC-T3-60-FM-UT*	Screw	2907917
12-24 V DC	24 V AC / DC	4 kA	26A	PLT-SEC-T3-24-FM-PT*	Push-in	2907925
	24 V AC / DC	4 kA	26A	PLT-SEC-T3-24-FM-UT*	Screw	2907916
	24 V DC	1 kA (In)	6A	TTC-6P-T3-24DC-PT-I	Push-in	1027586
	24 V DC	1 kA (In)	NA	TTC-6P-T3-24DC-UT-I	Screw	1027584

* FM - Remote relay alarm output. ** Go to www.phoenixcontact.com/en-au/au-lifetime-warranty for full details



Redundancy

For maximum operational safety. To prevent failures and downtime of complex applications, redundant power supply solutions are necessary. Two power supplies connected in parallel can be decoupled with either active or passive redundancy modules.



Monitored
Not Monitored

QUINT SINGLE-ORING active redundancy module (S-ORING)



Fully monitored single channel MOSFET technology redundancy.



Nominal Input-Output Voltage	Input Current	Output Current	Description	OVP Limit	Order #	
12-24 V DC	1 x 40A	1 x 40A	QUINT4-S-ORING/12-24DC/1X40	Standard	2907752	
12-24 V DC	1 x 40A	1 x 40A	QUINT4-S-ORING/12-24DC/1X40/VP	<30 V DC	1043418	
12-24 V DC	1 x 40A	1 x 40A	QUINT4-S-ORING/12-24DC/1X40/+	<28.8 V DC	2907753	

QUINT ORING active redundancy module with ACB Technology


Fully-monitored dual channel MOSFET technology with Auto Current Balancing - doubling the service life of your power supplies.



Nominal Input-Output Voltage	Input Current	Output Current	Description	Order #	
12-24 V DC	2 x 10A	2 x 10A (Redundancy) 1 x 20A (Increased Power)	QUINT4-ORING/12-24DC/2X10/2X10 NEW	1088206	
12-24 V DC	2 x 20A	2 x 20A (Redundancy) 1 x 40A (Increased Power)	QUINT4-ORING/12-24DC/2X20/2X20 NEW	1088207	
18-24 V DC	2 x 40A	2 x 40A (Redundancy) 1 x 80A (Increased Power)	QUINT-ORING/24DC/2X40/1X80	2902879	

Redundancy

Passive Redundancy modules: choose from QUINT, TRIO, UNO, or STEP POWER Diodes for easy decoupling. Rugged and reliable DIODE technology from 5 to 48V DC.



Nominal Input-Output Voltage	Input Current	Output Current	Description	Order #	
12-24 V DC	2 x 20A	2 x 20A (Redundancy) 1 x 40A (Increased Power)	QUINT4-DIODE/12-24DC/2X20/1X40	2907719	
48 V DC	2 x 20A	2 x 20A (Redundancy) 1 x 40A (Increased Power)	QUINT4-DIODE/48DC/2X20/1X40	2907720	
12-24 V DC	2 x 20A	2 x 20A (Redundancy) 1 x 40A (Increased Power)	TRIO2-DIODE/12-24DC/2X20/1X40	2907379	
12-24 V DC	2 x 10A	2 x 10A (Redundancy) 1 x 20A (Increased Power)	TRIO2-DIODE/12-24DC/2X10/1X20	2907380	
5-24 V DC	2 x 10A	2 x 10A (Redundancy) 1 x 20A (Increased Power)	UNO-DIODE/5-24DC/2X10/1X20	2905489	
5-24 V DC	2 x 5A	2 x 5A (Redundancy) 1 x 10A (Increased Power)	STEP-DIODE/5-24DC/2X5/1X10	2868606	

QUINT POWER Plus with inbuilt Active redundancy

Fully-monitored single channel MOSFET technology built into the QUINT4 Power Supply - as well as double over-voltage protection (OVP), protective coating and extreme temperature range.



Nominal Input-Output Voltage	Input Current	Output Current	Description	OVP Limit	Order #	
1 Phase / 230V AC	24 V DC	20A	QUINT4-PS/1AC/24DC/20/+	<30 V DC	2904617	
		10A	QUINT4-PS/1AC/24DC/10/+ NEW	<30 V DC	2904616	
24 V DC	24 V DC	20A	QUINT4-PS/24DC/24DC/20/SC/+	<30 V DC	1046881	


Uninterruptible Power Supplies (UPS)

DC power For critical applications, uninterruptible power supplies (UPS) can provide a lifeline to keep your system up and running.

+ UPS module

Selected based on output requirements

IQ Technology
Designed by PHOENIX CONTACT



DC QUINT Power Supply

Select UPS

What input /output voltage?

What output power/current?

Comms	Input/Output/Amps	Description	Order #
None	24DC/24DC/5A	QUINT4-UPS/24DC/24DC/5	2906990
None	24DC/24VDC/10A	QUINT4-UPS/24DC/24DC/10	2907066
None	24DC/24VDC/20A	QUINT4-UPS/24DC/24DC/20	2907071
None	24DC/24VDC/40A	QUINT4-UPS/24DC/24DC/40	2907077
USB	24DC/24DC/5A	QUINT4-UPS/24DC/24DC/5/USB	2906991
USB	24DC/24VDC/10A	QUINT4-UPS/24DC/24DC/10/USB	2907067
USB	24DC/24VDC/20A	QUINT4-UPS/24DC/24DC/20/USB	2907072
USB	24DC/24VDC/40A	QUINT4-UPS/24DC/24DC/40/USB	2907078
ETHERNET IP	24DC/24VDC/10A	QUINT4-UPS/24DC/24DC/5/EIP	2906994
ETHERNET IP	24DC/24DC/5A	QUINT4-UPS/24DC/24DC/10/EIP	2907069
ETHERNET IP	24DC/24VDC/20A	QUINT4-UPS/24DC/24DC/20/EIP	2907074
ETHERNET IP	24DC/24VDC/40A	QUINT4-UPS/24DC/24DC/40/EIP	2907080



Comms	Input/Output/Amps	Description	Order #
PROFINET	24DC/24DC/5A	QUINT4-UPS/24DC/24DC/5/PN	2906993
PROFINET	24DC/24VDC/10A	QUINT4-UPS/24DC/24DC/10/PN	2907068
PROFINET	24DC/24VDC/20A	QUINT4-UPS/24DC/24DC/20/PN	2907073
PROFINET	24DC/24VDC/40A	QUINT4-UPS/24DC/24DC/40/PN	2907079
ETHERCAT	24DC/24DC/5A	QUINT4-UPS/24DC/24DC/5/EC	2906996
ETHERCAT	24DC/24VDC/10A	QUINT4-UPS/24DC/24DC/10/EC	2907070
ETHERCAT	24DC/24VDC/20A	QUINT4-UPS/24DC/24DC/20/EC	2907076
ETHERCAT	24DC/24VDC/40A	QUINT4-UPS/24DC/24DC/40/EC	2907081

USB EtherNet/IP EtherCAT

QUINT4 - BATTERY CHARGER			Order #
	Input/Output/Amps	Description	2907990
	230 V AC IN / 24 V DC OUT / 10A	QUINT4-CHARGER/1AC/24DC/10	


UPS Energy Storage Selection Guides

UPS-BAT/PB						
W x H x D in mm	54 x 157 x 113	85 x 191 x 110	135 x 202 x 110	202 x 202 x 110	155 x 168 x 183	333 x 173 x 199
Capacity	1.2 Ah	4 Ah	7 Ah	12 Ah	20 Ah	40 Ah
Type	UPS-BAT/PB/24DC/1.2AH	UPS-BAT/PB/24DC/4AH	UPS-BAT/PB/24DC/7AH	UPS-BAT/PB/24DC/12AH	UPS-BAT/PB/24DC/20AH	UPS-BAT/PB/24DC/40AH
Order #	1274520	1274117	1274118	1274119	1348516	1354641

Buffer times for your QUINT DC UPS with the following PB energy storage devices:

Select your energy storage device for 24 V DC applications here. Example: 7 A is to be buffered for one hour.

QUINT4-UPS/24DC/24DC/10A and UPS-BAT/PB/24DC/12AH



1+1: Two energy storage devices of the same capacity are required in this case. The data is based on an ambient temperature of +20°C.

Uninterruptible Power Supplies (UPS)

	UPS-BAT/LI-ION		UPS-BAT/VRLA-WTR	
				
W x H x D in mm	135 x 202 x 110	264 x 224 x 197	172 x 177 x 178	358 x 174 x 169
Capacity	128 Wh	924 Wh	13 Ah	26 Ah
Type	UPS-BAT/LI/24DC/128WH	UPS-BAT/LI-ION/24DC/924WH	UPS-BAT/VRLA-WTR/24DC/13AH	UPS-BAT/VRLA-WTR/24DC/26AH
Order #	1396415	2908232	2320416	2320429

Buffer times for your QUINT DC UPS with the following energy storage devices: LI-ION and VRLA-WTR

Select your energy storage device for 24 V DC applications here. Example: 20 A is to be buffered for 6 minutes.



→ QUINT4-UPS/24DC/24DC/20A and UPS-BAT/LI-ION/24DC/128WH




Load Current	Buffer Time																																			
	Seconds														Minutes														Hours							
	10	15	30	1	2	3	5	6	7	8	9	10	20	30	40	45	50	1	2	3	5	8	10	15	20											
1 A																																				
2 A																																				
3 A																																				
5 A																																				
7 A																																				
10 A																																				
15 A																																				
20 A																																				
25 A																																				
30 A																																				
35 A																																				
40 A																																				

1+1: Two energy storage devices of the same capacity are required in this case. The data is based on an ambient temperature of +20°C.

DC UPS with Integrated Power Supply

	Power Supply AC-to-DC, DC-to-DC power supplies and UPS		+ UPS Module Selected based on output requirements
--	--	---	--



Phase	Output Voltage	Output Current	Description	Applicable Battery Size	Comms	Order #
1-Phase	24 V	5A	TRIO-UPS-2G/1AC/24DC/5	1.2 to 12 Ah	USB	2907160
		10A	TRIO-UPS-2G/1AC/24DC/10	1.2 to 38 Ah	USB	2907161
3-Phase		20A	TRIO-UPS-2G/3AC/24DC/20	4 to 38 Ah	USB	2906367

Buffer times for your TRIO DC UPS with the following PB energy storage devices:

Select your energy storage device for your TRIO DC UPS here. Example: 10 A is to be buffered for 10 minutes.



→ TRIO-UPS-2G/1AC/24DC/10 and UPS-BAT/PB/24DC/4AH




Load Current	Buffer Time																								
	Seconds			Minutes															Hours						
	10	15	30	1	2	3	5	6	7	8	9	10	20	30	40	45	50	1	2	3	5	8	10	15	20
1 A																									
2 A																									
3 A																									
5 A																									
7 A																									
10 A																									
15 A																									
20 A																									

The data is based on an ambient temperature of +20°C.

Uninterruptible Power Supplies (UPS)

AC Power - 1 kVA Capacity - ONLINE UPS

Note: Can be connected in parallel for 2kVA Capacity. (See manual for details)



For use with AC QUINT power supply

☐ Select UPS

☐ What input voltage?

☐ What output power/current?

QUINT UPS

QUINT IQ Technology

State of Charge: Describes current charging state and remaining runtime

State of Health: Provides information on the energy storage device life expectancy

Input Voltage	Output	Description	Order #
120 V AC/230 V AC	120 V AC/230 V AC - 1 kV A	QUINT4-UPS/1 AC/1 AC/1 kV A	2320283

+

☐ What type of energy-storage device: VRLA, CAP, or LI-ION?

How much current does the battery need to supply the system and for how long? See chart below.

Energy-storage type

VRLA



	UPS-BAT/PB				
W x H x D in mm	85 x 191 x 110	135 x 202 x 110	202 x 202 x 110	155 x 168 x 183	333 x 173 x 199
Capacity	4 Ah	7 Ah	12 Ah	20 Ah	40 Ah
Type	UPS-BAT/PB/ 24DC/4AH	UPS-BAT/PB/ 24DC/7AH	UPS-BAT/PB/ 24DC/12AH	UPS-BAT/PB/ 24DC/20AH	UPS-BAT/PB/ 24DC/40AH
Order #	1274117	1274118	1274119	1348516	1354641

Buffer times for your QUINT AC UPS/1KVA with the following PB energy storage devices:

Select your energy storage device for your QUINT AC UPS/1KVA (120 / 230 V application) here. Example: 400 W needs to be buffered for 50 minutes:

	Buffer Time																			
Performance	Minutes													Hours						
	2	3	4	5	8	10	15	20	25	30	40	50	1	1.5	2	3	4	6	9	10
100 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
200 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
300 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
400 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
500 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
600 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
700 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
800 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
900 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1



1+1
QUINT4-UPS/1AC/1AC/1KVA and
2 x UPS-BAT/PB/24DC/12AH

1+1: For the QUINT AC UPS/1KVA, two energy storage devices of the same capacity are always required. The data is based on an ambient temperature of +20°C.

	UPS-BAT/LI-ION		UPS-BAT/VRLA-WTR	
W x H x D in mm	135 x 202 x 110	264 x 224 x 197	172 x 177 x 178	358 x 174 x 169
Capacity	128 Wh	924 Wh	13 Ah	26 Ah
Type	UPS-BAT/LI-ION/ 24DC/128WH	UPS-BAT/LI-ION/ 24DC/924WH	UPS-BAT/VRLA-WTR/ 24DC/13AH	UPS-BAT/VRLA-WTR/ 24DC/26AH
Order #	2320351	2908232	2320416	2320429

Buffer times for your QUINT AC UPS/1KVA with the following energy storage devices: LI-ION and VRLA-WTR

Select your energy storage device for your QUINT AC UPS/1KVA (120 / 230 V application) here. Example: 400 W is to be buffered for three hours.

Performance	Buffer Time																			
	Minutes													Hours						
	2	3	4	5	8	10	15	20	25	30	40	50	1	1.5	2	3	4	6	9	10
100 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
200 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
300 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
400 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
500 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
600 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
700 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
800 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1
900 W	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1	1+1



1+1
QUINT4-UPS/1AC/1AC/1KVA and
2 x UPS-BAT/LI-ION/24DC/924WH

1+1: For the QUINT AC UPS/1KVA, two energy storage devices of the same capacity are always required. The data is based on an ambient temperature of +20°C.

Uninterruptible Power Supplies (UPS)

AC Power - 500 VA Capacity - OFFLINE UPS

For use with AC QUINT Power Supply

☐ Select UPS

☐ What input voltage?

☐ What output power/current?

QUINT UPS

QUINT IQ Technology

State of Charge: Describes current charging state and remaining runtime

State of Health: Provides information on the energy-storage device life expectancy

Input Voltage	Output	Description	Order #
120 V AC/230 V AC	120 V AC/230 V AC - 400 W/500 V A	QUINT4-UPS/1AC/1AC/500VA/USB	1067327

What type of energy storage-device: VRLA, CAP, or LI-ION?

How much current does the battery need to supply the system and for how long? See chart below.

Energy-Storage Type

VRLA



UPS Module



Energy Storage



UPS-BAT/PB					
W x H x D in mm	85 x 191 x 110	135 x 202 x 110	202 x 202 x 110	155 x 168 x 183	333 x 173 x 199
Capacity	4 Ah	7 Ah	12 Ah	20 Ah	40 Ah
Type	UPS-BAT/PB/ 24DC/4AH	UPS-BAT/PB/ 24DC/7AH	UPS-BAT/PB/ 24DC/12AH	UPS-BAT/PB/ 24DC/20AH	UPS-BAT/PB/ 24DC/40AH
Order #	1274117	1274118	1274119	1348516	1354641

Buffer times for your QUINT AC UPS/500VA with the following PB energy storage devices:

Select your energy storage device for your QUINT AC UPS/500VA (120 / 230 V application) here. Example: 125 is to be buffered for one hour.

Performance	Buffer Time																									
	Seconds							Minutes							Hours											
	0.2	0.4	2	8	15	20	40	1	2	3	5	10	20	30	40	45	50	1	2	3	5	8	10	15	20	
15 W																										1+1
35 W																										1+1
55 W																										
90 W																										
125 W																										
180 W																										
275 W																										



QUINT4-UPS/1AC/1AC/500VA/USB and UPS-BAT/VR-LA/24DC/20AH

1+1: Two energy storage devices of the same capacity are required in this case. The data is based on an ambient temperature of +20°C.

UPS-BAT/LI-ION			UPS-BAT/VRLA-WTR		
W x H x D in mm	135 x 202 x 110	264 x 224 x 197	172 x 177 x 178	358 x 174 x 169	
Capacity	128 Wh	924 Wh	13 Ah	26 Ah	
Type	UPS-BAT/LI-ION/ 24DC/128WH	UPS-BAT/LI-ION/ 24DC/924WH	UPS-BAT/VRLA-WTR/ 24DC/13AH	UPS-BAT/VRLA-WTR/ 24DC/26AH	
Order #	2320351	2908232	2320416	2320429	

Buffer times for your QUINT AC UPS/500VA with the following energy storage devices: LI-ION, and VRLA-WTR

Select your energy storage device for your QUINT AC UPS/ 500VA (120 / 230 V application) here. Example: 125 W is to be buffered for one hour.

Performance	Buffer Time																									
	Seconds								Minutes								Hours									
	0.2	0.4	2	8	15	20	40	1	2	3	5	10	20	30	40	45	50	1	2	3	5	8	10	15	20	
15 W																										1+1
35 W																										
55 W																										
90 W																										
125 W																										
180 W																										
275 W																										
400 W																										



QUINT4-UPS/1AC/1AC/500VA/USB and UPS-BAT/VR-LA-WTR/24DC/26AH

1+1: Two energy storage devices of the same capacity are required in this case. The data is based on an ambient temperature of +20°C.

Surge Protection - Power

FLT-SEC Series



NEW - VAL-MS PT



VAL-MS 100kA Series



PLT-SEC-T3 Series



Network Type			AS/NZS 1768 Category				Surge Protection Device		Relay Alarm Output	Order #	Availability Guarantee
		Voltage	C	B	A	+ FUSE	Description	Features			
3-Phase	N / E Separated TN-S / TT	230V / 400V	✓	✓			FLT-SEC-P-T1-3S-264/50-FM	limp = 50kA	✓	2909589	
			✓	✓		✓	FLT-SEC-H-T1-3C-264/25-FM	Inbuilt SPD Fuse	✓	2905871	
							(+ FLT-SEC-P-T1-N/PE-350/100-FM)	ADD N-E SPD Module	✓	2905472	
			✓	✓			FLT-SEC-P-T1-3S-350/25-FM	limp = 25kA / Imax = 100kA	✓	2905421	
			✓	✓			FLT-SEC-T1+T2-3S-350/25-FM	T1 and T2 Special SPD	✓	2905470	
			✓	✓			VAL-MS-3+1-100-320-A	Imax = 100kA	✓	1274064	
			✓	✓			VAL-ME-3+1-100-275-A	Imax = 100kA	✓	1106017	
			✓	✓	✓		VAL-MS-3+1-50-275-A	Imax = 50kA	✓	1105734	
			✓	✓	✓		VAL-SEC-T2-3S-350-FM	Imax = 40kA / Small Size	✓	2905340	★
			✓	✓	✓		VAL-MS 230/3+1 FM-PT	Imax = 40kA / Push-in	✓	1248960	★
3-Phase	N-E Combined (MEN) TN-C	230V / 400V	✓	✓			FLT-SEC-P-T1-3C-264/50-FM	limp = 50kA	✓	2907390	
			✓	✓		✓	FLT-SEC-H-T1-3C-264/25-FM	Inbuilt SPD Fuse	✓	2905871	
			✓	✓			FLT-SEC-P-T1-3C-350/25-FM	limp = 25kA / Imax = 100kA	✓	2905419	
			✓	✓			FLT-SEC-T1+T2-3C-350/25-FM	T1 and T2 Special SPD		2905469	
			✓	✓			VAL-MS-3-100-320-A	Imax = 100kA	✓	1274066	★
			✓	✓	✓		VAL-MS-3-50-275-A	Imax = 50kA	✓	1105739	★
			✓	✓	✓		VAL-SEC-T2-3C-350-FM	Imax = 40kA / Small Size	✓	2905339	
			✓	✓	✓		VAL-MS 320/3+0	Imax = 40kA / Low Price		2920230	
			✓	✓			FLT-SEC-P-T1-1S-264/50-FM	limp = 50kA	✓	2907388	
			✓	✓		✓	FLT-SEC-H-T1-1C-264/25-FM	Inbuilt SPD Fuse	✓	2801615	
1-Phase	N / E Separated TN-S / TT	230V					(+ FLT-SEC-P-T1-N/PE-350/100-FM)	ADD N-E SPD Module	✓	2905472	
			✓	✓			FLT-SEC-P-T1-1S-350/25-FM	limp = 25kA / Imax = 100kA		2905415	
			✓	✓			FLT-SEC-T1+T2-1S-350/25-FM	T1 and T2 Special SPD		2905466	
			✓	✓			VAL-MS-1+1-100-320-A	Imax = 100kA	✓	1274067	★
			✓	✓	✓		VAL-MS-1+1-50-275-A	Imax = 50kA		1105737	★
			✓	✓	✓		VAL-SEC-T2-1S-350-FM	Imax = 40kA / Small Size	✓	2905341	
			✓	✓	✓		VAL-MS 230/1+1	Imax = 40kA / Low Price		2804429	
				✓	✓		PLT-SEC-T3-230-FM-PT	Push-in Terminals	✓	2907928	★
				✓	✓		PLT-SEC-T3-230-FM-UT	Screw Terminals	✓	2907919	★
					✓		SFP 1-20/230AC	EMC Filter plus Surge Protection	✓	2859987	
1-Phase	N-E Combined (MEN) TN-C	230V	✓				FLT-SEC-P-T1-1C-264/50-FM	limp = 50kA	✓	2907387	
			✓	✓		✓	FLT-SEC-H-T1-1C-264/25-FM	Inbuilt SPD FUSE	✓	2801615	
			✓	✓			FLT-SEC-P-T1-1C-350/25-FM	Imax = 100kA	✓	2905414	
			✓	✓			FLT-SEC-T1+T2-1C-350/25-FM	Special T1 & T2	✓	2905465	
			✓	✓			VAL-MS-1-100-320-A	Imax = 100kA	✓	1274072	★
			✓	✓	✓		VAL-MS-1-50-275-A	Imax = 50kA	✓	1105740	★
			✓	✓	✓		VAL-MS 230	Imax = 40kA / Low Price	✓	2839127	
DC	24VDC +/-GND	24V DC			✓		PLT-SEC-T3-24-FM-PT	Push-in 26A	✓	2907925	★
					✓		PLT-SEC-T3-24-FM-UT	Screw-in 26A	✓	2907916	★
					✓		TTC-6P-T3-24DC-PT-I	Push-in 6A	OPT.	1027586	
					✓		TTC-6P-T3-24DC-UT-I	Screw-in 6A	OPT.	1027584	



ImpulseCheck - Surge Transient measurement and SPD remote monitoring device				
IPCH-4X-PCL-TCP-24DC-UT	Surge Measure and Record	✓	1045379	
Sensor - IPCH-SC-1.5	1.5M Sensor for ImpulseCheck		1045379	
Sensor - IPCH-SC-3.0	3.0M Sensor for ImpulseCheck		1069191	

Surge Protection: Measurement, Control, and Regulation (MCR)

Hint: Try our MCR configurator online - go to www.phoenixcontact.com.au and search #1389

What type of signal? Floating (e.g., Analogue 4-20mA / 0-10V), Common Ground (e.g., Digital), Antenna, or Data Do you require a Push-in, Screw, RJ45, or D-Sub (9 pin) connection? What is the Voltage or Frequency - Data Rate you require? What width do you require? Do you need a Direct or Floating (Indirect) Ground? Pluggable or Non-Pluggable SPD? Do you require SPD monitoring ? None, Local, or Remote (Single or Dual Stage)? Resulting Phoenix Contact part number										
Plugtrab (PT-IQ)										
Signal	Connection	Voltage	Type	Width (mm)	Ground	Design	Monitoring	Description	Order #	Plugtrab (PT-IQ)
MASTER (Mandatory)	Screw	20-30 VDC	MASTER	17.7mm	N/A	Pluggable	Remote 2 Stage	PT-IQ-PTB-UT	2800768	
	Push-in			17.7mm		Pluggable	Remote 2 Stage	PT-IQ-PTB-PT	2801296	
Floating (Analogue/ Loop, etc.)	Screw	12 VDC	2X2	17.7mm	Floating	Pluggable	Remote 2 Stage	PT-IQ-2X2+F-12DC-UT	2800985	
		24 VDC		17.7mm	Direct	Pluggable	Remote 2 Stage	PT-IQ-2X2-24DC-UT	2800980	
		24 VDC		17.7mm	Floating	Pluggable	Remote 2 Stage	PT-IQ-2X2+F-24DC-UT	2801264	
		48 VDC		17.7mm	Direct	Pluggable	Remote 2 Stage	PT-IQ-2X2-48DC-UT	2800986	
	Push-in	5 VDC	2X2	17.7mm	Floating	Pluggable	Remote 2 Stage	PT-IQ-2X2+F-5DC-PT	2801260	
		24 VDC		17.7mm	Direct	Pluggable	Remote 2 Stage	PT-IQ-2X2-24DC-PT	2801263	
		24 VDC		17.7mm	Floating	Pluggable	Remote 2 Stage	PT-IQ-2X2+F-24DC-PT	2801263	
		48 VDC		17.7mm	Floating	Pluggable	Remote 2 Stage	PT-IQ-2X2+F-48DC-PT	2801266	
Common Ground (Digital)	Screw	24 VDC	2X1	17.7mm	Direct	Pluggable	Remote 2 Stage	PT-IQ-2X1-24DC-UT	2800787	
		24 VDC	4X1	17.7mm	Direct	Pluggable	Remote 2 Stage	PT-IQ-4X1-24DC-UT	2800982	
		24 VDC		17.7mm	Floating	Pluggable	Remote 2 Stage	PT-IQ-4X1+F-24DC-UT	2800983	
		48 VDC		17.7mm	Direct	Pluggable	Remote 2 Stage	PT-IQ-4X1-48DC-UT	2801219	
	Push-in	24 VDC	2X1	17.7mm	Direct	Pluggable	Remote 2 Stage	PT-IQ-2X1-24DC-PT	2801247	
		24 VDC	4X1	17.7mm	Direct	Pluggable	Remote 2 Stage	PT-IQ-4X1-24DC-PT	2801271	
		24 VDC		17.7mm	Floating	Pluggable	Remote 2 Stage	PT-IQ-4X1+F-24DC-PT	2801272	
		48 VDC		17.7mm	Floating	Pluggable	Remote 2 Stage	PT-IQ-4X1+F-48DC-PT	2801274	
Data	Screw	5 VDC	5-HF	17.7mm	Direct	Pluggable	Remote 2 Stage	PT-IQ-5-HF-5DC-UT	2800797	
		12 VDC	5-HF	17.7mm	Floating	Pluggable	Remote 2 Stage	PT-IQ-5-HF+F-12DC-UT	2800801	
	Push-in	12 VDC	3-HF	17.7mm	Floating	Pluggable	Remote 2 Stage	PT-IQ-3-HF+F-12DC-PT	2801289	
		12 VDC	5-HF	17.7mm	Direct	Pluggable	Remote 2 Stage	PT-IQ-5-HF-12DC-PT	2801293	
		12 VDC		17.7mm	Floating	Pluggable	Remote 2 Stage	PT-IQ-5-HF+F-12DC-PT	2801295	
TERMITRAB Complete (TTC)										
Signal	Connection	Voltage	Type	Width	Ground	Design	Monitoring	Description	Order #	TERMITRAB Complete (TTC)
Optional Remote Signalling Set	Screw	10-36 VDC	FMRS	6.2mm x 2	Direct	NA	Remote Relay	TTC-6-FMRS-UT	2907811	
	Push-in			6.2mm x 2		NA	Remote Relay	TTC-6-FMRS-PT	2907811	
Floating (Analogue/ Loop, etc.)	Screw	12 VDC	1X2	6.2mm	Direct	Pluggable	Local (Flag)	TTC-6P-1X2-12DC-UT-I	2908192	
		24 VDC	1X2	6.2mm	Direct	Non-Pluggable	None	TTC-6-1X2-24DC-UT	2906798	
		24 VDC	1X2	6.2mm	Direct	Pluggable	Local (Flag)	TTC-6P-1X2-24DC-UT-I	2906809	
		24 VDC	1X2	6.2mm	Floating	Pluggable	Local (Flag)	TTC-6P-1X2-F-24DC-UT-I	1065317	
	Push-in	48 VDC	1X2	6.2mm	Direct	Pluggable	Local (Flag)	TTC-6P-1X2-48DC-UT-I	2908194	
		5 VDC	3	6.2mm	Direct	Pluggable	Local (Flag)	TTC-6P-3-5DC-PT-I	1061385	
		12 VDC	1X2	6.2mm	Direct	Pluggable	Local (Flag)	TTC-6P-1X2-12DC-PT-I	2908193	
		24 VDC	1X2	3mm	Direct	Non-Pluggable	None	TTC-3-1X2-24DC-PT	2907325	
		24 VDC	1X2	6.2mm	Floating	Pluggable	Local (Flag)	TTC-6P-1X2-F-24DC-PT-I	1065318	
		24VDC	2X2	6.2mm	Direct	Pluggable	Local (Flag)	TTC-6P-2X2-24-PT-I	1334595	
Common Ground (Digital)	Screw	48 VDC	1X2	6.2mm	Direct	Pluggable	Local (Flag)	TTC-6P-1X2-48DC-PT-I	2908195	
		12 VDC	2X1	6.2mm	Direct	Pluggable	Local (Flag)	TTC-6P-2X1-12DC-UT-I	2908201	
		24 VDC	2X1	6.2mm	Direct	Pluggable	Local (Flag)	TTC-6P-2X1-24DC-UT-I	2906810	
		24 VDC	2X1	6.2mm	Floating	Pluggable	Local (Flag)	TTC-6P-2X1-F-24DC-UT-I	1065319	
	Push-in	48 VDC	2X1	6.2mm	Floating	Pluggable	Local (Flag)	TTC-6P-2X1-F-48DC-UT-I	2908208	
		24 VDC	2X1	3mm	Direct	Non-Pluggable	None	TTC-3-2X1-24DC-PT	2907326	
		24 VDC	2X1	6.2mm	Floating	Pluggable	Local (Flag)	TTC-6P-2X1-F-M-24DC-PT-I	2906794	
		24 VDC	4X1	6.2mm	Direct	Pluggable	Local (Flag)	TTC-6P-4X1-24-PT-I	1334594	
Data (1 Mbps)	Screw	48 VDC	2X1	6.2mm	Direct	Pluggable	Local (Flag)	TTC-6P-2X1-48DC-PT-I	2908204	
		12 VDC	HF	6.2mm	Direct	Pluggable	Local (Flag)	TTC-6P-3-HF-M-12DC-UT-I	2906744	
	Push-in	12 VDC	HF	6.2mm	Floating	Pluggable	Local (Flag)	TTC-6P-3-HF-F-M-12DC-UT-I	2906786	
		12 VDC	HF	6.2mm	Floating	Pluggable	Local (Flag)	TTC-6P-3-HF-F-M-24DC-PT-I	2906756	
High Current	Screw	24 VDC	HC	6.2mm	Floating	Pluggable	Local (Flag)	TTC-6P-2-HC-M-24DC-UT-I	2906743	
		24 VDC	HC	6.2mm	Floating	Pluggable	Local (Flag)	TTC-6P-2-HC-M-24DC-PT-I	2906755	
Add-on Fuse Holder	Screw	60 VDC	6.3A max	6.2mm	N/A	5x20mm Fuse	N/A	TTC-6-FC-UT	1054762	
Coaxial Surge Protection (CN)										
Signal	Connection	Voltage	Frequency	Current	Ground	Design	Monitoring	Description	Order #	Coaxial (CN)
Coaxial	N-Connector Socket - Socket	70 VDC	6dB	10A	Direct	Non-replaceable	None	CN-UB-70DC-6-BB	2803166	
		280 VDC	3dB	5A	Direct	Replaceable GDT	None	CN-UB-280DC-3-BB	2801050	
		<55 Vp	380-470 MHz	5A	Direct	Non-replaceable	None	CN-LAMBDA/4-0.47-BB	2800021	
		<18 Vp	0.8-2.25 GHz	5A	Direct	Non-replaceable	None	CN-LAMBDA/4-2.25-BB	2801057	
		<11 Vp	2.4-7.6 GHz	5A	Direct	Non-replaceable	None	CN-LAMBDA/4-5.9-BB	2838490	
DATA / Communication Surge Protection (DT)										
Signal	Connection	Voltage	Current	Ground	Design	Monitoring	Description	Order #	Data (DT)	
CAT6+ / 10 Gbps	RJ45	<3.3 VDC / 60 VDC PoE++	1.5A	Direct	Non-replaceable	None	DT-LAN-CAT.6+	2881007		
CAT 5-6 / 1 Gbps	RJ45	<5 VDC / 57 VDC PoE+	1.5A	Direct	Non-replaceable	None	D-LAN-CAT.5-HC	2800763		
VDSL & Analogue / 50 Mbps	RJ45/12/11 & Screw	185 VDC / 130 VAC	380mA	Direct	Non-replaceable	None	DT-TELE-RJ45	2882925		
RS-485	D-SUB (9 Pin)	12 VDC	380mA	Direct	Non-replaceable	None	DT-UB-485/BS	2920612		
RS-485	Push-in	12 VDC	HF	600mA	Floating	Pluggable	Local (Flag)	TTC-6P-3-HF-F-M-24DC-PT-I		2906797
RS-485	Screw	12 VDC	HF	600mA	Floating	Non-Pluggable	Local (Flag)	TTC-6-3-HF-F-M-12DC-UT-I	2906769	

Circuit Breakers: Industrial and Device

Thermal-magnetic miniature circuit breakers (MCBs)

(For AC and DC industrial use only)

■ Do you require 7.5kA or 10kA SSC Rating?					
■ How many poles are required?					
■ What trip-curve characteristic is required?					
■ What current rating is required?					
■ Resulting Phoenix Contact part number					
TMC 7 Series: Thermal-Magnetic Industrial Miniature Circuit Breakers (MCB's)					
SSC	# of poles	Trip curve	Current rating	Type description	Order #
7.5kA	1	B	10A	TMC 71B 10A	1019916
			20A	TMC 71B 20A	1019921
			32A	TMC 71B 32A	1019924
		C	1A	TMC 71C 01A	1019972
			6A	TMC 71C 06A	1019977
			10A	TMC 71C 10A	1019980
			16A	TMC 71C 16A	1019984
			20A	TMC 71C 20A	1019985
			32A	TMC 71C 32A	1019988
			40A	TMC 71C 40A	1019989
			50A	TMC 71C 50A	1019990
			63A	TMC 71C 63A	1019992
		D	10A	TMC 71D 10A	1020045
			20A	TMC 71D 20A	1020052
			32A	TMC 71D 32A	1020055
	2	C	50A	TMC 71D 50A	1020057
			63A	TMC 71D 63A	1020059
			6A	TMC 72C 06A	1019999
		D	10A	TMC 72C 10A	1020002
			10A	TMC 73C 10A	1020023
			20A	TMC 73C 20A	1020028
		C	32A	TMC 73C 32A	1020031
			50A	TMC 73C 50A	1020033
			63A	TMC 73C 63A	1020036
			20A	TMC 73D 20A	1020097
			32A	TMC 73D 32A	1020100
			32A	TMC 73D 32A	1020100
10kA	1,2,3	B,C,D	1-63A	TMC 8XX XXA	Contact Sales

Full range of accessories available - BUSBARS, AUX CONTACT, ALARM CONTACT, SHUNT TRIPS, LOCK-OUTS etc.




Electronic Circuit Breakers (ECBs)

(For 24V DC device use)

Electronic Circuit Breakers Module (CBM)				
Channels	Amp	Function	Description	Order #
4	0.5-10A	Full feature/function model	CBM E4 24DC/0.5-10A NO-R	2905743
8	0.5-10A	Full feature/function model	CBM E8 24DC/0.5-10A NO-R	2905744
Electronic Circuit Breakers Module Compact (CBMC)				
Channels	Amp	Function	Description	Order #
4	1-4A	Remote reset version	CBMC E4 24DC/1-4A S-R*	1065727
4	1-10A	Remote reset version	CBMC E4 24DC/1-10A S-R	1065729
4	1-4A	Status output version	CBMC E4 24DC/1-4A NO*	2906031
4	1-10A	Status output version	CBMC E4 24DC/1-10A NO	2906032
4	1-4A	I/O link version	CBMC E4 24DC/1-4A+ IOL*	2910410
4	1-10A	I/O link version	CBMC E4 24DC/1-10A IOL	2910411
4	1-8A	Galvanically isolated version	CBMC EG4 24DC/1-8A NO	1065730

Single Channel Electronic Circuit Breakers (PTCB)					
Amp	Adjustable	Description	Order #	Status Output	Reset Input
1-4A	✓	PTCB E1 24DC/1-4A SI-R	1135753		
1-8A	✓	PTCB E1 24DC/1-8A SI-R	1135752	✓	✓
1A		PTCB E1 24DC/1A SI-R	1135751	✓	✓
2A		PTCB E1 24DC/2A SI-R	1135749	✓	✓
4A		PTCB E1 24DC/4A SI-R	1135745	✓	✓
6A		PTCB E1 24DC/6A SI-R	1135740	✓	✓
8A		PTCB E1 24DC/8A SI-R	1135734	✓	✓
1-3A	✓	PTCB E1 24DC/1-3A NO	2909909	✓	
1-4A	✓	PTCB E1 24DC/1-4A NO	2908261	✓	
1-8A	✓	PTCB E1 24DC/1-8A NO	2908262	✓	
1A		PTCB E1 24DC/1A NO	2909902	✓	
2A		PTCB E1 24DC/2A NO	2909903	✓	
3A		PTCB E1 24DC/3A NO	2909904	✓	
4A		PTCB E1 24DC/4A NO	2909906	✓	
6A		PTCB E1 24DC/6A NO	2909908	✓	
8A		PTCB E1 24DC/8A NO	2909910	✓	



CAPAROC: Modular Electronic Circuit Breaker System

(For 12V and 24V device use)



Power Modules



Current Rails and Extensions

Choose your required power module - Basic, IO-LINK, or Profinet Comms				
Select your length of current rails for the DIN mounting (based on 6.2mm = 1 slot wide)				
What circuit breaker modules do you require - 4 channel, 2 channel, or 1 channel?				
Do you want a 0V DC distribution module?				
Resulting Phoenix Contact part number				
CAPAROC Power Module (Mandatory Item)				
Comms	Voltage	Width	Description	Order #
Basic	12 - 24 VDC	2 slots	CAPAROC PM S-R	1115661
IO-LINK			CAPAROC PM IOL	1110986
Profinet		4 slots	CAPAROC PM PN	1110986

CAPAROC Current Rails (TOTAL CURRENT = 45A) (Mandatory Item)						
Size	Voltage	Width		Type	Description	Order #
CR8	12 - 24 VDC	8 Slots	49.6mm	Standard	CAPAROC CR 8	1115672
CR20		20 Slots	124mm	Standard	CAPAROC CR 20	1110989
CR4-EXT		4 Slots	24.8mm	Extension	CAPAROC CR EXT4	1110991
CR8-EXT		8 Slots	49.6mm	Extension	CAPAROC CR EXT8	1110990
CR20-EXT		20 Slots	124mm	Extension	CAPAROC CR EXT20	1115674
CR-CON		N/A	N/A	Connector	CAPAROC CR CON	1270955

CAPAROC Electronic Circuit Breaker Modules					
Channels	Current Rating	Voltage	Width	Description	Order #
4	1-10A	12 - 24 VDC	2 Slots	CAPAROC E4 12-24DC/1-10A	1115658
4	1-4A		2 Slots	CAPAROC E4 12-24DC/1-4A	1115657
2	2-10A		2 Slots	CAPAROC E2 12-24DC/2-10A	1110984
2	1-4A		2 Slots	CAPAROC E2 12-24DC/1-4A	1115655
1	1-10A		1 Slot	CAPAROC E1 12-24DC/1-10A	1115649
1	1-4A		1 Slot	CAPAROC E1 12-24DC/1-4A	1115415
1	10A		1 Slot	CAPAROC E1 12-24DC/10A	1157284
1	8A		1 Slot	CAPAROC E1 12-24DC/8A	1157279
1	6A		1 Slot	CAPAROC E1 12-24DC/6A	1157286
1	4A		1 Slot	CAPAROC E1 12-24DC/4A	1157285
1	2A		1 Slot	CAPAROC E1 12-24DC/2A	1157290
1	1A		1 Slot	CAPAROC E1 12-24DC/1A	1157288

CAPAROC 0 VDC Distribution Module				
Module	Voltage	Width	Description	Order #
Distribution	12 - 24 VDC	1 Slot	CAPAROC PD 0V	1110987



4 Channel

2 Channel



PD 0V

1 Channel

Modular Terminal Blocks

CLIPLINE complete: all connection methods – one system

Complete flexibility: terminal blocks with different connection technologies can be freely combined

Cost savings, thanks to uniform bridging, marking, and test accessories



■ What connection style best fits your application?	■ Will you be bridging terminals?
■ What wire size are you using? What is your current (Amps) requirement?	■ Resulting Phoenix Contact part number
■ How many connection points?	■ What accessories are needed?
■ How many end covers are needed?	

Push-in (PT)


mm²	I _{max}	Connections	Description	Order #	Cover	Bridge (2-Position)	Marking			
							Thermomark Card/ Prime		Bluemark ID	
1.5	15	2	PT 1.5/S	3208100	3208142	3213014 FBS 2-3,5	Side	Top	Side	Top
	-		PT 1.5/S PE	3208139			0829486 UCT-TMF 3,5	0829484 UCT-TM 3,5	0829486 UCT-TMF 3,5	0829484 UCT-TM 3,5
	15	3	PT 1.5/S-TWIN	3208155						
	15	4	PT 1.5/S-QUATTRO	3208197						
2.5	20	2	PT 2.5	3209510	3030417	3030161 FBS 2-5	0828744 UCT-TMF 5	0828734 UCT-TM 5	0818108 UCT-TMF 5	0818108 UCT-TM 5
	-		PT 2.5-PE	3209536						
	20	3	PT 2.5-TWIN	3209549						
	20	4	PT 2.5-QUATTRO	3209578						
	20		PTTB 2.5	3210567						
	-		PTTB 2.5-PE	3210596						
4	30	2	PT 4	3211757	3030420	3030336 FBS 2-6	0828746 UCT-TMF 6	0828736 UCT-TM 6	0828740 UCT-TMF 6	0818085 UCT-TM 6
	-		PT 4-PE	3211766						
	6.3		PT 4-HESI (5X20 FUSE)	3211861						
	6.3		PT 4-HESILED 24 (5X20 FUSE)	3211903						
	30	3	PT 4-TWIN	3211771						
	30	4	PT 4-QUATTRO	3211797						
	28		PTTB 4	3211786						
	-		PTTB 4-PE	3211854						




- Simple push-in spring ideal for solid and ferruled wires
- Tool-free termination
- 50 percent lower insertion force
- Orange pushbutton permits easy conductor release using any type of tool, without direct contact with live parts
- Uniformed Push-in Technology available on thousands of Phoenix Contact parts

Push-In Vertical (PTV)

mm²	I_Nom	Connections	Description	Order #	End Cover	Bridge (2-Position)	Marking			
							Thermomark Card/ Prime	Bluemark ID		
2.5	24A	2	PTV 2,5	1078960	1088746	3030161 FBS 2-5	0828734 UCT-TM 5	0818108 UC-TM 5		
	-		PTV 2,5 BU	1078962						
	-		PTV 2,5-PE	1078963						
	20A	2	PTVC 2,5-MT	1079059	1079914	N/A				
	-		PTVC 2,5-TG	1079061						
	-									
	24A	3	PTV 2,5-TWIN	1078966	1088747	3030161 FBS 2-5				
	-		PTV 2,5-TWIN BU	1078971						
	-		PTV 2,5-TWIN-PE	1078991						
	24A	4	PTV 2,5-QUATTRO	1078999	1088748				3030161 FBS 2-5	
	-		PTV 2,5-QUATTRO BU	1079006						
	-		PTV 2,5-QUATTRO-PE	1079012						
20A	PTV 2,5-QUATTRO-TG		1079072							
-			-	-						
-			-	-						
4	32A	2	PTV 4	1088728	1088746		3030336 FBS 2-6	0828736 UCT-TM 6		0818085 UC-TM 6
	-		PTV 4 BU	1088729						
	-		PTV 4-PE	1088730						
	20A		PTV 4-MT	1088739						
	-		PTV 4-TG	1088741						
	-									
	6.3A	2	PTV 4-HESI (5x20)	1088742	1079918					
	-		PTV 4-HESILED 24 (5X20)	1088743						
	-		PTV 4-HESILA 250 (5x20)	1088745						
	-			-	-					
	32A	3	PTV 4-TWIN	1088731	1088747					
	-		PTV 4-TWIN BU	1088732						
	-		PTV 4-TWIN-PE	1088733						
	32A	4	PTV 4-QUATTRO	1088734	1088748					
-	PTV 4-QUATTRO BU		1088735							
-	PTV 4-QUATTRO-PE		1088736							



- Easy and tool-free wiring of conductors with ferrules or solid conductors
- Compact design and front connection enable wiring in a confined space



Double Level Terminal Block

2.5	22A	4	PTTBV 2,5	1079073	1083611	3030161 FBS 2-5	0828734 UCT-TM 5	0818108 UCT-TM 5
	20A		PTTBV 2,5/U-OG/O-GN	1088773				
	22A		PTTBV 2,5 BU	1079074				
	-		PTTBV 2,5-PE	1079076				
4	28A	4	PTTBV 4	1088737	1083611	3030336 FBS 2-6	0828736 UCT-TM 6	0818085 UCT-TM 6
	-		PTTBV 4 BU	1088738				
	-		PTTBV 4-PE	1088774				




Modular Terminal Blocks

■ What connection style best fits your application?	■ Will you be bridging terminals?
■ What wire size are you using? What is your current (Amps) requirement?	■ Resulting Phoenix Contact part number
■ How many connection points?	■ What accessories are needed?
■ How many end covers are needed?	

PT Power High-Current									
mm²	I (nom)	Connections	Description	Order #	End Cover	Bridge (2-Position)	Marking		
							Thermomark Card/Prime	Bluemark ID	
35	125A	2	PTPOWER 35	3212064	N/A	3005963 FBS 2-16	0829142 UCT-TM 10	0818069 UC-TM 10	 • More easily identifiable connection and conductor marking thanks to lateral conductor routing • Time-saving conductor connection with tool-free push-in direct connection technology
	-		PTPOWER 35-BU	3212065					
	125A	6	PTPOWER 35-PE	3212066					
		8	PTPOWER 35-3L/N	3212068					
50	150A	2	PTPOWER 50	3260050		3260067 EB 2-20/PT			
	-		PTPOWER 50-BU	3260051					
	150A	6	PTPOWER 50-PE	3260052					
		8	PTPOWER 50-3L/N	3260053					
95	232A	2	PTPOWER 95	3260054		3260157 EB 2-25/PT			
	-		PTPOWER 95-BU	3260103					
	232A	6	PTPOWER 95-PE	3260106					
		8	PTPOWER 95-3L/N	3260109					
185	309A	2	PTPOWER 95-3L/N	3260112		3215057 EB 2-31/PT			
	-		PTPOWER 185	1054722					
	309A	6	PTPOWER 185-BU	1054723					
		8	PTPOWER 185-3L	1054728					
			PTPOWER 185-3L/N	1054729					

Screw Clamp (UT)										
2.5	20	2	UT 2.5	3044076	3047028	3030161 FBS 2-5	0828734 UCT-TM 5	0818108 UC-TM 5	 • Universal multi-wire connection with highest pullout force • Save money with uniform bridging, marking, and accessories as part of the Clipline Complete system • Maintenance-free conductor connection with the Reakdyn® principle – there is no need to tighten the terminal block screws	
	-		UT 2.5-PE	3044092						
	20	3	UT 2.5-TWIN	3044513						3047141
	20		UT 2.5-QUATTRO	3044542						3047170
	20	4	UTTB 2.5	3044636						3047293
	-		UTTB 2.5-PE	3044665						3047293
	20	6	UT 2.5-3L	3214259						3214314
	-		UT 2.5-3PE	3214275						
4	30	2	UT 4	3044102	3047028	3030336 FBS 2-6	0828736 UCT-TM 6	0818085 UC-TM 6		
	-		UT 4-PE	3044128						
	6.3		UT 4-HESI (5X20 FUSE)	3046032						-
	6.3		UT 4-HESILED 24 (5X20 FUSE)	3046090						-
	30	3	UT 4-TWIN	3044364						3047141
	30		UT 4-QUATTRO	3044571						3047170
	30	4	UTTB 4	3044814						3047293
	-		UTTB 4-PE	3044759						
6	50	2	UT 6	3044131	3047028	3030284 FBS 2-8	0828740 UCT-TM 8	0818072 UC-TM 8		
	-		UT6-PE	3044157						

Bolt Connection (RT)									
mm²	I (nom)	Connections	Description	Order #	End Cover	Bridge (2-Position)	Thermomark Card/Prime	Bluemark ID	
2.5	24	2	RT-3	3049013	3049097	3030336 FBS 2-6	0828740 UCT-TM 8	0818072 UC-TM 8	 • Captive hardware with a hinged cover delivers a safe termination • Save money with uniform bridging, marking, and accessories
6	41	2	RT-5	3049026		3030284 FBS 2-8	0829144 UCT-TM 12	0819194 UC-TM 12	
35	125	2	RT-8	3049042	3049194	3005947 FBS 2-10	0829146 UCT-TM 16	0819217 UC-TM 16	

CLIPLINE Complete: All Connection Methods – One System

Disconnect zone:

- Standardised disconnect zones
- Accommodates connectors, such as fuse plugs, component connectors, and isolating plugs




Test plugs:

- Reliable contacting of the test plugs with a 4 mm diameter
- Modular pluggable test points




Fuse plugs:

- Pluggable 5x20 mm cartridge glass fuses
- Plugs available with LED indication
- Common markers between terminals and fuses



Plug-in bridging:

- Tool-free installation
- 2-50 position bridges
- Different colour options available
- Common between termination types
- Removable teeth for skip-bridging



Plug-in zone:

- Time-saving and modular configuration
- Standardized plug-in zone





Distribution Blocks

■ What connection style best fits your application?	■ What colour is needed?
■ What wire size are you using? What is your current (Amps) requirement?	■ Resulting Phoenix Contact part number
■ How many connection points?	

Push-in (PTFIX 4/18)					
mm²	I (max)	Connections	Colour	Description	Order #
4	41	19	Grey	PTFIX 4/18X1,5-NS35 GY	1047454
			Blue	PTFIX 4/18X1,5-NS35 BU	1047455
			Red	PTFIX 4/18X1,5-NS35 RD	1047456
			Brown	PTFIX 4/18X1,5-NS35 BN	1047457
			Green	PTFIX 4/18X1,5-NS35 GN	1047458
			Yellow	PTFIX 4/18X1,5-NS35 YE	1047459
			Black	PTFIX 4/18X1,5-NS35 BK	1047460
			White	PTFIX 4/18X1,5-NS35 WH	1047461
			Violet	PTFIX 4/18X1,5-NS35 VT	1047462
			Orange	PTFIX 4/18X1,5-NS35 OG	1047463
			Pink	PTFIX 4/18X1,5-NS35 PK	1047464
			Black/Yellow	PTFIX 4/18X1,5-NS35-FE	1047465
Push-in (PTFIX 6/18)					
6	57	19	Grey	PTFIX 6/18X2,5-NS35 GY	3273110
			Blue	PTFIX 6/18X2,5-NS35 BU	3273112
			Red	PTFIX 6/18X2,5-NS35 RD	3273114
			Brown	PTFIX 6/18X2,5-NS35 BN	3273120
			Green	PTFIX 6/18X2,5-NS35 GN	3273118
			Yellow	PTFIX 6/18X2,5-NS35 YE	3273116
			Black	PTFIX 6/18X2,5-NS35 BK	3273124
			White	PTFIX 6/18X2,5-NS35 WH	3273122
			Violet	PTFIX 6/18X2,5-NS35 VT	3273126
			Orange	PTFIX 6/18X2,5-NS35 OG	3273128
			Pink	PTFIX 6/18X2,5-NS35 PK	3273127
			Black/Yellow	PTFIX 6/18X2,5-NS35-FE	3273130
Push-in (PTFIX 10/18)					
10	63	19	Grey	PTFIX 10/18X4-NS35 GY	3273636
			Blue	PTFIX 10/18X4-NS35 BU	3273638
			Red	PTFIX 10/18X4-NS35 RD	3273640
			Brown	PTFIX 10/18X4-NS35 BN	3273646
			Green	PTFIX 10/18X4-NS35 GN	3273644
			Yellow	PTFIX 10/18X4-NS35 YE	3273642
			Black	PTFIX 10/18X4-NS35 BK	3273650
			White	PTFIX 10/18X4-NS35 WH	3273648
			Violet	PTFIX 10/18X4-NS35 VT	3273652
			Orange	PTFIX 10/18X4-NS35 OG	3273654
			Pink	PTFIX 10/18X4-NS35 PK	3273653
			Black/Yellow	PTFIX 10/18X4-NS35-FE	3273656

- ✓

Ready-to-use blocks for fast assembly without manual bridging, offering time savings of up to 80%
- ✓

Flexible setup in your application, thanks to various mounting options: DIN rail mounting, direct mounting, or adhesive mounting
- ✓

Space savings of up to 50% on the DIN rail, thanks to transverse mounting
- ✓


Colour-coded assignment of conductors and terminal points for intuitive and safe installation with eleven colours
- ✓

Time-saving pre-treated and rigid conductor connection, thanks to tool-free push-in direct connection technology
- ✓

Alignment without any loss of pitch and flexible potential extension using standard plug-in bridges



Eleven colour options available



Time saving push-in technology



Easy to bridge

Interposing Relays

■ What application or load are you switching: electromechanical or solid state?	■ What connection technology: screw terminal (UT) or push-in (PT)?
■ What is the input-coil voltage: DC or AC?	■ Which kind of specialty relays: hazardous location, sensor/actuator, filter base?
■ What is your output current (Amps)? (Ratings are for resistive loads)	■ Resulting Phoenix Contact part number
■ How many sets of contacts do you need: SPDT, DPDT, etc.?	■ What accessories are needed?

Electromechanical Relays

Input-Coil Voltage	Output Current	Sets of Contacts	Termination Style	Description	Order #	
12 V DC	6 A	SPDT - 6.2 mm	Screw	PLC-RSC-12 DC/21	2966906	PLC relay assembly with electromechanical relay
		DPDT - 14 mm	Push-in	PLC-RPT-12 DC/21	2900316	
24 V DC	50 mA	SPDT - 6.2 mm	Screw	PLC-RSC-24 DC/21AU	2966265	
			Push-in	PLC-RPT-24 DC/21AU	2900306	
		DPDT - 14 mm	Screw	PLC-RSC-24 DC/21-21	2967060	
			Push-in	PLC-RPT-24 DC/21-21	2900329	
	6 A	SPDT - 6.2 mm	Screw	PLC-RSC-24DC/ 1AU/SEN	2966317	
			Push-in	PLC-RPT-24 DC/21	2900299	
		DPDT - 14 mm	Screw	PLC-RSC-24 DC/21-21	2967060	
			Push-in	PLC-RPT-24 DC/21-21	2900330	
		SPDT 6.2 mm	Screw	PLC-RSC- 24DC/ 1/ACT	2966210	
			Screw	PLC-RSC- 24DC/ 1AU/SEN	2966317	
24 V AC or DC	6 A	SPDT - 14 mm	Screw	PLC-RSC-24 DC/21HC	2967620	
			Push-in	PLC-RPT-24 DC/21HC	2900291	
		DPDT - 6.2 mm	Screw	PLC-RSC-24UC/21	2966184	
			Push-in	PLC-RPT-24UC/21	2900300	
230 V AC	6 A	SPDT - 6.2 mm	Screw	PLC-RSC-24UC/21-21	2967073	
			Push-in	PLC-RPT-24UC/21-21	2900332	
		SPDT - 6.2 mm	Screw	PLC-RSC-230UC/21	2966207	
			Push-in	PLC-RPT-230UC/21	2900305	
230 V AC	6 A	DPDT - 14 mm	Screw	PLC-RSC-230UC/21-21	2967099	
			Screw	PLC-RSC-230UC/21-21	2967099	



Solid State Relays

Input-Coil Voltage	Output Current	Sets of Contacts	Termination Style	Description	Order #	
5 V DC	3 A	NO ONLY - 6.2 mm	Screw	PLC-OSC-5 DC/24 DC/2/ACT	2980144	PLC Relay Assembly with Solid State Relay
			Push-in	PLC-OPT-5 DC/24 DC/2/ACT	2900375	
24 V DC	100 mA	NO ONLY - 6.2 mm	Screw	PLC-OSC-24 DC/ 48 DC/100	2966728	
			Push-in	PLC-OPT-24 DC/ 48 DC/100	2900352	
	3 A	NO ONLY - 6.2 mm	Screw	PLC-OSC-24 DC/ 24 DC/2	2966634	
			Push-in	PLC-OPT-24 DC/24 DC/2	2900364	
120 V AC or DC	3 A	NO ONLY - 6.2 mm	Screw	PLC-OSC-120UC/24 DC/2	2966650	
			Push-in	PLC-OPT-120UC/24 DC/2	2900355	
	3 A	NO ONLY - 6.2 mm	Screw	PLC-OSC-120UC/24 DC/2	2966650	
			Push-in	PLC-OPT-120UC/24 DC/2	2900355	



Note: AC outputs also available

Triple-rated, hazardous location relays (more options available, please enquire)

12 V DC	6 A	SPDT - 6.2 mm	Screw	PLC-RSC-12 DC/21/EX	2909522	
			Screw	PLC-RSC-12 DC/21-21/EX	2909517	
	10 A	SPDT - 14 mm	Screw	PLC-RSC-12 DC/21/HC/EX	2909518	
24 V DC	6 A	SPDT - 6.2 mm	Screw	PLC-RSC-24 DC/21/EX	2909524	
			Push-in	PLC-RPT-24 DC/21/EX	2909528	
		DPDT - 14 mm	Screw	PLC-RSC-24 DC/21-21/EX	2909509	
			Push-in	PLC-RPT-24 DC/21-21/EX	2909514	
230 V AC	6 A	SPDT 6.2 mm	Screw	PLC-RSC-230UC/21/EX	2909526	
			Screw	PLC-RSC-230UC/21-21/EX	2909512	
	10 A	DPDT 14 mm	Screw	PLC-RSC-230UC/21HC/EX	2909521	
			Screw	PLC-RSC-230UC/21HC/EX	2909521	

Note: Additional coil voltages and connection technology options are available

Specialty

120 V AC/DC	6 A	SPDT - 6.2 mm	Screw	PLC-RSC-120UC/21/SO46	5603593
-------------	-----	---------------	-------	-----------------------	---------

Note: Other specialty relays available (manual switch, force-guided, filter, high-density, DC motor control, etc.)

Replacement Parts


Mechanical Relays

Input-Coil Voltage	Output Current	Sets of Contacts	Description	Order #
12 V DC	6 A	SPDT - 6.2 mm	REL-MR-12 DC/21	2961150
24 V DC	6 A	SPDT - 6.2 mm	REL-MR-24 DC/21	2961105
		DPDT - 14 mm	REL-MR-24 DC/21-21	2961192
230 V AC	8 A	SPDT - 16 mm	REL-MR-230AC/21-21	2961451
	16 A		REL-MR-230AC/21HC/MS	2987914
	8A		REL-MR-230AC/21-21/MS	2987972



Solid-State Relays

5 V DC	3 A	SPST - 6.2 mm	OPT-5 DC/24 DC/2	2967989
24 V DC	3 A	SPST - 6.2 mm	OPT-24 DC/24 DC/2	2966595
60 V AC	3 A	SPST - 6.2 mm	OPT-60 DC/24 DC/2	2966605



PLC Relay Bridging

Easily bridge relays together with plug-in bridging – no tools required. Available in 2 positions or in continuous pieces for cutting to custom length.

Colour	2-Pos	500 mm
Red	2966236	2966786
Blue	2966812	2966692
Gray	2966825	2966838



General Purpose and Pluggable Relays

■ What application or load are you switching: electromechanical or solid state?					■ How many sets of contacts do you need? SPDT, DPDT, etc.	
■ What is the input coil voltage: DC or AC?					■ Which connection technology: Screw terminal (UT) or Push-in (PT)?	
■ What is your output current (Amps)?					What accessories are needed?	
RIF Slimline relays						
	Input Voltage	Output Current	Sets of Contacts	Termination Style	Description	Order #
RIF-0	12 V DC	6 A	NO only	Screw	RIF-0-RSC-12DC/ 1	2903367
				Push-in	RIF-0-RPT-12DC/ 1	2903362
	24 V DC	6 A	NO only	Screw	RIF-0-RSC-24DC/ 1	2903366
				Push-in	RIF-0-RPT-24DC/ 1	2903361
RIF-1	12 V DC	11 A	SPDT	Screw	RIF-1-RSC-LDP-12DC/1X21	2908500
				Push-in	RIF-1-RPT-LDP-12DC/1X21	2906224
		8 A	DPDT	Screw	RIF-1-RSC-LDP-12DC/2X21	2908501
				Push-in	RIF-1-RPT-LDP-12DC/2X21	2906223
	24 V DC	11 A	SPDT	Screw	RIF-1-RSC-LDP-24DC/1X21	2903358
				Push-in	RIF-1-RPT-LDP-24DC/1X21	2903342
		8 A	DPDT	Screw	RIF-1-RSC-LDP-24DC/2X21	2903350
				Push-in	RIF-1-RPT-LDP-24DC/2X21	2903334
		50 mA	SPDT	Screw	RIF-1-RSC-LDP-24DC/1X21AU	2903354
				Push-in	RIF-1-RPT-LDP-24DC/1X21AU	2903338
			DPDT	Screw	RIF-1-RSC-LDP-24DC/2X21AU	2903346
				Push-in	RIF-1-RPT-LDP-24DC/2X21AU	2903330
	230 V AC	8A	2PDT	Screw	RIF-1-RSC-LV-230AC/2X21	2903347
		10A	1PDT	Push-in	RIF-1-RPT-LV-230AC/1X21	2903339
		8A	2PDT	Push-in	RIF-1-RPT-LV-230AC/2X21	2903331
		10A	1PDT	Screw	RIF-1-RSC-LV-230AC/1X21	2903355
	8A	2PDT	Screw	RIF-1-RSC-LV-230AC/2X21	2903347	
RIF Ice-Cube Relays						
	Input Voltage	Output Current	Sets of Contacts	Termination Style	Description	Order #
RIF-2	24 V DC	10 A	2PDT	Screw	RIF-2-RSC-LDP-24DC/2X21	2903326
				Push-in	RIF-2-RPT-LDP-24DC/2X21	2903315
		6 A	4PDT	Screw	RIF-2-RSC-LDP-24DC/4X21	2903320
				Push-in	RIF-2-RPT-LDP-24DC/4X21	2903308
	230 V AC	5 A	4PDT	Screw	RIF-2-RSC-LV-230AC/4X21	2903316
				Push-in	RIF-2-RPT-LV-230AC/4X21	2903304
RIF-3	24 V DC	10 A	2PDT	Screw	RIF-3-RSC-LDP-24DC/2X21	2903303
				Push-in	RIF-3-RPT-LDP-24DC/2X21	2903297
		8.5 A	3PDT	Screw	RIF-3-RSC-LDP-24DC/3X21	2903300
				Push-in	RIF-3-RPT-LDP-24DC/3X21	2903294
	230 V AC	7 A	2PDT	Screw	RIF-3-RSC-LV-230AC/2X21	2903301
				Push-in	RIF-3-RPT-LV-230AC/2X21	2903295
		6 A	3PDT	Screw	RIF-3-RSC-LV-230AC/3X21	2903298
				Push-in	RIF-3-RPT-LV-230AC/3X21	2903292
RIF-4	24 V DC	10 A	3PDT	Screw	RIF-4-RSC-LDP-24DC/3X21	2903288
				Push-in	RIF-4-RPT-LDP-24DC/3X21	2903278
	230 V AC	8 A	3PDT	Screw	RIF-4-RSC-LV-230AC/3X21	2903285
				Push-in	RIF-4-RPT-LV-230AC/3X21	2903276



RIF-0
6.2 mm wide
66 mm tall
Lowest profile of all relays



RIF-1
16 mm wide
75 mm tall
Pin contacts



RIF-2
31 mm wide
75 mm tall
Blade contacts



RIF-3
40 mm wide
Pin contacts



RIF-4
42 mm wide
Small contactor style
Blade contacts

Note: Many additional contact arrangement and coil voltage options exist.



RIF-0
6.2 mm wide
66 mm tall
Lowest profile of all
relays



RIF-1
16 mm wide
75 mm tall
Pin contacts



RIF-2
31 mm wide
75 mm tall
Blade contacts



RIF-3
40 mm wide
Pin contacts



RIF-4
42 mm wide
Small contactor style
Blade contacts

Note: Many additional contact arrangement and coil voltage options exist.

Description	Order #
MACX-TR-1T-MUL	1096429
MACX-TR-2T-MUL	1103345
MACX-TR-2T-MUL-PT	1103355
MACX-TR-1T-MUL-PT	1096431

Smart Timer Relay

Exact time setting without
testing and calculation



Display with countdown function for
monitoring the module status



PIN code for protection
from unauthorised changes



Quick selection of time functions using
function diagrams on easy to read OLED
display or smartphone



Can be operated via the device keys or via
app with guided configuration



Error-free and fast transfer of existing
and stored configurations via smartphone
using NFC communication

Hybrid Motor Starters

■ What type of motor start do you need?				■ What are the required functions?						
■ What is the maximum load current?				■ Resulting Phoenix Contact part number (by connection technology)						
■ What is your input voltage?										
		Functions							Connection Technology	
		Direct Starter	Reversing Starter	Motor Protection	Emergency Stop ¹	Can Be Networked	ATEX	Short-Circuit Protection	Screw	Push-In
Maximum Load Current	Input Voltage ²									
Stand-Alone ³										
0.6 A	24 V DC	✓		✓	✓		✓		2900566	2903914
		✓	✓	✓	✓		✓		2900582	2903902
		✓	✓	✓	✓		✓	✓	2902746	
		✓	✓	✓					2900542	2903920
2.4 A	24 V DC	✓		✓	✓		✓		2900573	2903908
		✓	✓	✓	✓		✓		2900567	2903916
		✓	✓	✓	✓		✓		2900414	2903904
		✓	✓	✓	✓		✓	✓	2902744	
		✓		✓					2900543	2903922
9 A	24 V DC	✓	✓	✓	✓		✓		2900574	2903910
		✓	✓	✓	✓		✓		2900569	2903918
		✓	✓	✓	✓		✓		2900421	2903906
		✓	✓	✓	✓		✓	✓	2902745	
		✓		✓					2900545	2903924
		✓	✓	✓					2900576	2903912
		✓							2900530	
✓	✓						2900538			
Network-Capable (Gateway Required)										
0.6 A	24 V DC	✓		✓	✓	✓	✓		2905154	2905141
		✓	✓	✓	✓	✓	✓		2905151	2905138
		✓		✓		✓			2905162	2905148
		✓	✓	✓		✓			2905157	2905144
3 A	24 V DC	✓		✓	✓	✓	✓		2905155	2905142
		✓	✓	✓	✓	✓	✓		2905152	2905139
		✓		✓		✓			2905163	2905149
		✓	✓	✓		✓			2905159	2905146
9 A	24 V DC	✓		✓	✓	✓	✓		2905156	2905134
		✓	✓	✓	✓	✓	✓		2905153	2905140
		✓		✓		✓			2908164	2905150
		✓	✓	✓		✓			2905160	2905147

¹Dependent on the application up to PL e / SIL 3.


²Also available in 230 V versions. Check Phoenix Contact website for the full range.

³Modular options also available.

¹Dependent on the application up to PL e / SIL 3.

²Also available in 230 V versions. Check Phoenix Contact website for the full range.

³Modular options also available.

Solid State Contactors					
		Functions			
Maximum Load Current	Input Voltage	Direct Starter	Reversing Starter	Single-Phase	3-Phase
					
20 A	24 V DC	✓		1032919	
	230 V AC	✓		1032920	
30 A	24 V DC	✓		1032921	
	230 V AC	✓		1032922	
37 A	24 V DC	✓			2297277
		✓	✓		2297374
	230 V AC	✓			2297280
		✓	✓		2297387
50A	24 V DC	✓		1032926	
	230 V AC	✓		1032927	

CONTACTRON Speed Starter

■ Is the input single- or three-phased?			■ Housing and dimension specifications		
■ What is the size of your motor?			■ Resulting Phoenix Contact part number		
■ What is your nominal current (input/output)?					
Motor Power	Voltage/Current Input	Voltage/Current Output	Housing	Type	Order #
Single-phase load input, with EMC filter¹					
0.25 kW/0.3 HP	3.5 A	1.7 A	A2	CSS0.25-1/3-EMC	1201520
0.37 kW/0.5 HP	5.3 A	2.5 A	A2	CSS0.37-1/3-EMC	1201600
0.55 kW/0.7 HP	6.7 A	3.2 A	B2	CSS0.55-1/3-EMC	1201602
0.75 kW/1.0 HP	9.1 A	4.3 A	B2	CSS0.75-1/3-EMC	1201613
1.5 kW/2.0 HP	15.8 A	7.5 A	B2	CSS1.5-1/3-EMC	1201642
Three-phase load input, with EMC filter¹					
0.25 kW/0.3 HP	1.0 A	0.9 A	A2	CSS0.25-3/3-EMC	1201713
0.37 kW/0.5 HP	1.7 A	1.5 A	A2	CSS0.37-3/3-EMC	1201825
0.55 kW/0.7 HP	2.0 A	1.8 A	A2	CSS0.55-3/3-EMC	1201828
0.75 kW/1.0 HP	2.8 A	2.5 A	A2	CSS0.75-3/3-EMC	1201829
1.5 kW/2.0 HP	4.2 A	3.9 A	B2	CSS1.5-3/3-EMC	1201696

¹Also available without EMC filter- Check Phoenix Contact website for the full range-

Housing ²					
					
Description	A1	A2	B1 heatsink	B1 fan	B2
Cooling	Heatsink	Replaceable fan	Heatsink	Replaceable fan	Replaceable fan
Dimensions (H x W x D)	180 x 35 x 165 mm	180 x 35 x 185 mm	180 x 45 x 180 mm	180 x 45 x 180 mm	180 x 45 x 200 mm

²A1, B1 heatsink and B1 fan housing are available for motor starters without EMC filter only. For more details, check Phoenix Contact website.

Direct Start
Easy control directly via 24 V PLC output cards or the 24 V output of the device



Reversing Start
Reverse rotation via buttons directly on the device



Motor Protection
Comfortable protection via flexible nominal current setting of the motor including remote reset function



Safe Torque Off
The integrated safety function enables use in safety-related emergency stop applications



Various Speeds
Speeds can be customised and modified as desired



Ramp Function
Fully-adjustable soft motor start and shutdown.

Signal Conditioners

■ What type of conversion and/or isolation do you need?				
■ What is the module power? (Standard is module powered by separate 24 V DC)				
■ What is your input signal?				
■ What is the output signal?				
■ Resulting Phoenix Contact part number				
Fixed Signal Conversion and Isolation				
Module Power	Input Signal	Output Signal	Description	Order #
Line	0-10 V DC	0-10 V DC	MINI MCR-2-U-U	2902042
		Active 4-20 mA	MINI MCR-2-U-I4	2902029
	Active 4-20 mA	0-10 V DC	MINI MCR-2-I4-U	2902002
		Active 4-20 mA	MINI MCR-2-I-I	2901998
Universal and Configurable Analog Sign				
Module Power	Input Signal	Output Signal	Description	Order #
Line	Active/universal	Active/Universal	MINI MCR-2-UI-UI	2902037
	Active/universal	Active/Universal/Relay Out	MINI MCR-2-UNI-UI-UIRO	2902026
	4 mA ... 20 mA	4 mA-20 mA	MINI MCR-2-RPSS-I-I	2902014
	0 V ... 10 V	4 mA-20 mA	MINI MCR-2-U-I4-PT	2902030
	Universal	Contact Relay	MINI MCR-2-UI-REL-PT	2902035
	Universal	Universal	MINI MCR-2-UNI-UI-2UI	2905026
	Voltage	Universal	MINI MCR-2-U-UI	2902019
	Voltage	Voltage	MINI MCR-2-U-U-PT	2902043
Temperature Signal Conversion and Isolation				
Module Power	Input Signal	Output Signal	Description	Order #
Loop	RTD	Universal Analog	MINI MCR-2-RTD-UI	2902049
	Thermocouple	Universal Analog	MINI MCR-2-TC-UI	2902055
	Universal Temperature	N.O. Relay Set Point	MINI MCR-2-T-REL	2905632
	PT100	Common Analog	MINI MCR-SL-PT100-LP-NC	2810308
Low-Power Signal Conversion and Isolation				
Module Power	Input Signal	Output Signal	Description	Order #
Loop	Active 4-20 mA	Passive 4-20 mA	MINI MCR-2-I-I-ILP	2901994
			MINI MCR-2-2I-2I-ILP	2901996
	Active Universal Analog	Active 4-20 mA	MINI MCR-2-UI-I-OLP	2902061
			MINI MCR-2-RPS-I-I-OLP	2906446
	vvvv Passive 4-20 mA	Active 4-20 mA	MINI MCR-2-RPS-2I-2I-OLP	2906448
Specialty Signal Conversion and Isolation				
Module Power	Input Signal	Output Signal	Description	Order #
Line	4-20 mA/HART	2x 4-20mA/HART	MINI MCR-2-RPSS-I-2I	2905628
	Analog	Frequency and Set Point	MINI MCR-2-UI-FRO	2902031
	Frequency And PWM	Active 4-20 mA	MINI MCR-2-F-UI	2902056
	Load Cell/Strain Gage	4-20 ma/0-10 V	MCR-SGA-4/6-DC	5604058
	Potentiometer	Active 4-20 mA	MINI MCR-2-POT-UI	2902016
	Universal Analog	2x 4-20 mA	MINI MCR-2-UI-2I-NC	2905026
Universal Analog	Set Point/Relay Out	MINI MCR-2-UI-REL	2902033	
HART				
Module Power	Input Signal	Output Signal	Description	Order #
Line	4-20 mA/HART	4-20 mA/HART	MINI MCR-2-RPSS-I-I	2902014



MINI MCR-2


Connectivity, switching and conversion

Rapid power bridging and group error messaging

In addition to rapid power bridging, the DIN rail connector also simplifies wiring, system extension, or module replacement during operation. Group error messaging enables convenient diagnostics.

Service-friendly

Large-surface marking areas enable complete loop identification using standard marking material. All status and error indicators are always visible and provide an instant overview on site.



Easily accessible terminal points and FASTCON Pro plug-in connection terminal blocks



Measure signals during operation, without disconnecting the current loops.

Smart parameterisation and monitoring

Depending on the product type, you can access the devices wirelessly: via NFC and Bluetooth. Benefit from the comprehensive functions of the MINI Analog Pro app and parameterise the modules directly on site or read the current measured values during operation.



Heavy-Duty Connectors

Standard (Metal)



Evo (Plastic)



Selector Guide (Pick 4 Parts)

1	2	3	4			
INSERT (M&F)	BASE	SLEEVE HOUSING	CABLE GLAND			
	+		+		+	

How many poles do you need?

What connection technology do you prefer?

Gender (Male / Female)?

Panel mounting with or without cover?

Hood - top or lateral entry?

HEAVYCON STANDARD											
Poles	Technology	Socket (F)		Plug (M)		Panel Mounting Base		Hood - Top Entry		Hood - Lateral Entry	
		Part Number	Description	Part Number	Description	With Cover	W/O Cover	Low Profile	High Profile	Low Profile	High Profile
6 poles	Screw	1648128	HC-B 6-I-UT-F	1648115	HC-B 6-I-UT-M	1411319	1411318	1412574 (M20)	1412566 (M25)	1412570 (M20)	1412562 (M25)
	Push-in	1407727	HC-B 6-I-PT-F	1407728	HC-B 6-I-PT-M	1411319	1411318	1412574 (M20)	1412566 (M25)	1412570 (M20)	1412562 (M25)
	Crimp	1648160	HC-B 6-I-CT-F	1648157	HC-B 6-I-CT-M	1411319	1411318	1412574 (M20)	1412566 (M25)	1412570 (M20)	1412562 (M25)
10 poles	Screw	1648186	HC-B 10-I-UT-F	1648173	HC-B 10-I-UT-M	1411321	1411320	1412629 (M20)	1412605 (M32)	1412625 (M25)	1412600 (M25)
	Push-in	1407729	HC-B 10-I-PT-F	1407730	HC-B 10-I-PT-M	1411321	1411320	1412629 (M20)	1412605 (M32)	1412625 (M25)	1412600 (M25)
	Crimp	1605569	HC-B 10-I-CT-F	1605624	HC-B 10-I-CT-M	1411321	1411320	1412629 (M20)	1412605 (M32)	1412625 (M25)	1412600 (M25)
16 poles	Screw	1648241	HC-B 16-I-UT-F	1648238	HC-B 16-I-UT-M	1411325	1411324	1412730 (M32)	1412689 (M32)	1412726 (M32)	1412679 (M32)
	Push-in	1407731	HC-B 16-I-PT-F	1407732	HC-B 16-I-PT-M	1411325	1411324	1412730 (M32)	1412689 (M32)	1412726 (M32)	1412679 (M32)
	Crimp	1648283	HC-B 16-I-CT-F	1648270	HC-B 16-I-CT-M	1411325	1411324	1412730 (M32)	1412689 (M32)	1412726 (M32)	1412679 (M32)
24 poles	Screw	1648306	HC-B 24-I-UT-F	1648296	HC-B 24-I-UT-M	1411332	1411331	1412779 (M32)	1412754 (M32)	1412774 (M32)	1412750 (M32)
	Push-in	1407735	HC-B 24-I-PT-F	1407736	HC-B24-I-PT-M	1411332	1411331	1412779 (M32)	1412754 (M32)	1412774 (M32)	1412750 (M32)
	Crimp	1648348	HC-B 24-I-CT-F	1648335	HC-B 24-I-CT-M	1411332	1411331	1412779 (M32)	1412754 (M32)	1412774 (M32)	1412750 (M32)

HEAVYCON EVO									
Poles	Technology	Socket (F)		Plug (M)		Panel Mounting Base		Hood - Top And Lateral Entry	
		Part Number	Description	Part Number	Description	With Cover	W/O Cover	Low Profile	High Profile
6 poles	Screw	1648128	HC-B 6-I-UT-F	1648115	HC-B 6-I-UT-M	1407622	1407621	1407619	1407620
	Push-In	1407727	HC-B 6-I-PT-F	1407728	HC-B 6-I-PT-M	1407622	1407621	1407619	1407620
	Crimp	1648160	HC-B 6-I-CT-F	1648157	HC-B 6-I-CT-M	1407622	1407621	1407619	1407620
10 poles	Screw	1648186	HC-B 10-I-UT-F	1648173	HC-B 10-I-UT-M	1407633	1407632	1407626	1407627
	Push-In	1407729	HC-B 10-I-PT-F	1407730	HC-B 10-I-PT-M	1407633	1407632	1407626	1407627
	Crimp	1605569	HC-B 10-I-CT-F	1605624	HC-B 10-I-CT-M	1407633	1407632	1407626	1407627
16 poles	Screw	1648241	HC-B 16-I-UT-F	1648238	HC-B 16-I-UT-M	1407647	1407646	1420931	1407642
	Push-In	1407731	HC-B 16-I-PT-F	1407732	HC-B 16-I-PT-M	1407647	1407646	1420931	1407642
	Crimp	1648283	HC-B 16-I-CT-F	1648270	HC-B 16-I-CT-M	1407647	1407646	1420931	1407642
24 poles	Screw	1648306	HC-B 24-I-UT-F	1648296	HC-B 24-I-UT-M	1407662	1407661	1420935	1407657
	Push-In	1407735	HC-B 24-I-PT-F	1407736	HC-B24-I-PT-M	1407662	1407661	1420935	1407657
	Crimp	1648348	HC-B 24-I-CT-F	1648335	HC-B 24-I-CT-M	1407662	1407661	1420935	1407657

ACCESSORIES - CABLE GLAND

HEAVYCON STANDARD	
M20	1411163
M25	1411165
M32	1411166
M40	1411167

HEAVYCON EVO	
7-13mm	1407669 (M20 equivalent)
9-17mm	1407670 (M25 equivalent)
11-21mm	1407671 (M32 equivalent)
19-28mm	1407672 (M40 equivalent)

M12 Connectors

A comprehensive range of M8 and M12 flush-type connectors and panel feed-through has emerged as a result of the various requirements for sensor/actuator device connection technology in industrial environments.

Customer-specific developments for assembly enable optimum adaptation to individual device concepts.

- ✓ 3 to 17 positions
- ✓ A, B, D, or X coding
- ✓ Available in Screw, Insulation displacement, Push-in, and Crimp connection



Connectivity, switching and conversion

M8						
	Positions	Connection Tech	Gender	Diameter	Order #	Description
3-position Female  Male 	3-Pos.	Screw	Male Straight	3.5-5 mm	1501252	SACC-M 8MS-3CON-M-SW
			Female Straight		1506888	SACC-M 8FS-3CON-M-SW
		Insulation Displacement	Male Straight	2.5-5 mm	1441008	SACC-M 8MS-3QO-0,25-M
			Female Straight		1441066	SACC-M 8FS-3QO-0,5-M
4-position Female  Male 	4-Pos.	Screw	Male Straight	3.5-5 mm	1681169	SACC-M 8MS-4CON-M
			Female Straight		1506891	SACC-M 8FS-4CON-M-SW
		Insulation Displacement	Male Straight	3.5-5 mm	1441037	SACC-M 8MS-4QO-0,5-M
			Female Straight		1521601	SACC-FS-4QO-0,75-M SCO

M12						
	Positions	Connection Tech	Head	Diameter	Order #	Description
4-position Female  4-position Male 	4-Pos.	Screw	Male Straight	4-6 mm	1662528	SACC-M12MS-4CON-PG 7-M
			Male Angled		1681101	SACC-M12MR-4CON-PG7-M
			Female Straight		1681127	SACC-M12FS-4CON-PG7-M
			Female Angled		1681143	SACC-M12FR-4CON-PG7-M
		Insulation Displacement	Male Straight	4-8 mm	1641785	SACC-M12MS-4QO-0,75-M
			Female Straight		1641772	SACC-M12FS-4QO-0,75-M
		Push-In	Male Straight	4-8 mm	1424657	SACC-MS-4PL M SCO
			Male Angled		1424654	SACC-M12MR-4PL M
5-position Female  5-position Male 	5-Pos.	Screw	Male Straight	4-6 mm	1663116	SACC-M12MS-5CON-PG 7-M
			Male Angled	6-8 mm	1681460	SACC-M12MS-5CON-PG 9-M
			Female Straight	4-6 mm	1663129	SACC-M12MR-5CON-PG 7-M
			Female Angled		1662968	SACC-M12FS-5CON-PG 7-M
		Push-In	Male Straight	4-8 mm	1662984	SACC-M12FR-5CON-PG 7-M
			Female Straight		1424649	SACC-M12MS-5PL M
			Male Angled		1424652	SACC-M12FS-5PL M
			Female Angled		1424651	SACC-M12MR-5PL M
8-position Female  8-position Male 	8-Pos.	Screw	Female Straight	6-8 mm	1513347	SACC-M12FS-8CON-PG9-M
			Male Straight		1513334	SACC-M12MS-8CON-PG9-M

Cordsets



■ What thread size do you need on your cordset: M8 or M12?											
■ How many positions (wires) are required?											
■ What gender should the connectors be: female or male?											
■ Is the head orientation straight or right angle?											
■ What is the desired cordset length?											
■ Resulting Phoenix Contact part numbers (shielded and non-shielded)											
■ Select CMAT: Allows you to configure cable type/length (enter into extranet tool)											
■ Do you need a mating front- or rear-mount receptacle with the cordset?											
**Locknut not included with front mount. M8 locknuts (8 mm) = 1504071. M12 locknuts (16 mm) = 1504097											
M8											
	Positions	Gender	Head Orientation	Length	Non-Shielded PUR Jacket Part #	Non-Shielded CMAT #	Shielded PUR Jacket Part #	Shielded CMAT #	Front-Mount Receptacle	Rear-Mount Receptacle	
3-Position Female  Male 	3-Pos.	Male/Female	Straight	1.5 m	1681923	1405935	1455285	1405828	1500350	1453449	
		Female	Straight	5 m	1669628	1405956	1521737	1405834	1500334	1453478	
			Right Angle		1669631	1405957	1521782	1405835	1500334	1453478	
		Male	Straight		1681680	1405939	1521630	1405830	1500350	1453449	
			Right Angle		1681716	1405944	1521685	1405833	1500350	1453449	
		Female	Straight	10 m	1694101	1405956	1521740	1405834	1500334	1453478	
	Right Angle		1694169		1405957	1521795	1405835	1500334	1453478		
	Male	Straight	1693584		1405939	1521643	1405830	1500350	1453449		
		Right Angle	1694114		1405944	1521698	1405833	1500350	1453449		
	4-position Female  Male 	4-Pos.	Male/Female	Straight	1.5 m	1682168	1405902	1455735	1405810	1500363	1453452
			Female	Straight	5 m	1681868	1405923	1521931	1405822	1500347	1453481
				Right Angle		1681897	1405924	1521986	1405823	1500347	1453481
Male			Straight	1681800		1405906	1521834	1405818	1500363	1453452	
			Right Angle	1681839		1405911	1521889	1405821	1500363	1453452	
Female			Straight	10 m	1683484	1405923	1521944	1405822	1500347	1453481	
		Right Angle	1694172		1405924	1521999	1405823	1500347	1453481		
Male		Straight	1694143		1405906	1521847	1405818	1500363	1453452		
		Right Angle	1694156		1405911	1521892	1405821	1500363	1453452		
M12											
		Positions	Gender	Head Orientation	Length	Non-Shielded PUR Jacket Part #	Non-Shielded CMAT #	Shielded PUR Jacket Part #	Shielded CMAT #	Front-Mount Receptacle	Rear-Mount Receptacle
3-Position Female  Male 		3-Pos.	Male/Female	Straight	1.5 m	1681525		1500826			
	Female		Straight	5 m	1683510	1405947	1682809	1405927	1523434	1419632	
			Right Angle		1694525	1405959	1682838	1405934	1523450	1419629	
	Male		Straight		1668030	1405949	1682676	1405929	1523434	1419632	
			Right Angle		1668153	1405955	1682702	1405932	1523434	1419632	
	Female		Straight	10 m	1693034	1405958	1500680	1405933	1523450	1419629	
		Right Angle	1694538		1405959	1500693	1405934	1523450	1419629		
	Male	Straight	1682566		1405949	1500664	1405929	1523434	1419632		
		Right Angle	1694444		1405955	1500677	1405932	1523434	1419632		
	4-position Female  Male 	4-Pos.	Male/Female	Straight	1.5 m	1668373		1500868			
			Female	Straight	5 m	1668124	1405925	1682867	1405900	1523450	1419629
				Right Angle		1668247	1405926	1682922	1405901	1523450	1419629
Male			Straight	1668069		1405916	1682647	1405896	1523434	1419632	
			Right Angle	1668182		1405922	1682896	1405899	1523434	1419632	
Female			Straight	10 m	1683002	1405925	1500716	1405900	1523450	1419629	
		Right Angle	1681389		1405926	1500729	1405901	1523450	1419629		
Male		Straight	1682993		1405916	1694389	1405896	1523434	1419632		
		Right Angle	1694457		1405922	1500703	1405899	1523434	1419632		
5-position Female  Male 		5-Pos.	Male/Female	Straight	1.5 m	1681606	1405886	1500907	1405877	1520039	1419658
			Female	Straight	5 m	1669848	1405892	1682951	1405884	1520055	1419645
				Right Angle		1669877	1405893	1682980	1405885	1520055	1419645
	Male		Straight	1669783		1405888	1682731	1405879	1520039	1419658	
			Right Angle	1669819		1405891	1682773	1405883	1520039	1419658	
	Female		Straight	10 m	1683374	1405886	1500758	1405877	1520039	1419658	
		Right Angle	1694541		1405892	1500761	1405884	1520055	1419645		
	Male	Straight	1683361		1405893	1500732	1405885	1520055	1419645		
		Right Angle	1694460		1405888	1500745	1405879	1520039	1419658		
	8-position Female  Male 	8-Pos.	Male/Female	Straight	1.5 m	1522697	1405891	1522985	1405883	1520039	1419658
			Female	Straight	5 m	1520369	1405851	1522888	1405843	1523492	1419687
				Right Angle		1522642	1405852	1522930	1405844	1523492	1419687
Male			Straight	1522516		1405847	1526981	1405839	1523476	1419690	
			Right Angle	1522561		1405850	1522833	1405842	1523476	1419690	
Female			Straight	10 m	1520372	1405851	1522891	1405843	1523492	1419687	
		Right Angle	1522655		1405852	1522943	1405844	1523492	1419687		
Male		Straight	1522529		1405847	1522794	1405839	1523476	1419690		
		Right Angle	1522574		1405850	1522846	1405842	1523476	1419690		

M8/M12 Distributor Boxes

Use distributor boxes for quick and clear cabling in the field. Distributor boxes bundle several cables into one master cable that is connected to the controller. Thanks to the status indicator, you have an overview of a large number of signals.

- ✓ Increased machine availability, thanks to easy diagnostics
- ✓ Safety in the field, thanks to molded housing and high degree of protection
- ✓ Flexible cabling, thanks to the wide product range and various master cable connections

Connectivity, switching and conversion

M8 Metal Thread

					
8 Positions ● Single Occupancy ✓ LED	8 Positions ● Double Occupancy ✓ LED				
Connection Type			Connection Type		
Master Cables	Cable Glands	Connectors	Master Cables	Cable Glands	Connectors
1197232 (5m)	1197611 (Screw)	1197575 (M12 to M8)	1197314 (5m)	1197617 (Screw)	N/A
1197236 (10m)	1197616 (Spring)	1166980 (M16 to M8)	1197319 (10m)	1197620 (Spring)	

M12 Metal Thread

 8 Positions ● Single Occupancy ✗ LED			 8 Positions ● Double Occupancy ✗ LED			 8 Positions ● Single Occupancy ✓ LED			 8 Positions ● Double Occupancy ✓ LED		
Connection Type			Connection Type			Connection Type			Connection Type		
Master Cables	Cable Glands	Connectors	Master Cables	Cable Glands	Connectors	Master Cables	Cable Glands	Connectors	Master Cables	Cable Glands	Connectors
1517042 (5m)	1516881	N/A	1517068 (5m)	1516894	N/A	1517165 (5m)	1516823	N/A	1517181 (5m)	1516836	N/A
1517055 (10m)			1517071 (10m)			1517178 (10m)			1517194 (10m)		

M12 Plastic Thread

 8 Positions • Single Occupancy ✗ LED			 8 Positions • Double Occupancy ✗ LED			 8 Positions • Single Occupancy ✓ LED			 8 Positions • Double Occupancy ✓ LED		
Connection Type			Connection Type			Connection Type			Connection Type		
Master Cables	Cable Glands	Connectors	Master Cables	Cable Glands	Connectors	Master Cables	Cable Glands	Connectors	Master Cables	Cable Glands	Connectors
1452518 (5m)	1452783	N/A	1452547 (5m)	1452796 (Screw)	1692844 (M23 to M12)	1452699 (5m)	1452848 (Screw)	N/A	1452725 (5m)	1452851 (Screw)	1692459 (M23 to M12)
1452521 (10m)			1452550 (10m)	1452974 (Spring)		1452709 (10m)	1453025 (Spring)		1452738 (10m)	1453038 (Spring)	

Accessories

Master Cable Ring for Sensor/Actuator boxes

	
1503344	50m PUR/PVC Black

Master Cable M23 Plug Connection

	19 pos.
1684056	5m PUR/PVC black

Ethernet Switches

Unmanaged Switches

How many copper ports are required?						Are dual-power input and alarm contacts required?		
Are specialty ports required: Power Over Ethernet (PoE) and/or fiber optic?						Is the installation in a hazardous location?		
What are the total number of ports required?						Are extreme environmental conditions present?		
What speed is required in the network?						Resulting Phoenix Contact part number		
Unmanaged Switch 1000								
Copper Ports	Specialty Ports	Total Ports	Speed	Power Alarm	Hazardous	Type Description	Order #	
5		5	10/100	N	Y	FL SWITCH 1005N	1085039	
8		8	10/100	N	Y	FL SWITCH 1008N	1085256	
16		16	10/100	N	Y	FL SWITCH 1016N	1085255	
5		5	Gigabit	N	Y	FL SWITCH 1105N	1085254	
8		8	Gigabit	N	Y	FL SWITCH 1108N	1085243	
SFNB								
5		5	10/100	N	Y	FL SWITCH SFNB 5TX	2891001	
4	1 Fiber, SC MM	4	10/100	N	Y	FL SWITCH SFNB 4TX/FX	2891027	
4	1 Fiber, ST MM	4	10/100	N	Y	FL SWITCH SFNB 4TX/FX ST	2891028	
4	1 Fiber, SC SM	4	10/100	N	Y	FL SWITCH SFNB 4TX/FX SM20	2891029	
8		8	10/100	N	Y	FL SWITCH SFNB 8TX	2891002	
SFN								
5		5	10/100	N	Y	FL SWITCH SFN 5TX	2891152	
4	1 Fiber, SC MM	5	10/100	N	Y	FL SWITCH SFN 4TX/FX	2891851	
4	1 Fiber, ST MM	5	10/100	N	Y	FL SWITCH SFN 4TX/FX ST	2891453	
8		8	10/100	N	Y	FL SWITCH SFN 8TX	2891929	
7	1 Fiber, SC MM	8	10/100	N	Y	FL SWITCH SFN 7TX/FX	2891097	
7	1 Fiber, ST MM	8	10/100	N	Y	FL SWITCH SFN 7TX/FX ST	2891110	
6	2 Fiber, SC MM	8	10/100	N	Y	FL SWITCH SFN 6TX/2FX	2891314	
6	2 Fiber, ST MM	8	10/100	N	Y	FL SWITCH SFN 6TX/2FX ST	2891411	

Managed Switches

■ How many copper ports are required?	■ What special features are included?						
■ How many fiber optic ports are required?	■ What is the designation of the FL Switch?						
■ What are the total number of combo ports?	■ Resulting Phoenix Contact part number						
■ What is the speed?							
Copper Ports	Fiber Optic Ports	Combo Ports	Port Speed	Special Features	Designation FL SWITCH	Order #	
Intelligent Switches for the Machine: Switch 2000 and 2100							
Supply voltage: 18-32 V DC (redundant), temperature range: -0°C to +60°C, IP20, front port outlet direction							
5 x RJ45	-	-	10/100 Mbps	-	2005	2702323	
8 x RJ45	-	-		-	2008	2702324	
16 x RJ45	-	-		-	2016	2702903	
5 x RJ45	-	-	10/100/1,000 Mbps	-	2105	2702665	
8 x RJ45	-	-		-	2108	2702666	
16 x RJ45	-	-		-	2116	2702908	
Intelligent Switches for Universal Use: Switch 2200 and 2300							
Supply voltage: 12-57 V DC (redundant), temperature range: -40°C to +70°C, IP20, front port outlet direction, PROFINET Class B							
Approvals: DNV/GL, BV, ABS, LR, RINA, IECEx, ATEX Zone 2							
5 x RJ45	-	-	10/100 Mbps	Digital alarm output Fast Ring Detection, Large Tree Support, MRP Manager, up to 32 static VLANs, pool-based DHCP server and option 82	2205	2702326	
8 x RJ45	-	-			2208	2702327	
16 x RJ45	-	-			2216	2702904	
8 x RJ45	-	-	10/100/1,000 Mbps		2308	2702652	
6 x RJ45	2 x SFP	-			2306-2SFP	2702970	



PoE and Installation Technology

How many copper ports are required?					Are dual-power input and alarm contacts required?			
Are specialty ports required: Power Over Ethernet (PoE) and/or fiber optic?					Is the installation in a hazardous location?			
What are the total number of ports required?					Are extreme environmental conditions present?			
What speed is required in the network?					Resulting Phoenix Contact part number			
Copper Ports	Specialty Ports	Total Ports	Speed	Power Alarm	Hazardous	Description	Order #	SFNB
POE								
1	4 PoE+	5	10/100	Y	N	FL SWITCH 1001T-4POE	2891064	POE 
0	2 PoE+/2 Fiber SFP	4	Gigabit	Y	N	FL SWITCH 1000T-2POE-GT-2SFP	1026765	
0	8 PoE+/2 Fiber SFP	10	Gigabit	Y	N	FL SWITCH SWITCH 1000-8POE-GT	1102079	
1	4 PoE+/1 Fiber SFP	6	Gigabit	Y	N	FL SWITCH 1001T-4POE-GT-SFP	1026932	
1	4 PoE+	5	Gigabit	Y	N	FL SWITCH 1001T-4POE-GT	1026937	
IP67								
5		24	10/100	N	N	FL SWITCH 1605 M12	2700200	

What connection methods does it have?			What PoE standard does it comply to?								
What is the temperature rating?			What is the designation?								
What is the max power allowed?			Resulting Phoenix Contact part number								
Does it have any special features?											
	Connection Method	Temperature Range	Power Budget	Special Features	PoE Standard	Designation	Order #				
POE Injector											
	RJ45/RJ45	0°C to +55°C	2 x 15 W	Electrical isolation in the power supply unit	IEEE 802.3 af	FL PSE 2TX	2891013				
		0°C to +60°C	15/30 W	--	IEEE 802.3 af/at (PoE+)	INJ 1000	2703005				
			60 W	Electrical isolation in the power supply unit	Prepared for PoE bt (PoE++)	INJ 1010	2703007				
				RJ45/IDC	-40°C to +75°C	15/30 W	Electrical isolation in the power supply unit, surge protection and shield current diagnostics	IEEE 802.3 af/at (PoE+)	INJ 1000-T	2703006	
60 W	Prepared for PoE bt (PoE++)	INJ 1010-T				2703008					
15/30 W	IEEE 802.3 af/at (PoE+)	INJ 1100-T				2703009					
60 W	Prepared for PoE bt (PoE++)	INJ 1110-T				2703010					
15/30 W	IEEE 802.3 af/at (PoE+)	INJ 2102-T				2703012					
60 W	Prepared for PoE bt (PoE++)	INJ 2112-T				2703014					
15/30 W	IEEE 802.3 af/at (PoE+)	INJ 2103-T				1004065					
60 W	Prepared for PoE bt (PoE++)	INJ 2113-T				1004066					
	RJ45/Push-In	-40°C to +75°C				15/30 W		Electrical isolation in the power supply unit, surge protection and shield current diagnostics	IEEE 802.3 af/at (PoE+)	INJ 2101-T	2703011
									Prepared for PoE bt (PoE++)	INJ 2111-T	2703013
	RJ45/Screw					60 W			Prepared for PoE bt (PoE++)	INJ 2111-T	2703013

PoE and Installation Technology

What connection methods does it have?	Does it have surge protection?
What type of patch panel is this?	What is the designation?
How is it shielded?	Resulting Phoenix Contact part number
How is the shield connected?	

	Connection Method	Description	Shielding	Cable Shield Connection	Surge Protection	Designation	Order #
Patch Panels							
	RJ45/RJ45	Standard ethernet patch panel, 8-Pos., 10/100/1,000 Mbps	Right on the DIN rail	Using an RJ45 socket	No	PP-RJ-RJ	2703015
	RJ45/Screw			Toolless using shield contact spring		PP-RJ-SC	2703016
	RJ45/Push-In			Using an RJ45 socket		PP-RJ-SCC	2703018
	RJ45/IDC	Function variant ethernet patch panels 8-Pos., 10/100/1,000 Mbps		Toolless using shield contact spring	Yes	PP-RJ-IDC	2703019
RJ45/RJ45	PP-RJ-RJ-F					2703020	
	RJ45 /Screw					PP-FJ-SC-F	2703021
	RJ45/Push-In					PP-RJ-SCC-F	2703022
	RJ45/IDC					With surge protection and shield current diagnostics	



Toolless Shield Connection

Connect the cable shielding to the DIN rail without tools - with strain relief assured at the same time.



Shield Current Diagnostics

The reliable display of hazardous shield currents increases the safety of the installation.



Quick and Easy Installation

Installation takes 60% less time, thanks to patented cable connection technology.

What's the voltage range?	What wireless technology used?
What's the temperature range?	What's the input/output?
What's the wireless frequency?	Resulting Phoenix Contact part number

Wireless Ethernet							
Voltage Range	Temperature Range	Wireless Frequency	Wireless Technology	I/O	Description	Order #	
9-32 VDC	-40°C to 60°C	2.4/5 GHz	WLAN a, b, g, n	-	FL WLAN 2010	1119246	
9-32 VDC	0°C to 60°C	2.4 / 5 GHz	WLAN a, b, g, n	-	FL WLAN 1100	2702534	
9-30 VDC	-40°C to 65°C	2.4 / 5 GHz	Bluetooth/WLAN a, b, g, n	-	FL EPA 2 RSMA	1005957	
Wireless Serial / IO							 
19.2-30.5 VDC	-40°C to 70°C	2.4 GHz	Trusted Wireless	-	RAD-2400-IFS	2901541	
10.8-30.5 VDC	-40°C to 70°C	915 MHz	Trusted Wireless	-	RAD-900-IFS-AU	2702878	
19.2-30.5 VDC	-40°C to 70°C	-	-	-	RAD-RS485-IFS	2702184	
19.2-30.5 VDC	-40°C to 70°C	-	-	4 Digital Inputs	RAD-DI4-IFS	2901535	
19.2-30.5 VDC	-40°C to 70°C	-	-	4 Relay Outputs	RAD-DOR4-IFS	2901536	
19.2-30.5 VDC	-40°C to 70°C	-	-	8 Digital Inputs	RAD-DI8-IFS	2901539	
19.2-30.5 VDC	-40°C to 70°C	-	-	8 Digital Transistor Outputs	RAD-DO8-IFS	2902811	
19.2-30.5 VDC	-40°C to 70°C	-	-	4 Analogue Inputs	RAD-AI4-IFS	2901537	
19.2-30.5 VDC	-40°C to 70°C	-	-	4 Analogue Outputs	RAD-AO4-IFS	2901538	
19.2-30.5 VDC	-40°C to 70°C	-	-	2 Digital Inputs and Outputs, 1 Analogue Input and Output	RAD-DAIO6-IFS	2901533	
19.2-30.5 VDC	-40°C to 70°C	-	-	4 RTD PT100 Inputs	RAD-PT100-4-IFS	2904035	
19.2-30.5 VDC	-40°C to 70°C	-	-	4 NAMUR Digital Inputs	RAD-NAM4-IFS	2316275	

What's the antenna type?	What's the connection method?
What frequency	Resulting Phoenix Contact part number
Antenna gain	

Wireless Accessories - Antenna							
Antenna Type	Frequency	Gain	Connection	Description	Order #		
Omnidirectional	2.4 GHz	2 dBi	RSMA (Male)	RAD-ISM-2400-ANT-OMNI-2-1-RSMA	2701362		
Omnidirectional	2.4 GHz/5 GHz	2.5 dBi/5 dB	N (Female)	ANT-OMNI-2459-02	2701408		
Omnidirectional	2.4 GHz	6 dBi	N (Female)	RAD-ISM-2400-ANT-OMNI-6-0	2885919		
Directional	2.4 GHz/5 GHz	9 dBi	N (Female)	ANT-DIR-2459-01	2701186		
Omnidirectional	900 MHz	2 dBi	RSMA (Male)	RAD-900-ANT-OMNI-2-2-RSMA	2904801		
Omnidirectional	900 MHz	7 dBi	N (Female)	RAD-ISM-900-ANT-OMNI-5	2867199		
Omnidirectional	900 MHz	5 dBi	N (Female)	RAD-ISM-900-ANT-OMNI-FG-3-N	2867791		
Directional	900 MHz	5 dBi	N (Female)	RAD-ISM-900-ANT-YAGI-3-N	2867801		
Directional	900 MHz	8.5 dBi	N (Female)	RAD-ISM-900-ANT-YAGI-6.5-N	2867814		

What's the connection type?	What's the attenuation of the cable?
What's the length of the cable?	Resulting Phoenix Contact part number

Wireless Accessories - Coaxial cable					
Connection	Length	Attenuation	Description	Order #	
N (Male) -> RSMA (Male)	0.5 m	0.5 / 0.8 / 1.1 dB at 0.9 / 2.4 / 5.8 GHz	RAD-PIG-RSMA/N-0.5	2903263	
N (Male) -> RSMA (Male)	1 m	0.5 / 0.8 / 1.1 dB at 0.9 / 2.4 / 5.8 GHz	RAD-PIG-RSMA/N-1	2903264	
N (Male) -> RSMA (Male)	2 m	0.5 / 0.8 / 1.1 dB at 0.9 / 2.4 / 5.8 GHz	RAD-PIG-RSMA/N-2	2903265	
N (Male) -> RSMA (Male)	3 m	0.5 / 0.8 / 1.1 dB at 0.9 / 2.4 / 5.8 GHz	RAD-PIG-RSMA/N-3	2903266	
N (Male) -> RSMA (Male)	5 m	0.5 / 0.8 / 1.1 dB at 0.9 / 2.4 / 5.8 GHz	RAD-PIG-RSMA/N-5	2702140	
2x N (Male)	3 m	1.0 / 1.5 / 2.1 dB at 0.9 / 2.4 / 5.8 GHz	RAD-CAB-PFP240-10	5606124	
2x N (Male)	6 m	1.0 / 1.5 / 2.1 dB at 0.9 / 2.4 / 5.8 GHz	RAD-CAB-PFP400-20	5606125	

Secure Remote Connectivity


Phoenix Contact Order #	mGuard cloud compatible?	Does it have DMZ capability?				
Can it be installed in a hazardous location?	What external memory type does it have?	Is it cellular capable?				
How many copper ports does it have?	Does it have a full stateful firewall?	Can it fall over from a wired connection to cellular network?				
What is the temperature rating?	Is it VPN hub capable?					
mGuard						
						
Model	FL mGuard RS2000	FL mGuard RS2005	TC mGuard RS2000	FL mGuard RS4000	FL mGuard RS4004	TC mGuard RS4000
Order #	2700642	2701875	2903588	2200515	2701877	2903586
C1D2	Yes	Yes	Yes	Yes	Yes	Yes
LAN Ports Available	1	5	4	1	4	4
Temperature	-20°C -> +60°C	-20°C -> +60°C	-40°C -> +60°C	-20°C -> +60°C	-20°C -> +60°C	-40°C -> +60°C
mGuard Secure Cloud Compatible	Yes	Yes	Yes	Yes	Yes	Yes
External Memory	SD	SD	SD	SD	SD	SD
Full Stateful Firewall				Yes	Yes	Yes
VPN Hub Capability						
DMZ Capability				Yes	Yes	Yes
Cellular and GPS Capability					Yes	Yes
Failover from Wired to Cell			Yes			Yes

Cloud-Based Remote Maintenance

mGuard Secure Cloud



Functional components and features of the mGuard Secure Cloud



The mGuard Secure Cloud uses IPsec VPNs and ensures the confidentiality, authenticity, and integrity of data transmitted between devices. Service personnel use an approved VPN client, such as the mGuard Secure VPN Client Software or an FL mGuard smart, and connect their workstations to the mGuard Secure Cloud.

The machines are equipped with industry-capable remote maintenance routers and establish your VPN connection to the cloud as needed. The mGuard Secure Cloud web interface controls the service technician's access to the machines.

Features:

- Highly secure IPsec VPN communication
- 2-factor authentication
- User management for access to various customers and systems
- Superior availability worldwide
- Operated in Germany in accordance with the most stringent security and data protection standards
- Industry-proven mGuard security technology

Axioline F for the Control Cabinet

Technical Data			
Ambient Conditions		Supply Voltages	
Temperature Range (Operation)	-25°C to +60°C	Nominal Value	24 V DC
Relative Humidity (Operation)	5%-95% (No Condensation)	Ripple	±5% according to EN 61131-2
Vibration	5g According to EN 60068-2-6	Permissible Range	19.2 V DC-30.0 V DC
Shock	30g According to EN 60068-2-27	System Times	
Continuous Shock	10g According to EN 60068-2-29		
Degree of Protection	IP20		
Electromagnetic Compatibility		Approvals	
Noise Emission	Class B According to EN 61000-6-3	UL	
Noise Immunity	According to EN 61000-4		

Product description

What is the designation?

Resulting Phoenix Contact part number?

Network Connection

Bus Couplers	Description	Designation	Order #
	 Bus Coupler for PROFINET	AXL F BK PN	2701815
	 Bus Coupler for EtherCAT	AXL F BK EC	2688899
	 Bus Coupler for EtherNet/IP™	AXL F BK EIP	2688394

Bus couplers	Description	Designation	Order #
	 Bus Coupler for Modbus TCP	AXL F BK ETH	2688459
	 Bus Coupler for PROFIBUS	AXL F BK PB	2688530

Automation, networks and I/O

PLCnext Control

FLEXIBLE INTEGRATION OF OPEN-SOURCE SOFTWARE AND APPS

PLCnext Control devices enable you to work flexibly with your preferred programming languages, whether it's IEC 61131-3 or high-level languages. Unlimited flexibility with the quick and easy integration of open source software and apps, current and future communication standards, and intelligent networking through connection to the cloud afford maximum freedom for your transition into the digital age.



Description	Order #
AXC F 1152 - Compact controller	1151412
AXC F 2152 - Mid performance controller	2404267
AXC F 3152 - High performance controller	1069208

Axioline F for the Control Cabinet

What is the description of the product model?			
What is the designation?			
Resulting Phoenix Contact part number			
Acquiring Digital Data			
	Description	Designation	Order #
 DI Digital Input 16 to 64 channels - High-speed inputs 54 mm and 35 mm design width	16 Digital Inputs, 1-Wire	AXL F DI16/1 1H	2688310
	16 Digital Inputs, 1-Wire, High Speed	AXL F DI16/1 HS 1H	2701722
	16 Digital Inputs, 4-Wire	AXL F DI16/4 2F	2688022
	32 Digital Inputs, 1-Wire	AXL F DI32/1 1F	2688035
	64 Digital Inputs, 1-Wire	AXL F DI64/1 2F	2701450
 DO Digital Output 8 to 32 channels 2 A outputs 54 mm and 35 mm design width	8 Digital Outputs, 2-Wire, 2 A	AXL F DO8/2 2A 1H	2688381
	16 Digital Outputs, 1-Wire	AXL F DO16/1 1H	2688349
	16 Digital Outputs, 3-Wire	AXL F DO16/3 2F	2688048
	32 Digital Outputs, 1-Wire	AXL F DO32/1 1F	2688051
 DI DO Digital Input/Output 35 mm	8 Digital Inputs, 8 Digital Outputs, 1-Wire	AXL F DI8/1 DO8/1 1H	2701916
Acquiring Analog Data			
 AI Analog Input 4 to 8 channels 54 mm and 35 mm design width	4 Analog Inputs, Current	AXL F AI4 I 1H	2688491
	4 Analog Inputs, Voltage	AXL F AI4 U 1H	2688501
	8 Analog Inputs, Current/Voltage	AXL F AI8 1F	2688064
	4 Temperature Inputs, RTD	AXL F RTD4 1H	2688556
	4 Temperature Inputs, UTH	AXL F UTH4 1H	2688598
	8 Temperature Inputs, RTD	AXL F RTD8 1F	2688077
	8 Temperature Inputs, UTH	AXL F UTH8 1F	2688417
 AO Analog Output 4 to 8 channels 54 mm and 35 mm design width	4 Analog Outputs, Current/Voltage	AXL F AO4 1H	2688527
	8 Analog Outputs, Current/Voltage	AXL F AO8 1F	2688080
Special Function Modules			
 FKT Special Function Modules 54 mm and 35 mm design width	1 Interface can be configured as RS-485/RS-422 or RS-232	AXL F RS UNI 1H	2688666
	2 Counter Inputs, 2 Incremental Encoder Inputs	AXL F CNT2 INC2 1F	2688093
	1 SSI Interface, 1 Analog Output	AXL F SSI1 AO1 1H	2688433

Axioline Smart Elements IO

The pluggable Axioline Smart Elements are system-free modules without bus communication. The individual element only supports the I/O function. Only in combination with a backplane, which functions similarly to an adapter, bus communication for the respective I/O system is realised. The Axioline Smart Elements are therefore universal and flexible in use.



Description	Order #
AXL F BP SE4	1088135
AXL F BP SE6	1088136
AXL SE DI16/1	1088127
AXL SE DO16/1	1088129
AXL SE AI4 I 4-20	1088062
AXL SE AI4 U 0-10	1088104
AXL SE AO4 I 4-20	1088123
AXL SE AO4 U 0-10	1088126
AXL SE IOL4	1088132
AXL SE RS485	1088128
AXL SE SC-A	1088134

Enclosure Lights

The enclosure lights from Phoenix Contact provide optimum lighting for your control cabinet, and are easy to install without tools. In particular, the lower third of the control cabinet is ideally lit via a high-quality lens and prismatic reflector. Choose the lights tailored to your needs from two performance classes and a particularly flexible product range.

Class 409 PLD Enclosure Lights		
Model View		
Type	PLD E 409 W 350	PLD E 409 W 350 MS
Order #	1319569	1319573
Dimensions L x W x H	350 mm x 30 mm x 40 mm	350 mm x 30 mm x 40 mm
Luminous Flux	700 lm (Net Luminous Flux)	700lm (Net Luminous Flux)
Protection Class	II	II
Power Consumption	6 W	6 W
Motion Sensor	No	Yes

Advantages

- Optimum illumination of the entire control cabinet thanks to high-quality optics
- Worldwide 400-class application possibilities thanks to wide-range power supply
- UL approval also enables use in the North American market
- The 400-class push-in connection enables time savings during cabling
- The long LED service life eliminates maintenance work and replacing lights

Class 400 PLD enclosure lights

The enclosure lights of the 400 class are characterised by optimum lighting of the control cabinet interior, even in the lower area, thanks to high-quality optics. The wide range supply of 24 to 240 V AC/DC enables worldwide use. The push-in connection technology guarantees the quick and easy installation of the lights.

The light can be swiveled in increments and the delivery includes both screw and magnet fastening mounting options, providing a high degree of flexibility. This is also the case in terms of controlling the lights. You have the choice between a version with an integrated motion sensor or with a connection to a door position switch.



Resulting Phoenix Contact part number	How many hours of operation do you require?	What level of protection is needed?
What size screen do you need?	What type of touch functionality do you require?	What kind of special approvals are needed?
What resolution is required?	What type of processing power is needed?	
What is the minimum brightness required?	What temperature range is needed?	

HMI's for HTML5 Applications

Model View						
Designation	BWP 2043W	BWP 2070W	BWP2102W	BWP 4070W/P	BWP 4101W/P	BWP 4120W/P
Order #	1060549	1060632	1060630	1065546 (Configurable Product)		
Display (in cm)	10.92 (4.3 inches)	17.8 (7 inches)	26.4 (10.2 inches)	17.78 (7 inches)	25.65 (10.1 inches)	30.73 (12.1 inches)
Colours	262,144			16.7 million		
Resolution (W x H in pixels)	480 x 272 (WQVGA)	800 x 480 (WVGA)	1024 x 600 (WVGA)	1280 x 800 (WXGA)		
Brightness (in cd/m²)	300			400	850	320
Backlight (MTTF in h)	20,000			50,000		
Touch Technology	Polyester, Analog Resistive			Projective-Capacitive (PCAP)		
Processor	Cortex®-A9 (i.MX6 Solo)			ARM® Cortex®-A53, 4x 1.2 GHz		
Temperature Range	Operation: 0°C to +50°C Storage: -20°C to +85°C			Operation: 0°C to +50°C Storage: -20°C to +85°C		
Degree of Protection (Front/Back)	IP65/IP20			IP65/IP20		
Approvals	UL/cUL/Class I, Div. 2			UL/cUL, Class I, Div. 2, NEMA 4X		

HMI's for Standard Applications

Model View								
Designation	BTP 2043	BTP 2070W	BTP2102W	TP 3070W/P	TP 3090W/P	TP 3120W/P	TP 3156W/P	TP 3185W/P
Order #	1050387	1046666	1046667	2403459	2403460	2403461	2403462	2403862
Display (in cm)	10.92 (4.3 inches)	17.8 (7 inches)	26.4 (10.2 inches)	17.78 (7 inches)	22.68 (9 inches)	30.73 (12.1 inches)	39.62 (15.6 inches)	47.00 (18.5 inches)
Colours	262,144			16.77 Million				
Resolution (w x h in pixels)	480 x 272 (WQVGA)	800 x 480 (WVGA)		800 x 480 (WVGA)		1280 x 800 (WXGA)	1366 x 768 (WXGA)	
Brightness (in cd/m ²)	300			400	800	320		240
Backlight (MTTF in h)	20,000			40,000	70,000	50,000	70,000	50,000
Touch Technology	Polyester, Analog Resistive			Projective-Capacitive (PCAP)				
Processor	ARM®9 i.MX28, 454 MHz			ARM® Cortex®-A8, 1 GHz, Real-Time Clock (with battery backup)				
Temperature Range	Operation: 0°C to +50°C, Storage: -20°C to +85°C			Operation: -0°C to +50°C, Storage: -25°C to +70°C				
Degree of Protection (Front/Back)	IP66/IP20			IP65/IP20				
Approvals	UL/cUL/Class I, Div. 2			UL/cUL, Class I, Div. 2, NEMA 4X				

Safety Relays



Safety switch

Use our non-contact safety switches with RFID technology for intelligent safety door and position monitoring.




Safety relay modules

If you require just a small number of safety functions, you can choose from our large range of safety relays, safe signal conditioners, and safe motor starters.



Configurable safety systems

The PSRmodular configurable safety system is a flexible safety solution for monitoring your machine or system.



Safe I/Os

Integrate functional safety into your existing network, whether in the control cabinet or in the field. With SafetyBridge Technology, the safety function is processed directly in the I/O modules.



Safe control technology

With our safe high-performance controllers, you can integrate reliable functional safety into PROFIsafe networks for applications with special demands on safety and availability.



Safe power supplies

Our high-performance QUINT POWER power supplies ensure superior availability of your system and satisfy all functional safety requirements.

	Emergency stop		Solenoid switch		Start/restart		Changeover contact
	Safety door switch, mechanical		Two-hand function		Enabling current path / N/O contact		Contact with dropout delay
	Light grid		Transponder switch		N/C contact		

PSRmini: Highly compact safety relays for machine building

Type	Applications							Output contacts				Safety approvals		Width	Order #	
												PL in accordance with EN ISO 13849-1	SILCL in accordance with EN 62061	In mm	Screw connection	Push-in connection
PSR-MS20 ¹⁾ 24 V DC	●	●	—	●	—	—	A	1	—	—	1	c ⁶⁾	1 ⁴⁾	6.8	2904950	—
PSR-MS25 ¹⁾ 24 V DC	●	●	—	●	—	—	M	1	—	—	1	c ⁶⁾	1 ⁴⁾	6.8	2904951	—
PSR-MS40 ³⁾ 24 V DC	●	●	—	—	—	●	A	1	—	—	1	e	3	6.8	2904954	—
PSR-MS60 ³⁾ 24 V DC	●	●	●	●	—	● ¹⁰⁾	A	2	—	—	—	e	3	6.8	2904958	—
PSR-MC32 24...230 V DC	●	●	●	●	—	● ¹⁰⁾	A/M	3	—	1	—	e	3	22.5	2700524	—

PSRclassic: Conventional safety relays for machine building

												PL in accordance with EN ISO 13849-1	SILCL in accordance with EN 62061	In mm	Screw connection	Push-in connection
PSR-ESA2-B 24 V AC/DC	●	●	—	—	—	—	A	4	—	1	—	c ²⁾	1 ²⁾	—	2963802	296354
PSR-ESAM4/3X1-B Voltage variants	●	●	—	—	—	—	A/M	3	—	1	—	e	3	—	See catalogue for ordering data	
PSR-ESL4 ¹⁾ 24 V AC/DC	●	●	●	—	—	●	A/M	3	—	1	—	e	3	—	2981059	2981062
PSR-THC4 ³⁾ 24 V AC/DC	—	●	—	—	●	—	A	2	—	1	—	e	3	—	2963721	2963983
PSR-URM4 42 to 230 V AC/DC	Contact extension							4	—	2	—	e ³⁾	3 ³⁾	—	2702924	2702925
PSR-URM4 24 V AC/DC	Contact extension							5	—	2	—	e ³⁾	3 ³⁾	—	2963734	2964005

Safety Relays

 Emergency stop	 Solenoid switch	 Start/Restart	 Changeover contact
 Safety door switch, mechanical	 Two-hand function	 Enabling current path/ N/O contact	 Contact with dropout delay
 Light grid	 Transponder switch	 N/C contact	

PSRmultifunction: Multifunctional Safety Relays																
Type	Applications							Output Contacts		Safety Approvals		Width	Order #			
										PL in Accordance with EN ISO 13849-1	SILCL in Accordance with EN 62061	In mm	Screw Connection	Spring-Cage Connection	Push-In Connection	
PSR-MXF1 24 V DC	●	●	—	—	—	—	A/M	4	2	e	3	—	2902725	2902726	2903253	
PSR-MXF2 24 V DC	●	●	—	●	—	—	A/M	4	2	e	3	—	2903254	2903255	2903256	
PSR-MXF3 24 V DC	●	●	●	—	—	●	A/M	4	2	e	3	—	2903257	2903258	2903259	

PSRmini: Highly compact,safe coupling relays for the process industry															
Type	Applications	Output Contacts			Diagnostics/Proof Test				Safety Approvals				Width	Order #	
	Highly compact, safe coupling relays for failsafe controllers				Visual via LED	Active Error Acknowledgment via A1 ²⁾	Measurement on the Device	Self-Monitoring with Interlocking	SIL in Accordance with IEC 61508 / 61511	SIL in Accordance with IEC 50156	ATEX / IECEx / Class I Zone 2	G3 in Accordance with ANSI / ISA-S71.04	GL	In mm	Screw Connection
PSR-PS20 24 V DC	For safety-related shutdown (ESD)	1	1	1	●	●	●	—	3	3	●	●	●	6.8	2700356
PSR-PS21 24 V DC		1	1	1	●	●	●	—	2	2	●	●	●	6.8	2700357
PSR-PS23 24 V DC		1	1	—	●	—	●	—	3	3	●	●	●	6.8	2702663

PSRclassic: Classic,safe coupling relays for the process industry															
	Highly compact, safe coupling relays for failsafe controllers				Visual via LED	Active Error Acknowledgment via A1 ²⁾	Measurement on the Device	Self-Monitoring with Interlocking	SIL in accordance with IEC 61508 / 61511	SIL in Accordance with IEC 50156	ATEX / IECEx / Class I Zone 2	G3 in Accordance with ANSI / ISA-S71.04	GL	In mm	Screw Connection
PSR-FSP 24 V DC	For safety-related shutdown (ESD)	1	1	–	–	–	●	–	3	3	–	–	●	17.5	2981978
PSR-FSP/2x1 24 V DC		2	1	–	–	–	●	–	3	3	–	–	●	17.5	2986960

Force-guided Contact Relays

■ What application or load are you switching: electromechanical or solid state?	■ What connection technology: screw terminal (UT) or push-in (PT)?
■ What is the input-coil voltage: DC or AC?	■ Resulting Phoenix Contact part number
■ What is your output current (Amps)? (Ratings are for resistive loads)	■ What accessories are needed?
■ How many sets of contacts do you need: SPDT, DPDT, etc.?	

Electromechanical Relays					
Input-Coil Voltage	Output Current	Sets of Contacts	Termination Style	Description	Order #
24 V DC	6 A	DPDT - 14 mm	Screw	PLC-RSC- 24DC/2X21/FG	2910535
			Push-In	PLC-RPT- 24DC/2X21/FG	2910537
RIF Slimline Relays					
24 V DC	6 A	DPDT - 14 mm	Screw	RIF-1-RSC-LDP-24DC/2X21/FG	2909848
			Push-In	RIF-1-RPT-LDP-24DC/2X21/FG	2908215

Replacement Parts				
Mechanical Relays				
Input-Coil Voltage	Output Current	Sets of Contacts	Description	Order #
24 V DC	6 A	DPDT - 14 mm	REL-MR-24 DC/21-21	2961192

PSRswitch: Non-Contact Safety Switches					
Type	Description	Coding Type/Function	Connection Technology		
			Screw Connection	Spring-Cage Connection	M12 Connection
PSR-CT-F-SEN-1-8	Safety Sensor	Fixcode: The sensor accepts a single actuator. This actuator is taught in by the user during commissioning. It is not possible to teach in further actuators.	—	—	2702976
PSR-CT-C-SEN-1-8		Unicode: The sensor accepts one actuator. The actuator is taught in by the user during commissioning. It is possible to teach in an unlimited number of further actuators in succession. Previously taught in actuators are blocked by the sensor. They can no longer be used.	—	—	2702972
PSR-CT-M-SEN-1-8		Multicode: The sensor accepts all actuators. It is not necessary to teach them in during commissioning.	—	—	2702975
PSR-CT-C-ACT	Actuator	Coded, suitable for all sensor coding types	—	—	2702973
PSR-MC42	Safety Relay	With integrated IO-Link interface	2702901	2702902	—
SAC-8PY-M/2XF BK 1-PSR	Y Distributor	Type 1 for series connection of PSR-CT safety circuits	—	—	1054338
SAC-8PY-M/2XF BK 2-PSR		Type 2 for manual startup behaviour	—	—	1054339
SAC-8PY-M/2XF BK 3-PSR		Type 3 for integrated diagnostics via signal contact with PSR-CT safety circuits	—	—	1054341
SAC-5P-M12MS BK BR 1-2-4	Bridge Plug	Dummy plug for every sensor circuit	—	—	1054366

Functional safety

Safe I/Os

With our I/O systems, you can integrate functional safety easily and reliably into your favoured network, whether in the control cabinet or in the field. Use our safe PROFIsafe I/O modules as usual in combination with your safety controller in the PROFINET or PROFIBUS environment. As an alternative, SafetyBridge Technology allows you to realise decentralised safety solutions easily and regardless of network, without the need for a safety controller.




Configurable Safety Systems

With configurable safety systems from Phoenix Contact, you can adapt your safety technology so it is tailored to your needs. Use our high-performance basic modules as a stand-alone solution or extend the system flexibly with extension modules, including the monitoring of motion and analog value data. Our configurable safety systems combine functionality and flexibility. At the same time, they also close the gap between simple safety relays and programmable safe controllers.



Marking

Order #	Description	Terminal Marking				
		Thermomark Card 2.0	Thermomark Prime	Bluemark ID	Bluemark ID Colour	Topmark Neo
0829484	UCT-TM 3,5	✓	✓	✓	✓	✓
0828734	UCT-TM 5	✓	✓	✓	✓	✓
0828736	UCT-TM 6	✓	✓	✓	✓	✓
0828740	UCT-TM 8	✓	✓	✓	✓	✓
0829142	UCT-TM 10	✓	✓	✓	✓	✓
0829144	UCT-TM 12	✓	✓	✓	✓	✓
0829146	UCT-TM 16	✓	✓	✓	✓	✓
0818108	UC-TM 5			✓	✓	
0818085	UC-TM 6			✓	✓	
0818072	UC-TM 8			✓	✓	
0818069	UC-TM 10			✓	✓	
0819194	UC-TM 12			✓	✓	
0819217	UC-TM 16			✓	✓	
0829486	UCT-TMF 3,5	✓	✓	✓	✓	✓
0828744	UCT-TMF 5	✓	✓	✓	✓	✓
0828746	UCT-TMF 6	✓	✓	✓	✓	✓
0828748	UCT-TMF 8	✓	✓	✓	✓	✓
0829204	UCT-TMF 10	✓	✓	✓	✓	✓
0829214	UCT-TMF 12	✓	✓	✓	✓	✓
0829218	UCT-TMF 16	✓	✓	✓	✓	✓
0818153	UC-TMF 5			✓	✓	
0818140	UC-TMF 6			✓	✓	
0818137	UC-TMF 8			✓	✓	
0818124	UC-TMF 10			✓	✓	
0819233	UC-TMF 12			✓	✓	
0819262	UC-TMF 16			✓	✓	



Wire/Cable Marking Labels						
0801430	UCT-WMT (10X4)	✓	✓	✓	✓	✓
0801438	UCT-WMT (12X4)	✓	✓	✓	✓	✓
0801446	UCT-WMT (15X4)	✓	✓	✓	✓	✓
0801462	UCT-WMT (18X4)	✓	✓	✓	✓	✓
0801453	UCT-WMT (23X4)	✓	✓	✓	✓	✓
0801422	UCT-WMT (30X4)	✓	✓	✓	✓	✓
0819372	UC-WMT (10X4)			✓	✓	
0823517	UC-WMT (12X4)			✓	✓	
0819398	UC-WMT (15X4)			✓	✓	
0820293	UC-WMT (18X4)			✓	✓	
0819411	UC-WMT (23X4)			✓	✓	
0801422	UC-WMT (30X4)			✓	✓	
0828765	US-WMT (10X4)	✓	✓	✓	✓	
0828766	US-WMT (12X4)	✓	✓	✓	✓	
0828767	US-WMT (15X4)	✓	✓	✓	✓	
0828768	US-WMT (18X4)	✓	✓	✓	✓	
0828769	US-WMT (23X4)	✓	✓	✓	✓	
0828770	US-WMT (30X4)	✓	✓	✓	✓	



Wire/Cable Sleeves						
Conductor Diameter	10 mm	12 mm	15 mm	18 mm	23 mm	30 mm
0.6-1.2 mm	PATG 0/10 1013795	PATG 0/12 0827076	PATG 0/15 1013740	PATG 0/18 0820507	PATG 0/23 0828046	
1.5-2.5 mm	PATG 1/10 1013805	PATG 1/12 0827077	PATG 1/15 1013025	PATG 1/18 0820510	PATG 1/23 1013847	PATG 1/30 0822440
2-4 mm	PATG 2/10 1013818	PATG 2/12 0827078	PATG 2/15 1013038	PATG 2/18 0820523	PATG 2/23 1013850	PATG 2/30 0822453
4-7 mm	PATG 3/10 1013821	PATG 3/12 0827079	PATG 3/15 1013041	PATG 3/18 0820536	PATG 3/23 1013863	PATG 3/30 0822466
6-10 mm		PATG 4/12 0827080	PATG 4/15 1013054	PATG 4/18 0820549	PATG 4/23 0808011	PATG 4/30 0822479
10-14 mm			PATG 5/15 1013067	PATG 5/18 088059	PATG 5/23 0808024	PATG 5/30 0822482
14-22 mm			PATG 6/15 1013070	PATG 6/18 0828062	PATG 6/23 0808037	
22-30 mm			PATG 7/15 1013083		PATG 7/23 0808040	
30-35 mm			PATG 8/15 1013096		PATG 8/23 0808053	
35-45 mm			PATG 9/15 1013106			



Printing

■	How to select a printer			
■	What are you marking and with what material: CARD or ROLL material?			
■	How many labels do you need to print: volume?			
■	Do you need a desktop or mobile printer: size?			
NOTE: Card printers require magazine that matches the card material				
Printing Solutions				
Material	Volume	Size	Description	Order #
Card and Sheet	Manual Feed	Desktop	THERMOMARK CARD 2.0	1085267
Card and Sheet	Manual Feed	Desktop and Portable	THERMOMARK PRIME	5148888
Roll	< 50,000 Labels/yr.	Desktop	THERMOMARK ROLL 2.0	1085260
Roll	> 50,000 Labels/yr.	Large/Desktop	THERMOMARK ROLLMASTER	0804501
Cartridge	Low	Handheld	THERMOMARK GO.K	1184146
Cartridge	Low	Handheld	THERMOMARK GO.K SET	1184148
Cartridge	Low	Portable	THERMOMARK GO	1090747
Cartridge	Low	Portable	THERMOMARK GO SET	1221548



Print Ribbon						
Printer	Print Materials	Width (mm)	Length (mm)	Description	Order #	
Thermomark Roll 2.0	TML..., WML..., WML HF..., WML-FLAG..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP... and PMM...	110	300	THERMOMARK-RIBBON 110	5145384	
	WMS... and WMS-2 HF...	64	300	THERMOMARK-RIBBON 64-WMSU	801360	
	WMS... and WMS-2 HF...	110	300	THERMOMARK-RIBBON 110-WMSU	801358	
	WMTB HF..., WMS-2 HF..., TMT..., EMT..., EMLF..., PML...	110	300	THERMOMARK-RIBBON 110-WMTB HF	5148007	
	EML-HT...	110	300	THERMOMARK-RIBBON 110-EML-HT	800342	
Thermomark Card 2.0	UCT..., US..., and UM...	110	300	THERMOMARK-RIBBON 110-TC	801371	
	UCT..., US..., and UM...	110	70	TMP-RIBBON 110 BK 100	803374	
Thermomark Prime	US(2)-TM(F)..., US-TM(F)L..., US-WMTB..., US-EML..., US-EML(S)P..., US-EMLP-HA..., US-EM(S)P..., US-EML-RS...	110	60	TMP-RIBBON 110 BK 101	803714	



Print Ribbon					
Printer	Description	Width/Diameter	Length (m)	Description	Order #
Thermomark GO and Thermomark GO.K	Shrink Sleeve, White, Black Printing, 3:1 ratio	Cable Diameter 1-3.2 mm	1.8m	MM-WMS 3,2 (EX5)R C1 WH/BK	803923
		Cable Diameter 1.6-4.8 mm		MM-WMS 4,8 (EX9)R C1 WH/BK	803924
		Cable Diameter 2.1-6.4 mm		MM-WMS 6,4 (EX10)R C1 WH/BK	803925
		Cable Diameter 3.2-9.5 mm		MM-WMS 9,5 (EX16)R C1 WH/BK	803926
	Fabric Label, White, Black Printing, Adhesive	10 mm	6m	MM-EMLC (EX10)R C1 WH/BK	803933
		18 mm		MM-EMLC (EX18)R C1 WH/BK	803936
	Label, White, Black Printing, Adhesive	10 mm	8m	MM-EML (EX10)R C1 WH/BK	803970
		12 mm		MM-EML (EX12)R C1 WH/BK	803971
		18 mm		MM-EML (EX18)R C1 WH/BK	803972
		24 mm		MM-EML (EX24)R C1 WH/BK	803973
	Label, White, Black Printing, Highly Flexible, Adhesive	10 mm	8m	MM-EMLF (EX10)R C1 WH/BK	803937
		12 mm		MM-EMLF (EX12)R C1 WH/BK	803938
		18 mm		MM-EMLF (EX18)R C1 WH/BK	803939
		24 mm		MM-EMLF (EX24)R C1 WH/BK	803940
	Label, White, Black Printing, Highly Flexible, Adhesive	10 mm	8m	MM-EMLF (EX10)R C1 YE/BK	803941
		12 mm		MM-EMLF (EX12)R C1 YE/BK	803942
		18 mm		MM-EMLF (EX18)R C1 YE/BK	803943
		24 mm		MM-EMLF (EX24)R C1 YE/BK	803944

Shopfloor Productivity

Installation

What do you use to cut conductors, cables, and cable binders?					Do you ferrule wires? What size wire are you crimping?	
What do you use to strip wires and multi-conductor cables?					What tools do you need to terminate conductors?	
Installation						
Cut	Function	Conductor Size		Description	Order #	
	Cable-Cutting Tool	Up to 35 mm²		CUTFOX 12	1212128	
	Cable-Cutting Tool	Up to 50 mm²		CUTFOX 18	1212129	
	Diagonal Cutter	For hard and soft wires from 0.2-11 mm diameter		CUTFOX S VDE	1212207	
	Cable Tie Tool	For plastic cable ties 2.2-4.8 mm wide, up to 1.6 mm thick		UNIFOX-CT 4,8P	1212609	
	Cable Tie Tool	For steel cable ties up to 7.9 mm wide, up to 0.3 mm thick		UNIFOX-CT 7,9M	1212610	
Strip	Single conductor					
	Function	Conductor Size	Cable Type	Description	Order #	
	Self-Adjusting Stripping Tool	0.1-4 mm²	Especially for rubber and silicone insulation	WIREFOX 4	1212156	
	Self-Adjusting Stripping Tool	1.5-6 mm²	Especially for cables protected against short circuits and ground leakages	WIREFOX 6SC	1212158	
	Self-Adjusting Stripping Tool	0.02-10 mm²		WIREFOX 10	1212150	
	Multi-Conductor					
	Strips Sensor/Actuator Cables	Diameter 4.4-7 mm	Sensor/Actuator cables with PUR and PVC insulation	WIREFOX SAC	1212623	
	Strips Multi-Conductor Cables	Diameter 2.5-11 mm, up to 1 mm insulation	Multicore signal, control, and fiberglass wires	WIREFOX-D 11	1212160	
	Strips Large, Multi-Conductor Cables	Diameter 4.5-40 mm, up to 4.5 mm insulation		WIREFOX-D 40	1212161	
Crimp	Crimping Tools					
	Conductor Size		Crimp Shape	Description	Order #	
	0.14-6 mm²		Square	CRIMPFOX CENTRUS 6S	1213144	
	0.14-10 mm²		Square	CRIMPFOX CENTRUS 10S	1213154	
	0.14-10 mm²		Trapezoid	CRIMPFOX DUO 10	1031721	
Assemble	Assembling Tools					
	Tool			Description	Order #	
	Torque Screw Driver, Manual, Accuracy as per EN ISO 6789 Standard, Adjustable from 0.3 - 1.2 Nm			TSD-M 1,2NM	1212224	
	Torque Screw Driver, Manual, Accuracy as per EN ISO 6789 Standard, Adjustable from 1.2 - 3 Nm			TSD-M 3NM	1212225	
	Torque Screw Driver, Manual, Accuracy as per EN ISO 6789 Standard, Adjustable from 3 - 6 Nm			TSD-M 6NM	1212226	
	Micro Screwdriver, Flat Blade, Size: 0.4 x 2.0 mm x 60 mm Long Shaft, 2-Component Grip, with Non-Slip Grip and Twist Cap			SZS 0,4X2,0	1205202	
	Actuation Tool, for ST Terminal Blocks, also Suitable for Use as a Bladed Screwdriver, Size: 0.6 x 3.5 x 100 mm, 2-Component Grip, with Non-Slip Grip			SZF 1-0,6X3,5	1204517	
	Bit Screwdriver Set with Quick-Action Chuck, 17 Pieces of 89 mm Length Slotted, Crosshead (PZ and PH), Hex and Torx® bits			SF-M SET	1212543	
	Bit Screwdriver Set with Quick-Action Chuck, 17 Pieces of 89 mm Length Slotted, Crosshead, Hex and Torx® bits			SF-M SET 2	1212756	
	Cordless Screwdriver in Case, Including Battery, Charging Device 100-240 V, 2 bits, Two-Speed Gearbox, Forward/Reverse Running and 16-Stage Clutch Up to 450 rpm, Hexagonal Fast Connection.			SF-ASD 16 SET	1200295	
	Combination Pliers, Notched Gripping Surface, VDE 1000 V AC/1500 V DC Tested, Size: 180 mm			UNIFOX-C VDE	1212202	
	Offset Screwdriver Set, Hex, Metric, SW 1.5; 2; 2.5; 3; 4; 5; 6; 8; and 10 mm, with Ball Head, Matt Chrome-Plated, 9-art, in Practical Holder			SF-LHEX SET	1212544	
	Tape measure, 5 m			MEASURING TAPE 5M	1200298	
	Actuation Tool, for all 2.5 mm² - 4.0 mm² spring cages			ST-BW	1207608	
	Needle-Nose Pliers with Blade, Notched Grip Area, VDE 1000 V AC/1500 V DC Tested			UNIFOX-P VDE	1212701	
	Screwdrivers 7 piece, VDE-insulated, Flat blade 0.6 x 3.5, 0.8 x 4.0, 1.0 x 5.5; Phillips PH1, PH2; Pozidriv® + bladed PZSL 1, PZSL 2			SF-SL/PH/PZ-SL SET S-VDE	1212701	
Ferrules	Bootlace Ferrules					
	Size	Colour	Standard Pack	Description	Order #	
	0.5 x 8 mm	White	100	AI 0,5-8 WH	3200014	
	0.75 x 8 mm	Blue	100	AI 0,75-8 BU	3200027	
	0.75 x 12 mm	Grey	100	AI 0,75-12 GY	3200849	
	1 x 8 mm	Red	100	AI 1-8 RD	3200030	
	1 x 12 mm	Red	100	AI 1-12 RD	3200674	
	1.5 x 8 mm	Black	100	AI 1,5-8 BK	3200043	
	1.5 x 18 mm	Black	100	AI 1,5-18 BK	3200056	
	2.5 x 8 mm	Blue	100	AI 2,5-8 BU	3200522	
	2.5 x 8 mm	Grey	100	AI 2,5-8 GY	3200069	
	2.5 x 18 mm	Blue	100	AI 2,5-18 BU	3200580	
	4 x 10 mm	Grey	100	AI 4-10 GY	3200535	
	4 x 18 mm	Grey	100	AI 4-18 GY	3200593	
	6 x 12 mm	Green	100	AI 6-12 GN	3200108	
	6 x 18 mm	Green	100	AI 6-18 GN	3200111	
	Twin 0.5 x 8 mm	White	100	AI-TWIN 2X 0,5-8 WH	3200933	
	Twin 0.75 x 12 mm	Grey	100	AI-TWIN 2X 0,75-10 GY	3200975	
	Twin 1 x 10 mm	Red	100	AI-TWIN 2X 1-10 RD	3200988	
	Twin 1.5 x 12 mm	Black	100	AI-TWIN 2X 1,5-12 BK	3200991	
	Twin 2.5 x 13 mm	Blue	100	AI-TWIN 2X 2,5-13 BU	3200878	
	0.5 x 8 mm	White	1000	AI 0,5-8 WH-B	3201369	
	0.75 x 8 mm	Blue	1000	AI 0,75-8 BU-B	3201547	
	0.75 x 8 mm	Grey	1000	AI 0,75-8 GY-B	3201372	
	1 x 8 mm	Red	1000	AI 1-8 RD-B	3201385	
	1.5 x 8 mm	Black	1000	AI 1,5-8 BK-B	3201398	
	2.5 x 8 mm	Blue	500	AI 2,5-8 BU-B	3201408	
	2.5 x 8 mm	Grey	500	AI 2,5-8 GY-B	3201550	

Cable Duct and Din Rail

Cable Duct						
Height (mm)	Width (mm)	Length (m)	Colour	Quantity Per Box	Description	Order #
25 mm	25 mm	2m	Gray	25	CD 25x25	3240187
40 mm	25 mm	2m	Gray	24	CD 25x40	3240188
60 mm	25 mm	2m	Gray	15	CD 25x60	3240191
80 mm	25 mm	2m	Gray	10	CD 25x80	3240191
40 mm	40 mm	2m	Gray	25	CD 40x40	3240189
60 mm	40 mm	2m	Gray	20	CD 40x60	3240192
80 mm	40 mm	2m	Gray	10	CD 40x80	3240198
100 mm	40 mm	2m	Gray	10	CD 40x100	3240294
40 mm	60 mm	2m	Gray	20	CD 60x40	3240190
60 mm	60 mm	2m	Gray	12	CD 60x60	3240193
80 mm	60 mm	2m	Gray	10	CD 60x80	3240199
100 mm	60 mm	2m	Gray	8	CD 60x100	3240263
60 mm	80 mm	2m	Gray	10	CD 80x60	3240194
80 mm	80 mm	2m	Gray	6	CD 80x80	3240200
100 mm	80 mm	2m	Gray	8	CD 80x100	3240264
60 mm	100 mm	2m	Gray	8	CD 100x60	3240195
80 mm	100 mm	2m	Gray	6	CD 100x80	3240201
100 mm	100 mm	2m	Gray	6	CD 100x100	3240205



DIN Rail				
Length (m)	Quantity Per Box	Description	Long Description	Order #
2m	10	NS 35/7,5 PERF 2000MM	Steel, Galvanized, Passivated with a Thick Layer	0843103
2m	10	NS 35/7,5 UNPERF 2000MM	Steel, Galvanized, Passivated with a Thick Layer	0843101
2m	10	NS 35/15 PERF 2000MM	Steel, Galvanized, Passivated with a Thick Layer	0843113
2m	10	NS 35/15 UNPERF 2000MM	Steel, Galvanized, Passivated with a Thick Layer	0843112
2m	10	NS 15 PERF 2000MM	Steel, Galvanized, Passivated with a Thick Layer	1401682



DIN Rail Accessories				
Quantity Per Box	Description	Long Description	Order #	
100	NS 35/ 7,5 CAP	DIN Rail End Piece, for DIN Rail NS 35/7.5	1206560	
100	NS 35/ 15 CAP	DIN Rail End Piece, for DIN Rail NS 35/15	1206573	
50	CLIPFIX 35	Quick Mounting End Clamp for NS 35/7,5 DIN Rail or NS 35/15 DIN Rail	3022218	
50	CLIPFIX 35-5	Quick Mounting End Clamp for NS 35/7,5 DIN Rail or NS 35/15 DIN Rail	3022276	
10	E/AL-NS 35	Aluminium End Clamp, for NS35 Fixed with 2 Screws	1201662	
50	E/NS 35 N	End Clamp for NS 35/7,5 DIN Rail or NS 35/15 DIN Rail	0800886	
50	CLIPFIX 15	Quick Mounting End Clamp for NS 15	3022263	

DIN Rail and Cable Duct Cutters		
Description	Long Description	Order #
PPS COMPACT	Profile cutter for cutting standard DIN rails NS 35/7,5 and NS 35/15 to length (see 1105211 for measuring bar)	1104980
PPS COMPACT/ SCALE-SET I/M	Measuring bar version: inches/metric	1105211
PPS BASIC I/M	Profile cutter for cutting standard DIN rails to length, NS 15 / NS 35/7,5 / NS 35/15, and for cutting the NLS-CU 3/10 neutral busbar to length, with inch/metric measuring rail	1207585
PPS STANDARD M	Profile cutter for cutting and stamping holes in standard DIN rails, NS 32 / NS 35/7,5 / NS 35/15, and for cutting the NS 15 and NLS-CU 3/10 neutral busbar to length. Can accommodate 2 stamping bits, with metric measuring rail, delivered without stamping bits	1206175
PPS CLASSIC M	Profile cutter for cutting to length and stamping holes in standard DIN rails, NS 32 / NS 35/7,5 / NS 35/15, and for cutting the NS 15 and NLS-CU 3/10 neutral busbar to length. Can accommodate 2 stamping bits, bits easily exchangeable, with metric measuring rail, delivered without stamping bits	1206243
PPS CD M	Cable duct cutter for burr-free cutting cable ducts and their covers. can be used up to a width of 125 mm	1207569
CUTFOX-CD	Cable duct cutter, for cutting plastic cable ducts, covers, and profiles, 45° limit stop also for bevel cuts, 75 mm cutting length	1212474

PPS BASIC I/M



PPS CD M



CUTFOX-CD



Phoenix Contact's Complete Cabinet Confidence Infomobile

**Power, protect, and connect with
Phoenix Contact, your trusted
partner for cabinet solutions**

Step inside our Complete Cabinet Confidence Infomobile and take part in a virtual control-cabinet experience, plus multiple hands-on product opportunities.

Phoenix Contact is a global market leader in industrial electronics and automation technologies. Our expertise and commitment to innovation across a wide range of industries enable you to build your control cabinet with confidence.

With a focus on cost-effectiveness, quality, flexibility, and performance, Phoenix Contact delivers.

www.phoenixcontact.com.au/confidence



Lifetime Warranty

Choose Phoenix Contact with confidence



**LIFETIME
WARRANTY**

BUILD WITH CONFIDENCE

Phoenix Contact engineers durable and reliable products for your control cabinet. A dedication to quality and innovation, united with our strong commitment to provide customers peace of mind, form the foundation of this exclusive Phoenix Contact warranty program.

For customers participating in our Complete Cabinet Confidence Lifetime Warranty (LW) program, Phoenix Contact Australia will warrant many of our products to be free from defects in workmanship and materials for the lifetime of the product. Registration is required, and certain restrictions apply. Improperly applied or installed products may void warranty. See the complete terms and conditions for full details.

Our goal is to be your most trusted partner in building your control cabinet. We believe that achieving peace of mind should be easy!

Simple Three Step Registration

To assure your Phoenix Contact products are covered under our exclusive Lifetime Warranty, follow these steps:

Step 1: Submit your registration (www.phoenixcontact.com.au/LW).

Step 2: Select and install Phoenix Contact products in accordance with our recommendations.

Step 3: Make sure all electronics are powered and protected with appropriate Phoenix Contact power supplies and surge protection.

For participation in the Phoenix Contact Complete Cabinet Confidence Lifetime Warranty (LW) program, customer registration is required. Certain restrictions apply. Coverage of products in the program is limited to Phoenix Contact products sold in Australia. Improperly applied or installed products may void warranty.

To review the Lifetime Warranty Terms & Conditions, go to: www.phoenixcontact.com.au/LW



Ongoing communication with customers and partners worldwide

Phoenix Contact is a global, market leader based in Germany. Our group is known for its future-oriented components, systems, and solutions in the fields of electrical engineering, electronics, and automation.

With a global network reaching across more than 100 countries and 17,400 employees, we can stay in close contact with our customers, something we believe is essential to success. The wide variety of our innovative products makes it easy for our customers to find future-oriented solutions for multiple applications and industries. We especially focus on the fields of energy, infrastructure, process, and factory automation.



You will find our complete product range at:
www.phoenixcontact.com.au

PHOENIX CONTACT Pty. Ltd.

SYDNEY

Head Office

Unit 7, 2-8 South Street
RYDALMERE NSW 2116

Phone: 1300 786 411

Fax: 1300 723 399

E-mail: customerservice@phoenixcontact.com.au

Website: www.phoenixcontact.com.au

MELBOURNE

Unit 1 8-12 Butler Way
TULLAMARINE 3043 VIC
vicsales@phoenixcontact.com.au

BRISBANE

Unit 9, 56 Lavarack Avenue
EAGLE FARM 4009 QLD
customerservice@phoenixcontact.com.au

ADELAIDE

12B Main Assembly Bldg, Tonsley Park
1284 South Road
TONSLEY SA 5042
customerservice@phoenixcontact.com.au

PERTH

Unit 5, 175 Campbell Street
BELMONT WA 6104
wasaes@phoenixcontact.com.au



**LIFETIME
WARRANTY**

BUILD WITH CONFIDENCE



**PRICE
GUARANTEE**

BUILD WITH CONFIDENCE



**IN-STOCK
GUARANTEE**

BUILD WITH CONFIDENCE



**ESHOP
PLATFORM**

BUILD WITH CONFIDENCE



**INDUSTRY
4.0**

BUILD WITH CONFIDENCE