

# QUINT POWER – Highest system availability due to SFB Technology

**Standard circuit-breakers  
triggered reliably and quickly**



In order to be able to trigger standard circuit-breakers magnetically and quickly the SFB Technology supplies up to six times the nominal current for 15 ms.

## SFB configuration

Observe the following framework conditions for determining the maximum distance between the power supply and load:

- The performance class of the power supply.
- The cross section of the connecting cable.
- The tripping characteristic of the fuse component.



Schematic diagram of the maximum cable length

## Maximum distance between the power supply and load

The distances given in the table are worst-case values and therefore cover the entire tolerance range for the magnetic tripping of circuit breakers. The possible distances are often greater in practice.

## QUINT POWER 24V/5A

Maximum distance l [m] with device circuit breaker		Conductor cross section					
		A [mm <sup>2</sup> ]	0.75	1.0	1.5	2.5	
		AWG	18	(17)	16	14	
Phoenix Contact		CB TM1 1A SFB P		27	36	54	91
		CB TM1 2A SFB P		10	13	20	34

## QUINT POWER 24V/10A

Maximum distance l [m] with device circuit breaker		Conductor cross section					
		A [mm <sup>2</sup> ]	0.75	1.0	1.5	2.5	
		AWG	18	(17)	16	14	
Phoenix Contact		CM TM1 1A SFB P		27	36	54	91
		CM TM1 2A SFB P		18	25	37	63
		CM TM1 3A SFB P		11	15	22	38
		CM TM1 4A SFB P		6	8	13	22
		CM TM1 5A SFB P		4	5	8	14

## QUINT POWER 24V/20A

Maximum distance l [m] with device circuit breaker		Conductor cross section					
		A [mm <sup>2</sup> ]	0.75	1.0	1.5	2.5	4.0
		AWG	18	(17)	16	14	10
Phoenix Contact	CM TM1 1A SFB P	27	36	54	91	<130	<200
	CM TM1 2A SFB P	18	25	37	63	<100	<140
	CM TM1 3A SFB P	13	18	27	46	73	<100
	CM TM1 4A SFB P	10	14	21	35	57	86
	CM TM1 5A SFB P	8	11	17	29	46	70
	CM TM1 6A SFB P	6	8	12	20	32	48
	CM TM1 8A SFB P	--	5	7	12	20	30
	CM TM1 10A SFB P	--	3	4	8	13	19

## QUINT POWER 24V/40A

Maximum distance l [m] with device circuit breaker	Conductor cross section							
	A [mm <sup>2</sup> ]	0.75	1.0	1.5	2.5	4.0	6.0	10
	AWG	18	18	16	14	12	10	8
Phoenix Contact	CM TM1 1A SFB P	27	36	54	91	<130	<200	<300
	CM TM1 2A SFB P	18	25	37	63	<100	<140	<220
	CM TM1 3A SFB P	13	18	27	46	73	<100	<160
	CM TM1 4A SFB P	10	14	21	35	57	86	<140
	CM TM1 5A SFB P	8	11	17	29	46	70	<100
	CM TM1 6A SFB P	7	9	14	24	39	58	97
	CM TM1 8A SFB P	--	7	11	19	31	46	78
	CM TM1 10A SFB P	--	5	7	12	20	30	51
	CM TM1 12A SFB P	--	--	5	9	14	21	36
	CM TM1 16A SFB P	--	--	3	5	8	12	20

### Thermomagnetic device circuit breaker, type: Phoenix Contact CB TM1 SFB

The cable lengths determined are based on the following parameters:

Tripping: magnetic

DC correction factor (0 Hz): Phoenix Contact = 1.0

Characteristic: C

Characteristic C (5 to 10 times the rated current) x correction factor

+20 °C

Ambient temperature:

Internal resistance R<sub>i</sub> of the device circuit breaker: taken into consideration

Comments:

In addition to the short-circuit current, the power supply unit also supplies half the nominal current for load paths connected in parallel.