






Help for choosing the QUINT CAP

Select your QUINT CAP with integrated capacity here.



Energy storage devices


| | QUINT CAP* | | | |
|--|---|---|--|---|
| | | USB | USB | |
|  |  |  |  |  |
| Input | 22.5 V DC ... 30 V DC | 22.5 V DC ... 30 V DC | 22.5 V DC ... 30 V DC | 22.5 V DC ... 30 V DC |
| W x H x D in mm | 85 x 102.5 x 90 | 94 x 130 x 125 | 118 x 130 x 125 | 244 x 130 x 125 |

| | 24 V / 3.8 A | 24 V / 5 A | 24 V / 10 A | 24 V / 20 A * |
|-------------|---|-----------------------|------------------------|---|
| Type | QUINT4-CAP/24DC/3.8/1KJ/PT | QUINT4-CAP/24DC/5/4KJ | QUINT4-CAP/24DC/10/8KJ | QUINT4-CAP/24DC/20/16KJ/USB |
| Item number | 2320526 | 2320539 | 2320571 | 1065635 |
| | | | | 24 V / 20 A / PN <small>new</small> |
| Type | | | | QUINT4-CAP/24DC/20/16KJ/PN |
| Item number | | | | 1076860 |
| | | | | 24 V / 20 A / EIP <small>new</small> |
| Type | | | | QUINT4-CAP/24DC/20/16KJ/EIP |
| Item number | | | | 1076861 |
| | | | | 24 V / 20 A / EC <small>new</small> |
| Type | | | | QUINT4-CAP/24DC/20/16KJ/EC |
| Item number | | | | 1076858 |
| Information | Energy storage device based on maintenance-free double-layer capacitors | | | |

*1) These devices support SFB Technology.

Buffer times for QUINT CAP:

Example: 5 A is to be buffered for 1 minute.



The data is based on an ambient temperature of +25°C.