


Standardized potential distribution

With the bridges of the CLIPLINE complete system

FBS plug-in bridges and accessories

FBS plug-in bridges


The standard FBS plug-in bridges are used for easy potential distribution between terminal blocks with the same pitch. The plug-in bridges are available with up to 50 contact tabs, enabling you to connect up to 50 potentials together.



The FBS bridges can be inserted easily into the bridge shaft. The bridges sit firmly in the function slot thanks to the clever clamping technology.




If shorter plug-in bridges are required, the FBS bridges can easily be cut to length using a cutting tool (CUTFOX 18). The range also includes shorter plug-in bridges as an option.




After shortening the plug-in bridges, protective caps (FBSC) can be used to cover the live metal.



The CUTFOX-FBS can be used to cut off individual contact tabs to create non-adjacent bridges.



The non-adjacent bridges enable potential distribution between terminal blocks that are not adjacent to each other. The marking groove can be traced with the B-STIFT marker pen for visual identification.



To remove the plug-in bridges from the function slot, simply insert a screwdriver into the groove on the side and lever the bridge out.

Product overview FBS plug-in bridges

Pitch width: 3.5 mm / max. no-load current: 17.5 A						
Terminal blocks	FBS bridges (red)		FBS bridges (blue)		FBS bridges (gray)	
	Type	Item no.	Type	Item no.	Type	Item no.
XT 1,5... PT 1,5/S... PTS 1,5... MPT 1,5 MPT 1,5/S... MUT 1.5	FBS 2-3,5	3213014	FBS 2-3.5 BU	3213086	FBS 2-3.5 GY	3213153
	FBS 3-3,5	3213027	FBS 3-3.5 BU	3213099	FBS 3-3.5 GY	3213167
	FBS 4-3,5	3213030	FBS 4-3.5 BU	3213109	FBS 4-3.5 GY	3213180
	FBS 5-3,5	3213043	FBS 5-3.5 BU	3213112	FBS 5-3.5 GY	3213183
	FBS 10-3,5	3213056	FBS 10-3.5 BU	3213125	FBS 10-3.5 GY	3213196
	FBS 20-3,5	3213069	FBS 20-3.5 BU	3213138	FBS 20-3.5 GY	3213206
	FBS 50-3,5	3000706	FBS 50-3.5 BU	3000708	FBS 50-3.5 GY	3000707
Pitch width: 4.2 mm / max. no-load current: 17.5 A						
Terminal blocks	FBS bridges (red)		FBS bridges (blue)		FBS bridges (gray)	
	Type	Item no.	Type	Item no.	Type	Item no.
UT 1.5... ST 1.5...	FBS 2-4	3030116	FBS 2-4 BU	3030117	FBS 2-4 GY	3030118
	FBS 3-4	3030129	FBS 3-4 BU	3030130	FBS 3-4 GY	3030131
	FBS 4-4	3030132	FBS 4-4 BU	3030133	FBS 4-4 GY	3030134
	FBS 5-4	3030145	FBS 5-4 BU	3030146	FBS 5-4 GY	3030147
	FBS 10-4	3030158	FBS 10-4 BU	3036851		
	FBS 20-4	3030352	FBS 20-4 BU	3030353		
Pitch width: 5.2 mm / max. no-load current: 24 A						
Terminal blocks	FBS bridges (red)		FBS bridges (blue)		FBS bridges (gray)	
	Type	Item no.	Type	Item no.	Type	Item no.
XT 2,5... PT(V) 2,5... PTS 2,5... MPT 2,5... UT 2,5... MUT 2,5... ST 2,5... STS 2,5...	FBS 2-5	3030161	FBS 2-5 BU	3036877	FBS 2-5 GY	3038969
	FBS 3-5	3030174	FBS 3-5 BU	3036880	FBS 3-5 GY	3038972
	FBS 4-5	3030187	FBS 4-5 BU	3036893	FBS 4-5 GY	3038985
	FBS 5-5	3030190	FBS 5-5 BU	3036903	FBS 5-5 GY	3038998
	FBS 10-5	3030213	FBS 10-5 BU	3036916	FBS 10-5 GY	3039007
	FBS 20-5	3030226	FBS 20-5 BU	3036929	FBS 20-5 GY	3038671
	FBS 50-5	3038930	FBS 50-5 BU	3032114	FBS 50-5 GY	3032127
Pitch width: 6.2 mm / max. no-load current: 32 A						
Terminal blocks	FBS bridges (red)		FBS bridges (blue)		FBS bridges (gray)	
	Type	Item no.	Type	Item no.	Type	Item no.
PT(V) 4... PTS 4... MPT 4 UT 4... MUT 4... ST 4...	FBS 2-6	3030336	FBS 2-6 BU	3036932	FBS 2-5 GY	3032237
	FBS 3-6	3030242	FBS 3-6 BU	3036945	FBS 3-5 GY	3032240
	FBS 4-6	3030255	FBS 4-6 BU	3036958	FBS 4-5 GY	3032279
	FBS 5-6	3030349	FBS 5-6 BU	3036961	FBS 5-5 GY	3032266
	FBS 10-6	1008238	FBS 10-6 BU	3032198	FBS 10-5 GY	3032253
	FBS 20-6	3030271	FBS 20-6 BU	3032208	FBS 20-5 GY	3038671
	FBS 50-6	3030365	FBS 50-6 BU	3032211	FBS 50-5 GY	3032127

Product overview FBS plug-in bridges


Pitch width: 8.2 mm / max. no-load current: 41 A								
Terminal blocks	FBS bridges (red)		FBS bridges (blue)		FBS bridges (gray)		FBS bridges (CT)	
	Type	Item no.	Type	Item no.	Type	Item no.	Type	Item no.
XTV 6... PT(V) 6... UT 6... ST 6...	FBS 2-8	3030284	FBS 2-8 BU	3032567	FBS 2-8 GY	3032621	FBS 2-8-CT	3033830
	FBS 3-8	3030297	FBS 3-8 BU	3032619	FBS 3-8 GY	3032622	FBS 3-8-CT	3033831
	FBS 4-8	3030307	FBS 4-8 BU	3032570	FBS 4-8 GY	3032635	FBS 4-8-CT	3033832
	FBS 5-8	3030310	FBS 5-8 BU	3032583	FBS 5-8 GY	3032648		
	FBS 6-8	3032470	FBS 6-8 BU	3032596	FBS 6-8 GY	3032664		
	FBS 10-8	3030323	FBS 10-8 BU	3032677	FBS 10-8 GY	3032651	FBS 10-8-CT	3033833
Pitch width: 10.2 mm / max. no-load current: 57 A								
Terminal blocks	FBS bridges (red)		FBS bridges (blue)		FBS bridges (gray)			
	Type	Item no.	Type	Item no.	Type	Item no.	Type	Item no.
XTV 10... PT 10... UT 10... ST 10...	FBS 2-10	3005947					2-10	1103721
	FBS 3-10	3005949						
	FBS 5-10	3005948	FBS 5-10 BU	1040620				
Pitch width: 12 mm / max. no-load current: 76 A								
Terminal blocks	FBS bridges (red)							
	Type	Item no.						
XTV 16 PT 16 UT 16 ST 16	FBS 2-12	3005950						
Pitch width: 16 mm / max. no-load current: 101 A								
Terminal blocks	FBS bridges (red)							
	Type	Item no.						
PTPOWER 35 UT 35 ST 35	FBS 2-16	3005963						

Protective cap for cut-to-length FBS bridges			
Bridges	Type	Item no.	
FBS...-5 FBS...-6	FBSC	3012325	
FBS...-8	FBSC 8	1798933	


Wire bridges

Wire bridges

Wire bridges enable even longer distances to be bridged quickly and easily. Because the wire between the end points of the bridge is very flexible, it is also possible to establish non-adjacent bridging over several levels.



The wire bridges can be used to connect terminal blocks that are far apart. Compared to FBS bridges, contact tabs do not need to be removed in order to bridge terminal blocks.



The wire bridges can be used in all terminal blocks with a pitch of 5.2 mm and 6.2 mm.



The wire bridges make it easy to bridge levels. The advantage over PV bridges is that levels can be bridged, and even diagonal bridging is possible.

Wire bridges				
Terminal blocks	FBSW bridges (red)			
	Max. no-load current	Pitch width	Type	Item no.
XT 2,5 PT(V) 2,5 PTS 2.5 UT 2,5 ST 2.5	17.5 A	60 mm	FBSW N 2-5/60mm	1653820
		120 mm	FBSW N 2-5/120mm	1653821
		240 mm	FBSW N 2-5/240mm	1653822


PV potential bridges

PV potential bridges

The potential bridges are suitable for vertical level bridging of double-level terminal blocks or multi-level terminal blocks. For example, a double-level terminal block (PTTB 2,5) can be used to connect the lower and upper levels. NOTE: The double-level terminal blocks with the suffix ...PV already have a permanently integrated potential bridge, so a PV bridge is not required.



The PV bridges enable quick and easy bridging of double-level terminal blocks and multi-level terminal blocks. The bridges only connect levels that are directly below each other.



Connecting multiple level usually requires more than one PV bridge.




In addition to PV bridges, the portfolio also includes double-level terminal blocks and multi-level terminal blocks with integrated PV bridges. These terminal blocks are marked with the suffix "PV".

PV potential bridges				
Terminal blocks	RB bridge (red)			
	Max. no-load current	Type	Item no.	
QTTCB 1,5... XTTB 2,5... PTTB 2,5... PTTBS 2,5... STTB 2,5... PTTB 4... PT 2,5-3L... PT 2,5-4L...	32 A	FBS-PV	3032185	
PT 2,5-PE/3L... PT 4-PE/3L... UTTB 2,5... UTTB 4...	22 A	FBS-PV UT	3047358	
PT 2,5-4L/1P PT 2,5-4L/2P PT 2,5-PE/3L/2P ST 2,5-4L/2P-Z	10 A	FBS-PV PT 2,5-4L	3012318	
PTTB 1,5/S... PT 1,5/S-3L... and versions PT 1,5/S-PE/L/L	16 A	FBS 1,5/S-PV	3216263	


RB reducing bridges

RB reducing bridges

Unlike the standard FBS plug-in bridges, the reducing bridges (RB) connect terminal blocks with two different nominal cross-sections. This makes it possible to set up power supplies quickly and easily.



When setting up central power supplies, please note that the current values of the reducing bridges differ.



In contrast to a central supply, different current values must be observed for single-sided supply.



The portfolio of reducing bridges so extensive that you can choose the supply method for any connection technology.

RB reducing bridges (spring-cage terminal blocks)					
Terminal block (large cross-section)	Terminal block (small cross-section)	Single-sided supply	Central supply	RB bridges (red)	
				Type	Item no.
XT 2,5 ... PT(V) 2,5 ... ST 2,5 ...	PT 1,5/S	24 A	30 A	RB ST (2,5/4)-1,5/S	3214356
	XT 1,5 PT 1,5 / PTS 1,5 ST 1,5	31 A	31 A	RB ST (2,5/4)-1,5	3038943
	QTC 1.5	31 A	31 A	FBS 2-5	3030161
PT(V) 4 ... ST 4 ...	PT 1,5/S	24 A	40 A	RB ST (2,5/4)-1,5/S	3214356
	XT 1,5 / ST 1,5 ...	35 A	40 A	RB ST (2,5/4)-1,5	3038943
	QTC 1,5...	35 A	40 A	FBS 2-5	3030161
	XT 2,5 ... PT(V) 2,5 ... ST 2,5 ...	40 A	40 A		
	QTC 2,5 ...	40 A	40 A	FBS 2-6	3030336

Product overview RB reducing bridges

RB reducing bridges (spring-cage terminal blocks)					
Large cross-section	Small cross-section	Single-sided supply	Central supply	RB bridges (red)	
				Type	Item no.
XTV 6 ... PT(V) 6 ... ST 6 ...	PT 1,5/S	24 A	48 A	RB ST 6-1.5/S	3213250
	QTC 1,5 ...	35 A	40 A	RB ST 6-(2,5/4)	3030860
	XT 2,5 ... PT(V) 2,5 ... ST 2,5 ... QTC 2,5 ...	40 A	40 A		
	PT(V) 4 ... ST 4 ...	45 A	40 A		
XTV 10 ... PT 10 ... ST 10 ...	PT 1,5/S	24 A	48 A	RB ST 10-1.5/S	3213252
	QTC 1,5 ...	35 A	65 A	RB ST 10-(2,5/4)	3030873
	XT 2,5 ... PT(V) 2,5 ... ST 2,5 ... QTC 2,5 ...	40 A	65 A		
	PT(V) 4 ... ST 4 ...	45 A	65 A		
XTV 16 ... PT 16 ... ST 16 ...	PT 1,5/S	24 A	48 A	RB ST 16-1.5/S	3213254
	QTC 1,5 ...	35 A	70 A	RB ST 16-(2,5/4)	3030886
	XT 2,5 ... PT(V) 2,5 ... ST 2,5 ... QTC 2,5 ...	40 A	80 A		
	PT(V) 4 ... ST 4 ...	45 A	90 A		
	XTV 6 ... PT(V) 6 ... ST 6 ...	37 A	74 A	RB 16-6	3047072
PTPOWER 35 ...	XT 2,5 ... PT(V) 2,5 ... ST 2,5 ...	40 A	80 A	RB PTPOWER 35-ST (2,5/4)	3030900
	PT(V) 4 ... ST 4 ...	45 A	90 A		
	XTV 16 PT 16 ST 16	90 A	125 A	RB PTPOWER 35-ST 16	3032170
ST 35 ...	QTC 1,5 ...	35 A	70 A	RB ST 35-(2,5/4)	3030899
	XT 2,5 ... PT(V) 2,5 ... ST 2,5 ... QTC 2,5 ...	40 A	80 A		
	PT(V) 4 ... ST 4 ...	45 A	90 A		

Product overview RB reducing bridges

RB reducing bridges (screw terminal blocks)					
Large cross-section	Small cross-section	Single-sided supply	Central supply	RB bridges (red)	
				Type	Item no.
UT 4 ...	UT 2,5 ...	24 A	24 A	FBS 2-5	3030161
UT 6 ...	UT 2,5 ...	40 A	56 A	RB UT 6-(2,5/4)	3047251
	UT 4 ...	45 A	56 A		
	QTC 1,5 ...	35 A	56 A	RB UT 6-ST(2,5/4)	3047264
	XT 2,5 ... PT(V) 2,5 ... ST 2,5 ... QTC 2,5 ...	40 A	56 A		
	PT(V) 4 ... ST 4 ...	45 A	56 A		
UT 10 ...	UT 2,5 ...	40 A	65 A	RB UT 10-(2,5/4)	3047060
	UT 4 ...	45 A	65 A		
	QTC 1,5 ...	35 A	65 A	RB UT 10-ST(2,5/4)	3047086
	XT 2,5 ... PT(V) 2,5 ... ST 2,5 ... QTC 2,5 ...	40 A	65 A		
	PT(V) 4 ... ST 4 ...	45 A	65 A		
UT 16 ...	UT 2,5 ...	40 A	80 A	RB UT 16-(2,5/4)	3047073
	UT 4 ...	45 A	90 A		
	UT 6 ...	37 A	74 A	RB 16-6	3047072
	QTC 1,5 ...	35 A	70 A	RB UT 16-ST(2,5/4)	3047099
	XT 2,5 ... PT(V) 2,5 ... ST 2,5 ... QTC 2,5 ...	40 A	80 A		
	PT(V) 4 ... ST 4 ...	45 A	90 A		
UT 35 ...	UT 2,5 ...	40 A	80 A	RB UT 35-(2,5/4)	3047277
	UT 4 ...	45 A	90 A		
	UT 10 ...	57 A	114 A	RB UT 35-10	3032168
	UT 16	90 A	90 A	RB 35-16	3032169
	QTC 1,5 ...	35 A	70 A	RB UT 35-ST(2,5/4)	3047280
	XT 2,5 ... PT(V) 2,5 ... ST 2,5 ... QTC 2,5 ...	40 A	80 A		
	PT(V) 4 ... ST 4 ...	45 A	90 A		

Product overview RB reducing bridges

RB reducing bridges (bolt terminal blocks)					
Large cross-section	Small cross-section	Single-sided supply	Central supply	RB bridges (red)	
				Type	Item no.
RT 5 ...	RT 3 ... UT 2,5 ... UT 4 ...	40 A	56 A	RB UT 6-(2,5/4)	3047251
	QTC 1,5 ...	35 A	56 A	RB UT 6-ST(2,5/4)	3047264
	XT 2,5 ... PT(V) 2,5 ... ST 2,5 ... QTC 2,5 ... PT(V) 4 ... ST 4 ...	40 A	56 A		
RT 8 ...	RT 3 ...	40 A	56 A	RB ST 10-(2,5/4)	3030873
	UT 2,5...	40 A	65 A		
	UT 4 ...	45 A	65 A		
RB reducing bridges (fast-connection terminal blocks)					
Large cross-section	Small cross-section	Single-sided supply	Central supply	RB bridges (red)	
				Type	Item no.
QTC 2,5...	QTC 1,5 ...	31 A	31 A	FBS 2-5	3030161

Further information on the short-circuit currents, etc., can be found in the technical data documented on the item.

FBSR plug-in bridges

FBSR plug-in bridges

The plug-in mechanism on the FBSR plug-in bridges makes them easy to insert and remove. This type of bridge is recommended for applications where the plug-in bridge needs to be removed from time to time. To shorten the bridge and remove the contact tongues, just use the same steps as for FBS bridges.


Reduced current values

The FBSR bridges are a more cost-effective option compared to the standard bridges in the FBS series. In contrast to the FBS versions, however, the FBSR versions are suitable for lower current values. Choosing the right bridge can improve both the efficiency and cost-effectiveness of an application.




Comparison of current values between FBSR and FBS


Bridge (FBSR)	Current value (FBSR)	Bridge (FBS)	Current value (FBS)
-	-	FBS 2-3,5	17.5 A
-	-	FBS 2-4	17.5 A
FBSR 2-5	17.5 A	FBS 2-5	24 A
FBSR 2-6	24 A	FBS 2-6	32 A
FBSR 2-8	32 A	FBS 2-8	41 A
-	-	FBS 2-10	57 A
-	-	FBS 2-12	76 A
-	-	FBS 2-16	101 A



The FBSR bridges have a different clamping technology than the FBS plug-in bridges. This makes inserting and removing the plug-in bridges easier, but at the expense of the permitted current values.



As with the FBS plug-in bridges, the individual contact tabs can be removed.



The FBSR plug-in bridges can be pulled out of the bridge shaft easily with a screwdriver.


Product overview FBSR plug-in bridges

Pitch width: 3.5 mm / max. no-load current: 17.5 A		
Terminal blocks	FBS bridges (red)	
	Type	Item no.
XT 2,5... PT(V) 2,5... PTS 2,5... MPT 2,5... UT 2,5... MUT 2,5... ST 2,5... STS 2,5...	FBSR 2-5	3033702
	FBSR 3-5	3001591
	FBSR 4-5	3001592
	FBSR 5-5	3001593
	FBSR 10-5	3033710
Pitch width: 6.2 mm / max. no-load current: 24 A		
PT(V) 4... PTS 4...MPT 4 UT 4...MUT 4... ST 4...	FBSR 2-6	3033715
	FBSR 3-6	3001594
	FBSR 4-6	3001595
	FBSR 5-6	3001596
	FBSR 10-6	3033716
Pitch width: 8.2 mm / max. no-load current: 32 A		
XTV 6... PT(V) 6... UT 6... ST 6...	FBSR 2-8	3033808
	FBSR 3-8	3001597
	FBSR 4-8	3000585
	FBSR 5-8	3033809
	FBSR 10-8	3001599
	FBSR 16-8	3033816

FBSRH short-circuit plugs

FBSRH short-circuit plugs

The FBSRH short-circuit plugs are similar to the FBSR plug-in bridges. They also connect potentials, but come with an additional extraction tool, because these plugs are not intended to remain in place permanently. The FBSRH short-circuit plugs are only intended for generating a short circuit for testing purposes.



Like the other plug-in bridges, the short-circuit plugs can also be plugged in without tools.



The contact tabs can also be cut out easily using the CUTFOX-FBS.



In contrast to the plug-in bridges, the short-circuit bridges can be removed easily by hand thanks to the extraction tool.

Pitch width: 6.2 mm / max. no-load current: 24 A		
Terminal blocks	FBSRH bridges (red)	
	Type	Item no.
PT(V) 4... PTS 4...MPT 4 UT 4...MUT 4... ST 4...	FBSRH 2-6	3033812
Pitch width: 8.2 mm / max. no-load current: 32 A		
XTV 6... PT(V) 6... UT 6... ST 6...	FBSRH 2-8	3033802
	FBSRH 3-8	3033803
	FBSRH 4-8	3033804

FBSL plug-in bridges

FBSL plug-in bridges

The FBSL plug-in bridges have the same properties as the FBS standard plug-in bridges. The only difference is the length of the contact tabs. The contact tabs are shorter and can therefore only be used for special terminal blocks. These include the mini terminal blocks from the MUT series and special terminal blocks from the UTI installation terminal block range.



Pitch width: 3.5 mm / max. no-load current: 17.2 A		
Terminal blocks	FBSRH bridges (red)	
	Type	Item no.
MUT 1.5	FBSL 2-3.5	1301365
	FBSL 3-3.5	1301366
	FBSL 10-3.5	1301367
Pitch width: 8.2 mm / max. no-load current: 32 A		
UTI 6...	FBSL 2-8	3030324
	FBSL 3-8	3030325
	FBSL 4-8	3030326
	FBSL 5-8	3030327
	FBSL 10-8	3030328

Other products in the CLIPLINE complete portfolio

In addition to the plug-in bridges listed above, the CLIPLINE complete portfolio also includes special bridge bars and short-circuit plugs. However, as these products have special properties and are not suitable for the general terminal block portfolio, they are not included in this PDF.

The following pages will give you an overview of these special products. Further information on this can be found on the respective terminal block or directly on the item.



SB-ME bridge bars

The SB-ME bridge bars were developed for testing transformer terminal blocks. The bridges can be switched with a slider. The bridges can remain plugged in. To prevent unintentional operation, the slider can be secured with two screws.



SB-MEA bridge bars

The SB-MEA bridge bars have been specially developed for the test-disconnect terminal blocks of the MEA line. When inserted in the correct functional slot, the bridges ensure an automatic transformer short circuit as soon as the disconnect lever is actuated.



SCP and KSS short-circuit plugs

The SCP short-circuit plugs are designed for short-circuiting adjacent test-disconnect terminal blocks. They can be used as temporary current transformer short-circuiting options for maintenance and commissioning tasks on measuring and safety equipment in power generation systems. Connecting or disconnecting short-circuit plugs is only permitted while the power supply and all loads are disconnected.

Open communication with customers and partners worldwide

Phoenix Contact is a global market leader based in Germany. We are known for producing forward-thinking products and solutions for the comprehensive electrification, networking, and automation of all sectors of the economy and infrastructure. With a global network, we maintain close relationships with our customers, something we believe is essential for our common success.

You can find your local partner at
phoenixcontact.com

